


PRODUCT NUMBER: 0921-5-15-20-77-14-11-0

www.mill-max.com
DATA SHEET





0921-5-15-20-77-14-11-0 SPECIFICATIONS

General Info			
Description	Through Hole Mount Spring-Loaded Pin		
Plunger Type:	Round		
Mounting Feature ² :	Through-Hole Solder Mount		
Mounting Hole:	.070" (1,778mm)		
Inital Height: .256" (6,502mm)			
Stroke:	.090" (2,286mm)		
Packaging:	Packaged in Bulk		
RoHS ³ :	Yes		
Product Lifecycle ⁴ :	Active		

Materials				
Shell Material ⁵ : Brass Alloy				
Shell Plating ⁶ : 20 p	ו" Gold over Nickel			
Spring Plating ⁷ : 10 µ	ו" Gold over Nickel			

Technical Specs			
Durability:	Up to 1,000,000 Cycles @ Mid-Stroke		
Operating Temperature Range ⁸ :	-55/+125° C		
Current Rating ⁹ :	See Spring Specifications Below		
Contact Resistance ¹⁰ :	See Spring Specifications Below		
Shock ¹¹ :	No Elect. Discontinuity > 1µs @ 50g		
Vibration ¹² :	No Elect. Discontinuity > 1μs @ 10-2000HZ, 20 G		

NOTES:

1. Standard Tolerances:

Lengths +/-.006" (0,15)

Diameters: +/-.002" (0,051)


Angles: +/- 2°

- 2. For through-hole solder mounting of this part, the suggestion is to make the finished hole size, at its minimum, .004" larger than the diameter being soldered into the mounting hole.
- Mill-Max products labeled with the RoHS symbol are compliant with all three ROHS Directives. All of our products previously described as RoHS (2002/95/EC) and RoHS-2 (2011/65/EC) are also compliant with RoHS-3 (2015/863/EU).
- 4. Part is Active and in Production, No Scheduled Obsolescence
- 5. Brass Alloy 360 per ASTM B 16, or 385 per ASTM B455
- 6. GOLD per ASTM B 488, Type 1 (99.7% min. gold), Code C (130-200 HK (Knoop hardness)); NICKEL per ASTM B 689, Type 2 (Bright)
- 7. GOLD per ASTM B 488, Type 1 (99.7% min. gold), Code C (130-200 HK (Knoop hardness)), NICKEL per ASTM B 689, Type 2 (Bright)
- 8. Storage per IEC 60512-11-(4,9,10,12) and peak operating temperature per IEC 60512-5-2, Test 5b
- 9. Per IEC 60512-5-2; Current Carrying Capacity; Current Derating
- 10. Per EIA-364-23C: Low Level Contact Resistance.
- 11. Per IEC 60512-6-3: Test 6c: Shock
- 12. Per IEC 60512-6-4: Test 6d: Vibration (sinusoidal)

ADDITIONAL PARTS, PACKAGING, & ASSEMBLY INFO


0921-0-XX-20-76-14-11-0

Solder mount in .070 [1,78] min. mounting hole




0921-1-XX-20-7X-14-11-0


Solder mount in .070 [1,78] min. mounting hole



0921-0-57 Tape & Reel Details




0921-1-57 Tape & Reel Details




0921-5-15-20-77-14-11-0

Solder mount in .070 [1,78] min. mounting hole



SPRING:

#77 SPRING STANDARD FORCE SPRING	Full Stroke Capability: .090"± .005" [2,29 ± 0,127]	
Spring Material: Beryllium Copper Alloy 172	Force @ Mid. Stroke: 60 g ± 20 g	
Mid. Stroke: .045" [1,14]	Initial Force (Pre-Load): 5 g	



The stroke, force and current rating values are measured using spring pins with an internal construction per the design specification. Individual spring pin performance may vary from these values based on design differences.

Material	Beryllium Copper	Grams Force	60.0000g
Max Stroke	0.09	Maximum Current	7A @ 30° C Temp. Rise
Maximum Operating Temp @ Max Current	120.00° C	20% De-rated Maximum Current	5.60A
Contact Resistance	20.00mΩ Max		

ADDITIONAL NOTES AND SPECIFICATIONS

In the interest of improved design, quality and performance, Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. The tolerance on dimensions of critical to function features is typically held tighter than the stated standard tolerances, such as press-fits, holes and lengths affecting the coplanarity of SMT products. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.

RELATED LINKS AND DOCUMENTS

 $Engineering\ Notebook: (\ \underline{https://www.mill-max.com/engineering-notebooks/spring-loaded-pogo-pins-connectors}\)$

Environmental Compliance: (https://www.mill-max.com/rohs)