

**Industrial Ethernet
IE-C5DB4WE0015MCSA20-E**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Assembled IE lines, railway cable RW (reduced wire), cat. 5, PUR, black, RJ45 plug, no tools required, IP20 and M12 straight pin

General ordering data

Type	IE-C5DB4WE0015MCSA20-E
Order No.	1220310015
Version	System cable, M12 D-code – IP 67 straight pin, RJ45 IP 20 no tools needed, Cat.5 (ISO/IEC 11801), Radox GKW S, 1.5 m
GTIN (EAN)	4050118350784
Qty.	1 pc(s).

Industrial Ethernet IE-C5DB4WE0015MCSA20-E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	1.5 m	Length (inches)	0.059 inch
Net weight	128 g	Insulation cross-section	1.58 mm

Temperatures

Operating temperature, max.	90 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	90 °C	Storage temperature, min.	-40 °C
Operating temperature	-40 °C...90 °C	Storage temperature	-40 °C...90 °C
Installation temperature			

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Standards

Fire safety for railway vehicles	According to DIN 5510-2 fire safety levels 1,2,3,4, According to BS 6853, According to EN50288-2-2, According to EN 45545, HL1 - HL3	Fire protection in buses	according to ISO 6722-1 5.22 (UN ECE-R 118.01)
Flames propagate vertically on bundled cables	According to BS4066-3, DIN EN 50266-2-5, According to IEC 60332-3-25 D	Impervious to smoke	According to BS 6853 Appendix D, in accordance with EN 50268-2, According to IEC 61034-2
Corrosiveness of fumes	to IEC 60754-2	Hydrogen halide content	According to EN-50267-2-1, According to IEC 60754-1
Poisonous gases	According to BS 6853 Appendix B	Fluorine content	According to EN 60684-2 Section 45.2
Multi-wire metallic data and control cable	According to EN50288-2-2		

Cable structure

Strands	7	Cross-section	2*2*AWG 22/7 - 2*2*0.36 mm ²
Insulation cross-section	1.58 mm	Shielding	SF/UTP
Material sheath	Radox GWK S	Sheath diameter, min.	6.2 mm
Sheath diameter, max.	7 mm	Sheathing colour	black

Electrical properties of cable

Category	Cat.5 (ISO/IEC 11801)
----------	-----------------------

Mechanical and material properties of cable

Min. bending radius, repetitive	6 *diameter	Abrasion resistance	very good
Resistance to oils	in accordance with EN 50306-3	Halogen	halogen-free, according to IEC 60754-2
Corrosiveness of fumes	to IEC 60754-2	Impervious to smoke	According to BS 6853 Appendix D, in accordance with EN 50268-2, According to IEC 61034-2

**Industrial Ethernet
IE-C5DB4WE0015MCSA20-E**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
plug

Connector left	M12 D-code – IP 67 straight pin	Connector right	RJ45 IP 20 no tools needed
----------------	------------------------------------	-----------------	-------------------------------

Classifications

ETIM 6.0	EC002599	eClass 6.2	27-06-91-90
eClass 7.1	27-06-91-90	eClass 8.1	27-06-91-90
eClass 9.0	27-06-03-08	eClass 9.1	27-06-03-08

Approvals

ROHS	Conform
------	---------

Downloads


Brochure/Catalogue	FL FIELDWIRING EN PI PROFINET CABLING EN
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN

Data sheet**Industrial Ethernet
IE-C5DB4WE0015MCSA20-E**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings**Detailed drawing**

RJ45		M12
1	yellow	1
3	white	2
2	orange	3
6	blue	4



**Industrial Ethernet
IE-C5DB4WE0015MCSA20-E**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Accessories
Screwty® cable gland tool

The ideal tool for any application

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
Screwty Set	1910000000	Tools, Bolting tool	4032248436842	1 pc(s).
Screwty- M12	1900000000	Tools, Cable gland tool for moulded M12 lines	4032248375868	1 pc(s).

TM HF 18 mm


The TM sleeves contain no halogens and virtually no pollutants. The sleeves are equipped with the TM-I 12 or TM-I 18 tags. They cover a wide range of applications for cables and lines. This system has particularly proved its worth in traffic engineering. The slim design guarantees firm seating on the conductor.

- Halogen-free
- The slim design guarantees firm seating on the conductor
- TMX 18 for mounting with cable-ties (width 3.6 mm)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
TM 4/18 HF/ HB	1719850000	TM, Socket x 11.4 mm, Polyethylene LD, Colour code: Transparent, Conductor O.D.: 6 - 10 mm	4008190353209	500 pc(s).

**Industrial Ethernet
IE-C5DB4WE0015MCSA20-E**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Accessories

Tool



Tools for stripping the sheathing from uncut power lines and outlet lines, plus screwdrivers for installing Pick-to-Light components.

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
Screwty Set - DM	1920000000	Tools, Bolting tool	4032248436859	1 pc(s).
Screwty-M12- DM	1900001000	Tools, Cable gland tool for moulded M12 lines	4032248436408	1 pc(s).

TM HF 12 mm



The TM sleeves contain no halogens and virtually no pollutants. The sleeves are equipped with the TM-I 12 or TM-I 18 tags. They cover a wide range of applications for cables and lines. This system has particularly proved its worth in traffic engineering. The slim design guarantees firm seating on the conductor.

- Halogen-free
- The slim design guarantees firm seating on the conductor
- TMX 18 for mounting with cable-ties (width 3.6 mm)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
TM 4/12 HF/ HB	1719840000	TM, Socket x 11.4 mm, Polyethylene LD, Colour code: Transparent, Conductor O.D.: 6 - 10 mm	4008190353193	500 pc(s).