Filtering/Line Conditioning — Product Selection Guide

- Find your application in the left column.
- Then look across for the appropriate product.

	PRODUCTS			
APPLICATIONS	Islatrol® IE Series	Islatrol® IC+/LRIC+ Series	Islatrol® SP-6TVN Series	Islatrol® RM Series
Programmable Logic Controllers	Comments of the second			
Control Panels (AC Power)	Company of the second s			
Various OEM Equipment	Comments of the second			
Home Entertainment/Office			· · · · · · · · · · · · · · · · · · ·	
AC Rack Equipment				· = + 11 [14] + (*



Islatrol[®] IE Series Active Tracking Filter[®]

Series connected DIN/flange mount high-frequency noise filter/surge suppressor. Ideal applications include critical industrial loads drawing up to 20 Amps of continuous current. Typical applications include any microprocessor-based products, including industrial PLCs, OEM applications, and motion control systems.

Features

- Multi-staged design, combining a unique hybrid clamping network with the active tracking technology of the Islatrol® family
- Surge current capacity 45,000 Amps
- Transient protection in all modes: line to neutral, line to ground, and neutral to ground
- LED status indication and form C contact for remote indication
- DIN mountable enclosure
- UL 1449, 1283, CUL recognized, CE
- 10 year warranty

Performance Technical Specifications General Technical Specifications

UL 1449 Surge Vo	ltage Rating	
120V Normal Mod	e	330 Volts
120V Common Mo	ode	400 Volts
240V Normal Mod	e	600 Volts
240V Common Mo	ode	800 Volts
Peak Surge Curre	nt Capability (8	x 20 μ s)
Line to Neutral		15,000 Amps
Line to Ground		15,000 Amps
Neutral to Ground		15,000 Amps
Total		45,000 Amps
Frequency Respo	nse (Forward-R	everse)
Normal Mode	100 kHz to 50	MHz - 90 dB Min
Common Mode	5 MHz to 50	MHz - 60 dB Min
Typical Category A	Ringwave (6 kV,	200 A, 100 kHz)
Normal Mode/Co	mmon Mode	
3 Amp		1 V/300 V
5 Amp		0.7 V/292 V
10 Amp		0.7 V/300 V
20 Amp		0.7 V/300 V
Typical Category B	Ringwave (6 kV,	500 A, 100 kHz)
Normal Mode/Co	mmon Mode	
3 Amp		178 V/300 V
5 Amp		162 V/291 V
10 Amp		153 V/300 V
20 Amp		200 V/300 V

MCOV 120 Volt 150 VRMS 275 VRMS 240 Volt Line Frequency 47 - 63 Hz Terminal Connection Mounting Type DIN/Flange Weight < 3 lbs **Response Time** Normal Mode < 0.5 ns Common Mode < 5 ns **Operating Temperature** -40°C to +45°C Derate Linearly to 60% at +70°C 0% to 95% **Operating Humidity**

Ordering Information

Voltage*	Continuous Current	Model
120 V	3 Amps	IE-103
120 V	5 Amps	IE-105
120 V	10 Amps	IE-110
120 V	20 Amps	IE-120
1201		
Voltage*	Continuous Current	Model
Voltage * 240 V	Continuous Current 3 Amps	Model
Voltage* 240 V 240 V	Continuous Current 3 Amps 5 Amps	Model IE-203 IE-205
Voltage * 240 V 240 V 240 V	Continuous Current 3 Amps 5 Amps 10 Amps	Model IE-203 IE-205 IE-210
Voltage* 240 V 240 V 240 V 240 V 240 V	Continuous Current 3 Amps 5 Amps 10 Amps 20 Amps	Model IE-203 IE-205 IE-210 IE-220

* All voltage configurations are single phase - 2 wire + gnd.

Dimensional Diagram



Islatrol[®] IE Series

Active Tracking Filter[®]





Islatrol[®] IC+/LRIC+ Series

Active Tracking Filter®

Series connected high-frequency noise filter with transient protection. Offers the flexibility of either receptacle/line cord connection or hard-wired connection to critical loads (up to 30 Amperes). Applications include industrial or office equipment, computers placed in harsh environments.

Features

- Typically reduces normal mode transients to +/-2 volts
- Surge current capacity 45,000 Amps
- Transient protection in all modes: line to neutral, line to ground, and neutral to ground
- LED power indication
- UL 1283, CSA recognized
- 10 year warranty

MCOV

IVICOV	
120 Volt	150 VRMS
240 Volt	275 VRMS
Line Frequency	47 - 63 Hz
Response Time	
Normal Mode	< 0.5 ns
Common Mode	< 5 ns
Operating Temperature	

-40°C to +45°C at Full Loa		
Derate Linearly to 60% at +70		
Operating Humidity	0% to 95%	
Peak Surge Current C	apability (8 x 20 µs)	
Line to Neutral	15,000 Amps	
Line to Ground	15,000 Amps	
Neutral to Ground	15,000 Amps	
Load Surge Current R	ating	
10 mSec	5 x Nomina	
1 sec	3 x Nomina	
10 sec	2 x Nomina	
Packaging		

• High Impact Plastic Case

- Vacuum Impregnated Magnetics
- Epoxy Encapsulated

Frequency Response (Forward-Reverse)

Normal Mode	100 kHz to 50 MHz - 90 dB Min
Common Mode	5 MHz to 50 MHz - 60 dB Min

Model	Normal	Common
IC+102 / LRIC+102	1.0/0.9	302 / 287
IC+105 / LRIC+105	0.7 / 0.8	292 / 307
IC+107 / LRIC+107	0.7 / 0.7	302 / 293
IC+115 / LRIC+115	0.7 / 0.7	304 / 306
IC+130 / IC+202	0.5/1.1	306 / 536
IC+205 / IC+207	1.5/0.8	628/616
IC+215 / IC+230	0.6/0.9	572 / 566
Typical Category B Ring	gwave (6 kV, 500) A, 100 kHz)
Model	Normal	Common
IC+102 / I RIC+102	178/188	302/285

Typical Category A Ringwave (6 kV, 200 A, 100 kHz)

IC+105 / LRIC+105	162 / 191	291/300
IC+107 / LRIC+107	173 / 190	300 / 298
IC+115 / LRIC+115	153 / 149	307 / 309
IC+130 / IC+202	241 / 302	299 / 532
IC+205 / IC+207	378 336	594 / 596
IC+215 / IC+230	272 342	548 / 578

Note: All measurements in volts. IEEE test results with no AC applied. Normal mode—L1-N or L1-L2; Common mode—L-G, N-G or L1-G, L2-G.

System Design

Series Blocking Inductors voltage blocking current smoothing inductors

Shunt Absorbing Components sine wave tracking circuitry

MOV Transient Protection high-energy transient protection line to neutral, line to ground, neutral to ground

Pulse Capacitor

high-frequency noise absorption

Connection Diagram





Islatrol[®] IC+/LRIC+ Series

Active Tracking Filter®

Dimensional Diagram



S-15R RECEPTACLE



Ordering Information

120 VAC Models with barrier strip at input and output/with wire leads at input and output (WL)

Model	Rated Output (Amps)	Case Dimensions (In) A x B x C	Mounting Flange Dimensions (In) D x E x F x G	Screw Size	Weight (lbs)
IC+102 / IC+102WL	2.5	4 x 2.88 x 1.81	4.38 x 2.12 x 5.31 x 0.19	#6	1.0
IC+105 / IC+105WL	5.0	4 x 2.88 x 1.81	4.38 x 2.12 x 5.31 x 0.19	#6	1.3
IC+107 / IC+107WL	7.5	4.75 x 4.75 x 2.35	5.25 x 3.50 x 6.25 x 0.19	#6	2.0
IC+115 / IC+115WL	15	6.25 x 4.75 x 2.35	6.75 x 3.50 x 7.75 x 0.19	#8	3.5
IC+130 / IC+130WL	30	7.75 x 4.75 x 2.35	8.25 x 3.50 x 9.00 x 0.19	#8	6.0

120 VAC Models with 5 foot line cord and single NEMA 5-15 receptacle

			-		
Model	Rated Output (Amps)	Case Dimensions (In) A x B x C	Mounting Flange Dimensions (In) D x E x F x G	Screw Size	Weight (lbs)
LRIC+102	2.5	4.5 x 3.0 x 1.88	N/A	N/A	1.3
LRIC+105	5.0	4.5 x 4.5 x 2.38	N/A	N/A	2.0
LRIC+107	7.5	6.0 x 4.5 x 2.38	N/A	N/A	2.3
LRIC+115	15	7.5 x 4.5 x 2.38	N/A	N/A	4.0

240 VAC Models with barrier strip at input and output/with wire leads at input and output (WL)

Model	Rated Output (Amps)	Case Dimensions (In) A x B x C	Mounting Flange Dimensions (In) D x E x F x G	Screw Size	Weight (lbs)
IC+202 / IC+202WL	2.5	4 x 2.88 x 1.81	4.38 x 2.12 x 5.31 x 0.19	#6	1.3
IC+205 / IC+205WL	5.0	4.75 x 4.75 x 2.35	5.25 x 3.50 x 6.25 x 0.19	#6	2.0
IC+207 / IC+207WL	7.5	6.25 x 4.75 x 2.35	6.75 x 3.50 x 7.75 x 0.19	#8	3.3
IC+215 / IC+215WL	15	7.75 x 4.75 x 2.35	8.25 x 3.50 x 9.00 x 0.19	#8	5.8
IC+230 / IC+230WL	30	7.75 x 4.75 x 2.35	8.25 x 3.50 x 9.00 x 0.19	#8	6.0



Islatrol® E Series Active Tracking Filter® for DC Voltages

Provides continuous sine wave Active Tracking[®] filtration, normal mode (line to line or line to neutral) for protection from spikes, transients, and noise on AC power line. Available in either hardwired, printed circuit board mount, wire lead mount or single receptacle/line cord configurations, single phase or three phase, 50/60 Hz.

Ordering Information

35 VDC, printed circuit board mount or with wire leads at input and output (Add "WL" suffix in place of "PC" suffix.)

Model Number	Amperes	Weight (lbs)
E-025PC	0.25	1
E-05PC	0.50	1
E-1PC	1.00	1

Islatrol® Active	Tracking Filters®	carry a	10 year warranty
------------------	-------------------	---------	------------------

Model Number	Amperes	Weight (lbs)
E-1 (only 35 VDC)	1.0	3
E-2	2.5	3
E-5	5.0	3
E-7	7.5	3
E-15	15.0	9
E-30	30.0	9
E-50	50.0	10
E-100	100.0	15

Filtering/Line Conditioning



Repositionable Outlets

Islatrol[®] — SP-6TVN

Industrial Strength Surge Suppression (Series)

The Islatrol[®] SP-6TVN is an industrial-strength surge suppression/filtering device that plugs into a standard duplex receptacle. It features uniquely designed repositionable outlets for easy installation behind desks and other furniture. It protects your sensitive home or office equipment, including TVs, home theaters, satellite dishes, computers, printers, copiers, and fax machines, from damaging power disturbances traveling through your wiring into your electrical outlets.

Features

- Plugs into standard 120 V, 15 Amp electrical outlet
- Total peak surge current capacity of 39,000 Amps
- Cables for telephone, video, and data connections
- Repositionable outlets rotate to accommodate available space
- Perfect for tight spaces, behind furniture and appliances
- Intelligent monitoring against improper wiring/grounding
- 60 dB maximum high frequency
- Operational indicator lamp
- 5 year limited warranty

General Technical Specifications

AC Power Protection

Nominal Operating Voltage	120 VAC, Single Phase
Operating Voltage Range	120 VAC +/- 10%
Operating Frequency Range	47 — 63 Hz
Rated Output (Amps)	15 Amperes
ANSI/IEEE C62.41 Category	Category A & B
Connection Type	(6) 5-15R Receptacles and 5-15P Plug
Phase Configuration	2 Wire + Gnd
Size	7.5 x 4.75 x 1.75 (Inches)
Enclosure	High Impact Plastic
Weight	2.0 lbs (0.9 kgs)
Modes Of Protection	L-N, L-G, N-G
Indication of Suppression Status	Status Indicator
Response Time	< .5 ns Normal Mode
Certifications	UL 1449 Listed
Warranty	5 Year

ANSI/IEEE C62.41 Cat A Ringwave (6 kV, 200 A, 100 kHz)

Normal Mode	265 V
Common Mode	290 V

ANSI/IEEE C62.41 Cat B Ringwave (6 kV, 500 A, 100 kHz)

Normal Mode	-		275 V
Common Mode			290 V

Frequency Response

130 VAC

Normal Mode	60 dB Maximum, forward/reverse, 100 kHz to 50 MHz
Common Mode	40 dB Maximum, forward/reverse, 5 MHz to 50 MHz

Network

Type RJ-45

.

Low Voltage Protection			
	Video 1 & 2	Phone	
Connection Type	Type "F"	Type RJ-11	
Cables Provided	6'(2x) Type "F"	6' RJ-11 Male	

Cables Provided	6'(2x) Iype "F" 6'Ends	6'RJ-11 Male 6'Ends	6 RJ-45 Male Ends
Peak Surge Current	5 kA (8 x 20 μs)	2 kA (10 x 1000 μs)	3 kA (8 x 20 μs)
Capacitance	<12 pf	<50 pf	<70 pf
Protection Level	L-G	T-R, T-G, R-G	L-G (8 Lines)
Clamping Voltage (DC)	145 V	270-350 V	30 V
Attenuation	1 dB @ 2 Ghz	N/A	N/A

Maximum Continuous Operating Voltage (MCOV)
Line to Neutral	

Peak Surge Current (8 x 20 ms)	12 000 4
Line to Neutral	13,000 Amps
Line to Ground	13,000 Amps
Neutral to Ground	13,000 Amps
Total	39,000 Amps



Model shown: RM-115-10 RM

Islatrol[®] — RM Series

This line of AC surge protectors is ideal for protecting the power feeding valuable rack equipment. All models provide ten protected outlets on the back and two protected convenience outlets on the front. This series provides 40,000 Amps of surge protection and up to 60 dB of high-frequency noise filtering. Status LEDs indicate the correct power is coming to the unit, whether the unit is properly grounded and whether the surge components are still in tact. Units are available with an optional digital meter, mounted on the front of the unit, that will monitor the voltage, current and power of the protected equipment.

Features

- 40 kA surge protection
- 60 dB max noise filtering
- 15 & 20 A models available
- Power, ground and surge status indicators
- Digital meter
- Optional twist lock plug
- 1 year warranty

General Technical Specifications

Model	Voltage	Amperage	Plug (NEMA)	Receptacles (NEMA)	Digital Meter	Locking Plug
RM-115-10RM	120 V	15 A	5-15P	5-15R	Yes	No
RM-120-10RM	120 V	20 A	5-20P	5-20R	Yes	No
RM-120-10RML	120 V	20 A	L5-20P	5-20R	Yes	Yes

Rackmount AC Power Protection

Rated Voltage	120 V
Rated Current	15 A & 20 A
Peak Surge Current	20 kA/mode, 40 kA/phase
Response Time	<5 ns
EMI/RFI Filtering	60 dB Max
LED Indicators	Green-Power on Green-Ground OK Green-Surge Circuit OK
Digital Meter (Optional)	Voltage Amps, Watts, VA, Hz, PF, Kwh, and Clock
Input Power 15 A Models	SJT 14/3C Power Cord (15 ft) with NEMA 5-15P Plug
20A Models	SJT 12/3C Power Cord (15 ft) with NEMA 5-20P Plug NEMA L5-20P Plug- Optional

Front- (2) NEMA 5-15R
Back- (10) NEMA 5-15R
Front- (2) NEMA 5-20R
Back- (10) NEMA 5-20R
Thermal Protected MOVs
Circuit
1.75"H x 19"W x 3.8"D (1U)
UL1449
1 Year