

REVISION C


DESIGNED & DIMENSIONED IN MILLIMETERS

OPA-X-X-XX **PORTS** <u>FOOTPRINT</u> SINGLE: -S **BLANK STANDARD** DOUBLE: -D <u>FLANGE</u> -F: FULL OPPOSED: -1 ALIGNED: -2


DO NOT SCALE FROM THIS PRINT







OPA-S-X-F



NOTES:

1. RECOMMEND USE OF M2.5 OR 4-40 SCREW, OR SCREW WITH NUT, SCREW HEAD DIAMETER & NUT WIDTH ≤ 5mm (SCREW & NUT NOT PROVIDED). RECOMMEND 2in-lbf TORQUE FOR SCREW MOUNT APPLICATIONS

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. TOLERANCES ARE:

2°

DECIMALS ANGLES X.X: ±0.3 X.XX: ±0.05 X.XXX: ±0.025

MATERIAL:

CONSENT OF SAMTEC, INC. DO NOT SCALE DRAWING

SHEET SCALE: 2:1

PROPRIETARY NOTE

SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR

THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO

OR IRANSPERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN

520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

DESCRIPTION


OPTICAL PANEL ADAPTER


DWG. NO.

OPA-X-X-XX

BY: JEAN W. 02/05/2015 SHEET 1 OF 3

F:\DWG\MISC\MKTG\OPA-X-X-X-XX-MKT.SLDDRW







RECOMMENDED MOUNTING CUTOUT OPA-D-X-F

NOTES:

- 1. ALSO COMPLIANT WITH FOCIS STANDARD TOLERANCE OF ±0.25mm
 2. RECOMMEND USE OF M2 OR 2-56 SCREW, OR SCREW WITH NUT,
 (SCREW & NUT NOT PROVIDED).
 RECOMMEND 2in-lbf TORQUE FOR SCREW MOUNT APPLICATIONS.





PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.

520 PARK EAST BLVD, NEW ALBANY, IN 47150

PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

SHEET SCALE: 2:1

DESCRIPTION:

OPTICAL PANEL ADAPTER

DWG. NO.

OPA-X-X-XX


BY: JEAN W. 02/05/2015 SHEET 2 OF 3


REVISION C

MATERIALS TABLE						
PART NUMBER	ADAPTER BODY	SPRING CLIP	DUST CAP			
OPA-S-1-F	POLYETHERIMIDE	STAINLESS STEEL	POLYCARBONATE			
OPA-S-2-F	POLYETHERIMIDE	STAINLESS STEEL	POLYCARBONATE			
OPA-D-1-F	POLYETHERIMIDE	STAINLESS STEEL	POLYCARBONATE			
OPA-D-2-F	POLYETHERIMIDE	STAINLESS STEEL	POLYCARBONATE			

COLOR TABLE				
PART NUMBER	ADAPTER BODY	DUST CAP		
OPA-S-1-F	BLACK	CHARCOAL		
OPA-S-2-F	GRAY	CHARCOAL		
OPA-D-1-F	BLACK	CHARCOAL		
OPA-D-2-F	GRAY	CHARCOAL		

BOM TABLE						
PART NUMBER	BOM ITEM	DESCRIPTION	QTY	COST QTY		
OPA-S-1-F	CCS-185473-01-CN	BULKHEAD ADAPTER	1	1		
	BAG-SS-06X08-Z	PACKAGING BAG	0.02	0.02		
	LABEL-4X2	LABEL	0	0.00001		
OPA-S-2-F	CCS-185473-02-CN	BULKHEAD ADAPTER	1	1		
	BAG-SS-06X08-Z	PACKAGING BAG	0.02	0.02		
	LABEL-4X2	LABEL	0	0.00001		
OPA-D-1-F	CCS-185473-03-CN	BULKHEAD ADAPTER	1	1		
	BAG-SS-06X08-Z	PACKAGING BAG	0.04	0.04		
	LABEL-4X2	LABEL	0	0.00002		
OPA-D-2-F	CCS-185473-04-CN	BULKHEAD ADAPTER	1	1		
	BAG-SS-06X08-Z	PACKAGING BAG	0.04	0.04		
	LABEL-4X2	LABEL	0	0.00002		





PACKAGING QUANTITY				
PART NUMBER	MAX PER BAG			
OPA-S-1-F	50			
OPA-S-2-F	50			
OPA-D-1-F	25			
OPA-D-2-F	25			

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY 10 SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS TO USE FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.

SHEET SCALE: 2:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

DESCRIPTION:

OPTICAL PANEL ADAPTER

DWG. NO.

OPA-X-X-XX

BY: JEAN W.

02/05/2015 SHEET 3 OF 3