SPECIFICATIONS


(RoHS Compliant)

 Model Number:
 CR4028-LD24BPL
 Version: 00

 Part Number:
 17002004A
 Mar 24, 2023



Mechanical Drawing:



Motor:

Nominal Voltage = 24 vdcOperating Voltage Range = 21.6-26.4 vdcNominal Running Current = 0.06 amps Max. Locked Rotor Current = 0.15 amps **Running Power** = 1.44watts Average Speed = 6000 RPMBearings = BallAir Flow = 8.0 CFMAcoustic =40 dBAWeight =50g

Construction:

Venturi: Plastic, Black, UL 94V-0 Propeller: Plastic, Black, UL 94V-0

Life Expectancy:

This fan is designed for continuous duty life of 45,000 hours at 70°C.

Additional Features:

Brushless DC Motor Automatic Restart Capability

Electronic Locked Rotor Protection

Polarity Protected

Operating Temperature: -10°C to 70°C Storage Temperature: -40°C to 85°C

Termination:

250±10mm, 24AWG UL1007 Leadwires

Red = Power(+)
Black = Return(-)

Agencies:

UL, CE

PQ Curve:

