SPECIFICATIONS


(RoHS Compliant)

 Model Number:
 CR1225-MD48BPL
 Version: 00

 Part Number:
 17002072A
 Aug 30, 2023



Mechanical Drawing:



Motor:

Nominal Voltage =48 vdcOperating Voltage Range =43.2-52.8 vdcNominal Running Current = 0.22 amps Max. Locked Rotor Current = 0.60 ampsRunning Power = 10.56 watts Average Speed = 4000 RPMBearings = Ball Air Flow = 127.4 CFMAcoustic $= 58 \, \mathrm{dBA}$ Weight = 140g

Construction:

Venturi: Plastic, Black, UL 94V-0 Propeller: Plastic, Black, UL 94V-0

Life Expectancy:

This fan is designed for continuous duty life of 50,000 hours at 40 °C.

Additional Features:

Brushless DC Motor Automatic Restart Capability Electronic Locked Rotor Protection

Polarity Protected
Operating Temperature: -10°C to 70°C
Storage Temperature: -40°C to 85°C

Agencies:

UL,CE

Termination:

250±10mm, 24AWG UL1007 Leadwires

Red = Power(+) Black = Return(-)

PQ Curve:

