




# DIMENSIONS



# PCB LAYOUT



# TERMINATION



# ORDERING INFORMATION

SERIES	8609	2	32	5	3	13	7	4	5	ELF
ROWS FITTED WITH CONTACTS										
ROW a b	2		32							
ROW a -	1		16							
NO. OF CONTACTS										
TYPE OF INSULATOR										
2 ROW MALE INSULATOR	5									
METHOD OF MOUNTING										
STANDARD MOUNTING - STYLE B/2	3									
TERMINATION										
ANGLED SPILL	13									
OPTIONS										
NO OPTION	7									
WITH HARPOONS	H									
PERFORMANCE CLASS										
DIN 41612 CLASS 3	4									
DIN 41612 CLASS 2	5									
DIN 41612 CLASS 1	6									
AS PER MIL C 55302 / JSS 50808	8									
PITCH PER ROW										
2.54 mm	5									
LEAD FREE VERSION	ELF									

GENERAL CHARACTERISTICS & RoHS INFO

REFER DRAWING C-8609-0000A

mat'l. code		surface		tolerance		projection		product family	
SEE DWG C-8609-0000A		ISO 1302 ✓		ISO 406 ISO 1101		mm		8609	
ltr		ecn no		date		tolerances unless otherwise specified		title	
A		104-0063		MINI 2004-09-17		0.X ±0.1		DIN STANDARD HEADER	
B		105-0089		MINI 2005-05-19		0.XX ±0.1		ANGLED SPILL DIN 41612 STYLE B/2	
C		106-0061		MINI 2006-05-31		0.XXX ±0.1		scale 3:2	
D		107-0155		KR 2007-11-14		dr MINI K V 2004-09-17		dwg no sheet 1 of 1 size	
E		108-0146		KR 2008-10-21		enr RAKHEE G 2004-09-17		C-8609-2009 A3	
F		ELX-I-40953		MJA 2021-05-19		chr M JACOB 2021-05-19		type Product Customer Drawing	
sheet index		revision		F		appd SAN0J 2021-05-19			
sheet		1							