





Item (Detail view)

2-conductor through terminal block



Item no.	292-601	GTN / EAN	4044918306830
Content	1 piece	Order unit	piece
Order quantity	50 piece	Increase in order quantity	(50, 100, 150, 200, ...)
Customer item no.		Customs Tariff no.	85369010000
Customs duty for the country of origin	DE	Available	-
List price	On request	Net price	On request
Availability	On request		

Note: Some items may not be available from your local WAGO company. Please note that the quantities ordered in the shopping cart are rounded up to the PU (SPU).

RoHS Compliant

Article details Approvals Downloads/Certificates Accessories

Description	2-conductor through terminal block																																																																																												
Remarks																																																																																													
Item properties	<table border="1"> <thead> <tr> <th colspan="3">Miscellaneous</th> </tr> <tr> <th>Name</th> <th>Value</th> <th>Unit</th> </tr> </thead> <tbody> <tr> <td>Packaging type</td> <td>BOX</td> <td></td> </tr> <tr> <td>Ratings per</td> <td>IEC/EN 60947-7-1</td> <td></td> </tr> <tr> <td>Rated voltage (III / 3) [V]</td> <td>800</td> <td>V</td> </tr> <tr> <td>Rated impulse voltage (III / 3) [kV]</td> <td>8</td> <td>kV</td> </tr> <tr> <td>Rated current [A]</td> <td>41</td> <td>A</td> </tr> <tr> <td>Legend (ratings)</td> <td>(III / 3) ± Overvoltage category III / Pollution degree 3</td> <td></td> </tr> <tr> <td>Type of wiring</td> <td>Front-entry wiring</td> <td></td> </tr> <tr> <td>Total number of connection points</td> <td>2</td> <td></td> </tr> <tr> <td>Total number of potentials</td> <td>1</td> <td></td> </tr> <tr> <td>Number of levels</td> <td>1</td> <td></td> </tr> <tr> <td>Connection technology</td> <td>CAGE CLAMP®</td> <td></td> </tr> <tr> <td>Actuation type</td> <td>Operating tool</td> <td></td> </tr> <tr> <td>Connectable conductor materials</td> <td>Copper</td> <td></td> </tr> <tr> <td>Solid conductor</td> <td>0.2 ... 6 mm² / 24 ... 10 AWG</td> <td></td> </tr> <tr> <td>Fine-stranded conductor</td> <td>0.2 ... 6 mm² / 24 ... 10 AWG</td> <td></td> </tr> <tr> <td>Strip length</td> <td>12 ... 13 mm / 0.47 ... 0.51 inch</td> <td></td> </tr> <tr> <td>Width</td> <td>8 mm / 0.315 inch</td> <td></td> </tr> <tr> <td>Height from upper edge of DIN-35 rail</td> <td>31.5 mm / 1.24 inch</td> <td></td> </tr> <tr> <td>Depth</td> <td>62 mm / 2.441 inch</td> <td></td> </tr> <tr> <td>Design</td> <td>horizontal</td> <td></td> </tr> <tr> <td>Type of mounting</td> <td>Carrier rail 35 x 15</td> <td></td> </tr> <tr> <td>Marking level</td> <td>Side marking</td> <td></td> </tr> <tr> <td>Color</td> <td>gray</td> <td></td> </tr> <tr> <td>Insulating material</td> <td>Polyamide 66 (PA 66)</td> <td></td> </tr> <tr> <td>Fine lead [m]</td> <td>0.207</td> <td>m</td> </tr> <tr> <td>Weight [g]</td> <td>13.26</td> <td>g</td> </tr> <tr> <td>Main product function</td> <td>Through term. block</td> <td></td> </tr> <tr> <td>Product type</td> <td>Through rail-mount term. blocks</td> <td></td> </tr> </tbody> </table>			Miscellaneous			Name	Value	Unit	Packaging type	BOX		Ratings per	IEC/EN 60947-7-1		Rated voltage (III / 3) [V]	800	V	Rated impulse voltage (III / 3) [kV]	8	kV	Rated current [A]	41	A	Legend (ratings)	(III / 3) ± Overvoltage category III / Pollution degree 3		Type of wiring	Front-entry wiring		Total number of connection points	2		Total number of potentials	1		Number of levels	1		Connection technology	CAGE CLAMP®		Actuation type	Operating tool		Connectable conductor materials	Copper		Solid conductor	0.2 ... 6 mm ² / 24 ... 10 AWG		Fine-stranded conductor	0.2 ... 6 mm ² / 24 ... 10 AWG		Strip length	12 ... 13 mm / 0.47 ... 0.51 inch		Width	8 mm / 0.315 inch		Height from upper edge of DIN-35 rail	31.5 mm / 1.24 inch		Depth	62 mm / 2.441 inch		Design	horizontal		Type of mounting	Carrier rail 35 x 15		Marking level	Side marking		Color	gray		Insulating material	Polyamide 66 (PA 66)		Fine lead [m]	0.207	m	Weight [g]	13.26	g	Main product function	Through term. block		Product type	Through rail-mount term. blocks	
Miscellaneous																																																																																													
Name	Value	Unit																																																																																											
Packaging type	BOX																																																																																												
Ratings per	IEC/EN 60947-7-1																																																																																												
Rated voltage (III / 3) [V]	800	V																																																																																											
Rated impulse voltage (III / 3) [kV]	8	kV																																																																																											
Rated current [A]	41	A																																																																																											
Legend (ratings)	(III / 3) ± Overvoltage category III / Pollution degree 3																																																																																												
Type of wiring	Front-entry wiring																																																																																												
Total number of connection points	2																																																																																												
Total number of potentials	1																																																																																												
Number of levels	1																																																																																												
Connection technology	CAGE CLAMP®																																																																																												
Actuation type	Operating tool																																																																																												
Connectable conductor materials	Copper																																																																																												
Solid conductor	0.2 ... 6 mm ² / 24 ... 10 AWG																																																																																												
Fine-stranded conductor	0.2 ... 6 mm ² / 24 ... 10 AWG																																																																																												
Strip length	12 ... 13 mm / 0.47 ... 0.51 inch																																																																																												
Width	8 mm / 0.315 inch																																																																																												
Height from upper edge of DIN-35 rail	31.5 mm / 1.24 inch																																																																																												
Depth	62 mm / 2.441 inch																																																																																												
Design	horizontal																																																																																												
Type of mounting	Carrier rail 35 x 15																																																																																												
Marking level	Side marking																																																																																												
Color	gray																																																																																												
Insulating material	Polyamide 66 (PA 66)																																																																																												
Fine lead [m]	0.207	m																																																																																											
Weight [g]	13.26	g																																																																																											
Main product function	Through term. block																																																																																												
Product type	Through rail-mount term. blocks																																																																																												

Upwards