

CHERRY G80-1800

Small dimensions and top performance!



Models may vary from the image shown

Standard? Yes! Boring? No - the compact design of the 19 inch PC keyboard is highly distinctive. For space-saving applications and optimum longevity requirements.

FUNCTION AND PERFORMANCE

- Individual keys with Gold Crosspoint contacts (MX technology)
- Codeset 3 support (PS/2 connection only) e.g. for Unix computers
- Perfect key feeling
- High-quality keyboard for outstanding writing performance, fulfilling even the highest demands
- Extremely high service life of individual keys

TECHNICAL DATA

| | |
|---------------------------------------|------------------------------|
| Weight main product: | 32 oz |
| Dimensions product without packaging: | 15,94 in x 7,09 in x 1,73 in |

| | |
|--|--|
| Weight of product incl. packaging: | 41.98 oz |
| Dimensions product incl. packaging: | 18,11 in x 10,63 in x 1,97 in |
| Content of master carton (pieces): | 18 |
| Cable-length: | 5.74 ft |
| Storage temperature: | -4 °F - 140 °F |
| Working temperature: | 32 °F - 122 °F |
| Product approvals: | <ul style="list-style-type: none">• CE• cURus• FCC• VDE• UKCA• China RoHS |
| System Requirements- Hardware: | <ul style="list-style-type: none">• USB-A• PS/2 |
| Operating system: | <ul style="list-style-type: none">• Windows 7• Windows 8• Windows 10• Windows 11 |
| Scope of delivery: | <ul style="list-style-type: none">• Manual• Keyboard |
| Reliability: | MTBF 90: > 10 Mio. |
| Service life per key (in million strokes): | 50 mio. actuations |
| Switching characteristics: | linear |
| Max. current consumption (mA) of keyboard: | 16 mA |
| Keyboard format: | Compact (96%) |
| Integrated metal plate: | yes |
| N-key rollover: | not specified |
| Anti-ghosting: | not specified |
| Key encryption: | no |
| Internal memory: | no |
| Actuating force (cN): | 60 cN |

| | |
|-------------------------------|-------------------------|
| Forward travel: | 2 mm |
| Key stroke total travel path: | 4 mm |
| Key labeling: | Laser etching |
| Palm rest: | Palm rest not available |
| USB hub: | no |
| Illumination: | no |
| Adjustable feet: | integrated |
| Status LEDs: | in housing |
| Key technology: | Mechanical |

| | |
|------------------|--|
| Switches: | CHERRY MX BLACK |
| Keycap material: | ABS |
| Model number: | MX 1800 |
| Warranty: | 1 additional year voluntary limited manufacturers warranty |

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

| EAN & Part number | Switches | Color | Illumination | Layout |
|----------------------------------|-----------------|------------|--------------|---------------------|
| 4025112065040 G80-1800LPCDE-2 | CHERRY MX BLACK | black | no | DE (Germany) |
| 4025112064975 G80-1800LPCEU-2 | CHERRY MX BLACK | black | no | EU (USA+ €-Symbol) |
| 4025112072031 G80-1800LPCGB-2 | CHERRY MX BLACK | black | no | GB (United Kingdom) |
| 4025112064968 G80-1800LPCDE-0 | CHERRY MX BLACK | light-grey | no | DE (Germany) |
| 4025112072000 G80-1800LPCES-0 | CHERRY MX BLACK | light-grey | no | ES (Spain) |
| 4025112064937 G80-1800LPCEU-0 | CHERRY MX BLACK | light-grey | no | EU (USA+ €-Symbol) |
| 4025112064951 G80-1800LPCFR-0 | CHERRY MX BLACK | light-grey | no | FR (France) |
| 4025112064944 G80-1800LPCGB-0 | CHERRY MX BLACK | light-grey | no | GB (United Kingdom) |
| 4025112073335 G80-1800LPCIT-0 | CHERRY MX BLACK | light-grey | no | IT (Italy) |

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.