STREAM KEYBOARD WIRELESS

The best STREAM ever as a wireless keyboard.







Models may vary from the image shown

The CHERRY STREAM KEYBOARD WIRELESS is the wireless version of the familiar STREAM KEYBOARD. The 2.4 GHz wireless key-board has all the features that have made its wired counterpart so popular. The new STREAM KEYBOARD WIRELESS is the perfect choice for all those who have been waiting for the wireless ver-sion of the CHERRY classic. The wireless keyboard is plain but elegant, and will appeal to a wide range of tastes. The slim design also reflects current trends. With the feet up or down, it is clear that the wireless keyboard is extremely stable, rigid, and non-slip. This is ensured by the inte-grated metal plate, the two feet and the eight rubber pads on the underside.

At the heart of every keyboard is the key technology. Like all products in the STREAM family, the STREAM KEYBOARD WIRELESS uses CHERRY's own SX scissor technology. This ensures uniquely comfortable, precise and quiet typing. All these attributes lay the foundation for productive work and make the flat keyboard the ideal companion in the office or at home.

The 2.4 GHz wireless connection is also reliable and uncompli-cated. The keyboard comes with a plug & play receiver to con-nected to the PC. Thanks to wireless technology with a range of 10 meters and AES-128 encryption, the desktop is no longer a tangle of cables but tidy space for you to work in

comfort.

The computer keyboard has a full-size layout and a number pad, which means it immediately feels familiar. There are also useful status LEDs integrated in the CAPS LOCK, NUM and SCROLL LOCK keys.

This feature is usually only found in higher price ranges. The red status LED shows you at a glance whether the Caps Lock key is ac-tivated, for example. In addition, the LEDs flash when you need to change batteries. However, with a battery life of up to 36 months, this rarely happens.

In any work environment, users require certain functions particu-larly often. The CHERRY STREAM KEYBOARD has handy extra keys for the most important functions. These include six keys for controlling your multimedia player. Three other keys for the browser, e-mail and calculator can be easily accessed. The lock key is especially invaluable in the office environment. The user can simply press it to log out when leaving the workstation.

Additional flexibility is offered by the CHERRY KEYS software. It can be downloaded free of charge from www.cherry.de. With just a few clicks, you can configure the office keyboard any way you want. Environmental protection and sustainability are matters that comprise many aspects. With the CHERRY STREAM KEYBOARD, for example, we have managed to make the packaging completely plasticfree. It has also been honored with the oldest of all envi-ronmental protection labels, the Blue Angel. In addition, the key-board bears the GS "safety tested" seal. The only legally regulated test mark in Europe certifies compliance with defined ergonomic and safety standards. All these criteria provide guidance for sus-tainability when buying products, as well as for the health and safety of your employees. The STREAM KEYBOARD WIRELESS is the perfect wireless standalone keyboard for frequent users with high demands. Based on CHERRY SX scissor technology, the wireless keyboard is quiet, durable and requires no maintenance. It is ideal for anyone who appreciates the advantages of the STREAM KEYBOARD but also wants the benefits of wireless

transmission.



FUNCTION AND PERFORMANCE

- → Maximum productivity:
- → Super silent keystroke
- → Proprietary SX scissor technology
- → Unbeatable typing feel
- → Highest quality:
- → Rubberized feet for perfect slip resistance
- \rightarrow Durable key labels
- → Keyboard with AES-128 encryption
- → Integrated metal plate for maximum torsional rigidity
- → Blue Angel eco label
- → Optimum operating comfort:
- → Battery life up to 36 months
- → Status LEDs indicate and low battery level
- → Integrated status LEDs for the CAPS LOCK, NUM and SCROLL keys
- → Keyboard with 10 office & multimedia keys
- → Very latest design:
- → Low profile
- → GS certificate (full size layout)

TECHNICAL DATA

Weight main product:	33 oz
Dimensions product without packaging:	18,2 in x 6,39 in x 0,91 in
Storage temperature:	-4 °F - 140 °F
Working temperature:	32 °F - 104 °F
Product approvals:	 CE China RoHS GS Blauer Engel cURus Windows Hardware Compatibility

System

USB-A

UKCA

Requirements-Hardware:

Operating system:	Windows 7
	Windows 8
	 Windows 10
	 Windows 11
Scope of delivery:	• 2 x AA battery
	 Keyboard

 Nano-USB-Receiver Manual

MTBF > 80.000 Stunden Reliability: Software support: **CHERRY KEYS**

USB dongle: yes Encryption in wireless ves

mode:

Wireless range (m): 33 ft Number of batteries:

Alkaline Battery type:

Battery design: ДД Battery rechargeable: no Battery replaceable: yes no

Battery charging socket:

Service life per key (in million strokes):

20 mio. actuations

standard

20 mA

Switching

characteristics:

Max. current consumption (mA) of

keyboard:

Full-size (100%) Keyboard format:

Integrated metal plate: yes Volume (dB) of 49 db

keyboard:

N-key rollover: not specified Anti-ghosting: not specified

Key encryption: no Internal memory: no Actuating force (cN): 65 cN

Actuating force tol.: 10 cN

Palm rest: Palm rest not available

USB hub:



Special key functions: • Unmute/Mute

Volume up

Volume down

Last track

• Play/Pause

Next track

PC lock

Browser

• e-mail program

Calculator

Illumination: no

Adjustable feet: integrated

Status LEDs: in keys
Key technology: Scissor
Keycap material: ABS
Model number: JD-85K
Warranty: 1 additional year voluntary limited manufacturers warranty

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

Actual battery life is strongly depending on individual user behavior and hardware setup.



EAN & Part number	Color	Illumination	Layout
4025112097041 JK-8550BE-2	black	no	BE (Belgium)
4025112096945 JK-8550CH-2	black	no	CH (Switzerland)
4025112097027 JK-8550CN-2	black	no	CN (China)
4025112096952 JK-8550CS-2	black	no	CS (Czech Republic / Slovak Republic)
4025112096969 JK-8550DE-2	black	no	DE (Germany)
4025112096976 JK-8550ES-2	black	no	ES (Spain)
4025112096983 JK-8550EU-2	black	no	EU (USA+ €-Symbol)
4025112096990 JK-8550FR-2	black	no	FR (France)
4025112097003 JK-8550GB-2	black	no	GB (United Kingdom)
4025112097010 JK-8550PN-2	black	no	PN (PanNordic)
4025112097034 JK-8550TW-2	black	no	TW (Taiwan)
4025112097058 JK-8550US-2	black	no	US (USA)

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.