

Powerful soldering intelligence on a single platform.

Weller® WX — Intelligent hand-soldering solutions for electronic assembly.



Weller®

WX

A system that saves you money.

The Weller WX system keeps your cost of ownership low with Intelligent power management to conserve energy and an exceptional degree of tool compatibility.



200 I 240W Total Power

Supports operation of one 200W tool or simultaneous operation of two 120W tools (WX2 Only)



Viewable From All Angles

Blue LED Backlighting to strengthen visibility



Global Language Support

Display multiple languages through menu selection



Intuitive Interface

Six touch keys with radius finger guide for turn-and-click navigation



Automatic Energy Saving Mode

Selectable stand-by mode with visual process control via blue LED light ring on most models (light on = heater on, light off = heater off)





Robust Touch Screen

Patented, capacitive touch screen made of antistatic, chemical and temperature resistant glass



Intelligent Tool Recognition

Quick change connectors enable rapid tool interchange



Multi-Purpose USB Port

Quick and localized software updates, parameter configuration and data logging via USB stick



Intelligent Accessory Management

Dual port configuration to manage fume extractors, heating plates and programmable logic controllers



Increased Accuracy

Digital sensor in pencil optimized at short range for peak performance



Programmable Read and Write Memory

Supports quick tool exchange and reduces adjustments needed to the soldering station

STEP 1

Choose Active-Tip or Power-Response Tip Technology for applications.



Active (Integral) Tip Technology

This highly-innovative technology offers ultra precise heating and temperature control specifically designed for micro-soldering applications. The fully-integrated tip cartridge delivers the fastest recovery on the market for fine tips at just a slightly higher tip price. Temperature sensitive and miniature applications are mastered with precision and safety.


55W Iron

- Ultra precise performance
- Extremely accurate tip temperature
- Micro-soldering at its finest
- Fastest heat up and recovery time of all three technologies

RT

Most delicate and temperature-sensitive applications; for use under microscope; ultra fine tips with fastest heat response and best temp-control; cartridge tips.

Chisel



RT Non-MS-spec series		Ø a mm	b mm	Order number
Use with WXMP (T0052920399)				
RT 1SC		0.4	0.15	T0054461299
RT 1SCNW*		0.3	0.1	T0054462699
RT 3		1.3	0.4	T0054460399
RT 4		1.5	0.4	T0054460499
RT 8		2.2	0.4	T0054460899
RT 9		0.8	0.4	T0054460999
RT 11		3.6	0.9	T0054461199
RT 5 30°		0.8	0.4	T0054460599

RT-MS MS-spec series		Ø a mm	b mm	Order number
Use with WXMP-MS (T0052921399)				
RT 1SCMS		0.4	0.15	T0054461599
RT 1SCNWMS*		0.3	0.1	T0054462671
RT 3MS		1.3	0.4	T0054461699
RT 4MS		1.5	0.4	T0054461899
RT 8MS		2.2	0.4	T0054462299
RT 9MS		0.8	0.4	T0054462399
RT 11MS		3.6	0.9	T0054463199
RT 5MS 30°		0.8	0.4	T0054461999
RT 3XMS 30°		1.3	0.5	T0054460373

Sloped



Type	a mm	Order number
RT 6 45°	1.2	T0054460699

Type	a mm	Order number
RT 6MS 45°	1.2	T0054462099


*Non-wettable








MS tips: separate ground



Conical



RT Non-MS-tips series		Ø a mm	Order number
Use with WXMP (T0052920399)			
	RT 1	0.2	T0054460199
	RT 1NW*	0.1	T0054462599
	RT 2	0.8	T0054460299
	RT 14	0.4	T0054460171
	RT 15	.75	T0054460271

RT-MS MS-tips series		Ø a mm	Order number
Use with WXMP-MS (T0052921399)			
	RT 1MS	0.2	T0054461499
	RT 1NWMS*	0.1	T0054462571
	RT 2MS	0.8	T0054461799
	RT 12MS 25°	0.5	T0054463299
	RT 13MS 30°	0.4	T0054463399
	RT 14MS	0.4	T0054460173
	RT 15MS	.75	T0054460273

Gull wing



Type	Ø a mm	b mm	Order number
	1.2	2.0	T0054461099

Type	Ø a mm	b mm	Order number
	1.2	2.0	T0054462499

Knife



Type	Ø a mm	Order number
	2.2	T0054460799

Type	Ø a mm	Order number
	2.2	T0054462199

MS tips: separate ground

Measuring tip

Type	Order number
Measuring tip	K1101

*Non-wettable



2X40W Tweezer

RTW = tweezers

Most delicate and temperature-sensitive applications; for use under microscope; ultra fine tips with fastest heat response and best temp-control; cartridge tips.

RTW

Chisel



RTW <i>Non-MS-spec series</i>	\emptyset a mm	b mm	Order number
Use with WXMP (T0052920399)			
RTW 2 45°	0.7	0.4	T0054465299
RTW 3 45°	3.0	1.0	T0054465399
RTW 4 45°	6.0	1.0	T0054465499
RTW 9	3.0	1.0	T0054466699
RTW 11	6.0	1.0	T0054466799
RTW10	10.0	1.0	T0054466899
RTW 8	1.3	0.4	T0054466499

RTW-MS <i>MS-spec series</i>	\emptyset a mm	b mm	Order number
Use with WXMP-MS (T0052921399)			
RTW 2MS45°	0.7	0.4	T0054465799
RTW 3MS 45°	3.0	1.0	T0054465899
RTW 4MS 45°	6.0	1.0	T0054465999
RTW 9MS	3.0	1.0	T0054466999
RTW 11MS	6.0	1.0	T0054467099
RTW10MS	10.0	1.0	T0054467199
RTW 8MS	1.3	0.4	T0054466599
RTW 7NWMS*	0.8	0.4	T0054466371

Conical



Type	\emptyset a mm	Order number
RTW 1 45°	0.4	T0054465199
RTW 6NW* 45°	0.2	T0054465699

Type	\emptyset a mm	Order number
RTW 1MS 45°	0.4	T0054465599
RTW 6NWMS* 45°	0.2	T0054465671

Measuring tip

Type	Order number
RTW	T0054466299

*Non-wettable

MS tips: separate ground



65W Iron

Power-Response Technology

The newly improved technology maximizes soldering performance on the most-delicate to the most-difficult applications. A perfect balance between power, response, temperature control and lower tip costs makes this unique technology the most attractive solution for top quality professional soldering designed to meet the highest industry standards.

Maximum power and response for top performance

Optimal balance between power, control and operating costs with widest range of tips


Highest quality soldering standard for wide range of applications



XNT

SMDs and THDs with very small solder pads and increased heat demand, lower cost, non-cartridge style tips.

Chisel



XNT	Ø a mm	b mm	c mm	Order number
XNT 15CMW*	0.3	0.1	27.0	T0054488199
				NEW
XNT 15C	0.4	0.15	27.0	T0054486299
XNT H	0.8	0.4	28.0	T0054485999
XNT K	1.2	0.4	28.0	T0054486099
XNT A	1.6	0.4	28.0	T0054485199
XNT 6	1.6	0.4	29.5	T0054485699
XNT 8	2.4	0.8	27.0	T0054485799

Type	Ø a mm	b mm	c mm	Order number
XNT C	3.2	0.8	27.0	T0054485899
XNT D	4.0	0.8	28.0	T0054485399
XNT HX 45°	0.8	0.4	36.5	T0054487399
XNT 4X 45°	1.2	0.4	34.6	T0054487499
XNT AX 45°	1.6	0.8	28.0	T0054486499
XNT BX 45°	2.4	0.8	36.5	T0054488299
				NEW
XNT MX 45°	3.2	0.8	37.5	T0054488399
				NEW

Sloped



Type	a mm	Order number
XNT 4 45°	1.2	T0054485599
XNT AA 45°	1.6	T0054488499
		NEW
XNT BB 45°	2.4	T0054488599
		NEW

Type	a mm	Order number
XNT CC 45°	3.2	T0054488699
		NEW
XNT F 45°	1.2	T0054488799
		NEW

*Non-wettable

Conical



XNT		Ø a mm	c mm	Order number
XNT 1		0.5	27.0	T0054485099
XNT 1L		0.2	42.8	T0054487199

Type	Ø a mm	c mm	Order number
XNT S	0.4	37.5	T0054486899


Knife



Type	Ø a mm	c mm	Order number
XNT KN	2.0	33.0	T0054486399

Type	a mm	b mm	c mm	Order number
XNT GW 1 45°	1.0	1.5	27.5	T0054488099


Gull wing



Type	a mm	b mm	c mm	Order number
XNT GW 45°	1.4	2.0	33.0	T0054485499

Type	Ø a mm	c mm	Order number
XNT M	3.2	37.5	T0054486799
XNT 1LX 45°	0.2	36.5	T0054487299
XNT 1X 45°	0.4	28.0	T0054486599
XNT 1SLX 45°	0.4	39.5	T0054487599

Round



Type	Ø a mm	c mm	Order number
XNT 1S	0.2	28.5	T0054485299
XNT AS	1.6	29.5	T0054486999
XNT L	2.0	37.5	T0054486699
XNT C5	3.2	29.5	T0054487099

SMT

Type	Ø a mm	b mm	c mm	Order number
XNT SMT 01	10.4	0.6	7.1	T0054487699
XNT SMT 02	16.8	0.6	7.1	T0054487799

Type	Ø a mm	b mm	c mm	Order number
XNT SMT 03	20.8	0.6	7.1	T0054487899

Accessories

Type	Ø a mm	c mm	Order number
Measuring tip			E1131
XNT Screw M4		26.0	T0054487999

Type	Order number
Barrel	T0058765758
Barrel for bent tips	T0058765767

*Non-wettable




120W Iron



XT

Most difficult, high-mass soldering jobs; maximum power with ergonomic iron handle, lower cost, non-cartridge style tips.

Chisel



XT	Ø a mm	b mm	c mm	Order number
XT H	0.8	0.4	36.5	T0054471399
XT A	1.6	0.7	36.5	T0054470399
XT AL	1.6	1.0	39.5	T0054470199
XT ASL	1.6	0.45	36.5	T0054474099
XT M	3.2	1.2	39.5	T0054470299
XT B	2.4	0.8	36.0	T0054470499
XT BSL	2.4	0.45	36.0	T0054474199
XT B SL	2.5	0.8	36.3	T0054473899
XT C	3.2	0.8	36.0	T0054470599

Type	Ø a mm	b mm	c mm	Order number
XT D	4.6	0.8	34.5	T0054470699
XT CSL	3.2	0.45	36.0	T0054474299
XT E	5.9	1.2	34.5	T0054470799
XT DL	4.6	0.8	39.5	T0054473699
XT MX	3.2	0.8	53.5	T0054474599
XT HX	0.8	0.4	51.5	T0054473799
XT AX 30°	1.6	0.7	51.5	T0054474399
XT BX 30°	2.4	0.8	51.5	T0054474499


Round



Type	Ø a mm	c mm	Order number
XT BS	2.4	36.5	T0054471599
XT CS	3.2	36.5	T0054471699

Type	Ø a mm	c mm	Order number
XT DS	5.0	34.5	T0054471799

Sloped



Type	a mm	c mm	Order number
XT F 30°	1.2	36.5	T0054471899
XT AA 60°	1.6	36.5	T0054470899
XT BB 45°	2.4	36.5	T0054470999
XT CC 45°	3.2	36.5	T0054471099

Type	a mm	c mm	Order number
XT DOH 45 45°	4.0	40.5	T0054473099
XT D 45°	5.0	40.5	T0054472199

*Non-wettable

Gull wing



XT		Ø a mm	b mm	c mm	Order number
	XT GW1 45°	2.3	3.2	36.5	T0054471299
	XT GW2 45°	3.5	4.8	36.5	T0054473599

Type	Ø a mm	b mm	c mm	Order number
	0.8	0.9	41.5	T0054473999

Knife

Type	Ø a mm	c mm	Order number
	2.0	45.0	T0054471199

Conical



Type	Ø a mm	c mm	Order number
	1.0	36.5	T0054471499

SMT

Type	Ø a mm	b mm	Order number
	4.0	10.0	T0054473190
	4.0	20.0	T0054473290

Type	Ø a mm	b mm	Order number
	4.0	33.0	T0054473390

*Adapter required, must be ordered separately

Accessories

Type	Ø a mm	c mm	Order number
Measuring tip (For the WXP120)			K1141
		36.0	T0054471999
		36.0	T0054472099

Type	Order number
	WXP 120 T0058765711
	WXP 120 T0058765766

*Adapter required, must be ordered separately



200W Iron

XHT

Most difficult, high-mass soldering jobs; maximum power with ergonomic iron handle, lower cost, non-cartridge style tips.

Chisel



XHT		Ø a mm	b mm	c mm	Order number
	XHT C	3.2	1.2	48.0	T0054480499
	XHT D	5.0	1.2	48.0	T0054480199

Type	Ø a mm	b mm	c mm	Order number
	7.6	1.5	48.0	T0054480299
	9.3	2.0	48.0	T0054480599

STEP 2

Align tip with iron technology.



Active (Integral) Tip Technology

RT/RTW

Non-mil-spec series



WXMP Micro-Soldering Iron (T0052920399) with safety rest WDH51 (T0051517199)

- 55W | 12V / max. temperature 450 °C (850 °F)
- Extremely powerful due to an integrated active soldering tip, ideal for working under a microscope
- RT3 chisel tip included

Order number (Set)
T0051320499



WXMT Micro-Tweezers (T0051317799) with safety rest WDH60 (T0051516999)

- 2 x 40W | 12V / max. temperature 450 °C (850 °F)
- Ideal for soldering and desoldering very small SMD parts
- RTW2 cartridge included

Order number (Set)
T0051317899

Active (Integral) Tip Technology

RTMS/RTWMS

Mil-spec series



WXMPMS Micro-Soldering Iron (T0052921399) with safety rest WDH51 (T0051517199)

- 55W | 12V / max. temperature 450 °C (850 °F)
- Extremely powerful due to an integrated active soldering tip, ideal for working under a microscope
- RT3MS chisel tip included

Order number (Set)
T0052921799



WXMTMS Micro-Tweezers (T0051317999) with safety rest WDH60 (T0051516999)

- 2 x 40W | 12V / max. temperature 450 °C (850 °F)
- Ideal for soldering and desoldering very small SMD parts
- RTW2MS cartridge included

Order number (Set)
T0051320399



Power-Response Technology



WXP65 Soldering Iron (T0052921199) with safety rest WDH10 (T0051516199)

- 65W | 24V / max. temperature 450 °C (850 °F)
- Very fast heat-up time suitable for small, extreme precision soldering
- XNTA soldering tip included

Order number (Set)
T0052921299



WXP120 Soldering Iron (T0052920199) with safety rest WDH10 (T0051516199)

- 120W | 24V / max. temperature 450 °C (850 °F)
- For soldering small and large components with high-heat demands
- XTB soldering tip included

Order number (Set)
T0052920299



WXP200 Soldering Iron (T0052920599) with safety rest WDH31 (T0051515899)

- 200W | 24V / max. temperature 450 °C (850 °F)
- Ideal for soldering that requires high heat e.g. for LED back planes
- XHTD chisel tip included

Order number (Set)
T0052920699

STEP 3

Choose station or system.

Stations:



Order number:
WX1



Order number:
WX2



Dimensions LxWxH	170 x 151 x 130 mm (6.69 x 5.94 x 5.12 in)
Power Supply	120 V 50/60 Hz
Power Consumption	200 W (WX1), 240 W (WX2)
Temperature Range	Adjustable temperature range varies among tools (200 – 850 °F)
Temperature Accuracy	± 9 °C (± 17 °F)
Temperature Stability	± 6 °C (± 10 °F)
Control Panel	Glass with antistatic coating
Resolution	255 x 127 (128 dots)
Background Lighting	Four LEDs
USB Port	Front-mounted USB port for firmware updates, parameter setting and monitoring
Communication Ports (2)	Control of Weller fume extraction units and heating plates

Systems:



Order number: WX2020
WX2 station with two WXP120 soldering irons and two WDH10 tool stands



Order number: WX2021
WX2 station with WXMP-MS soldering iron and WDH51 tool stand, WXMT-MS de-soldering tweezer and WDH60 tool stand



Order number: WX1010
WX1 station with WXP120 soldering iron and WDH10 tool stand



Order number: WX1011
WX1 station with WXMP-MS micro soldering iron and WDH51 tool stand



Order number: WX1012
WX1 station with WXP65 soldering iron and WDH10 tool stand

STEP 4

Select peripherals.



Zero Smog 4V
Portable volume extraction up to four workstations

Order number:
T0053660299

Zero Smog 6V
Portable on wheels volume extraction up to eight stations

Order number:
T0053666299

Zero Smog 20T
Portable on wheels tip extraction up to 20 FE soldering irons

Order number:
T0053670299



WX Compatible Heating Plates

WHP1000
850W contact preheater area 220 x 150 mm (8.75 x 6.0 in)

Order number:
WHP1000

WHP3000
600W infra-red contact preheater area 120 x 190 mm (4.7 x 7.5 in)

Order number:
WHP3000

WHP3000 (230V)
1200W infra-red contact preheater area 190 x 240 mm (7.5 x 9.4 in)

Order number:
T0053364699

WX Accessories



WX to PC adapter

Order number:
T0058764711



WX to WFE/ WHP adapter

Order number:
T0058764712



WX to adapter cable connectivity

Order number:
T0058764710



WDC2 Dry tip replacement cleaner for WDH tool stands

Order number:
T0051512599



Replacement brass wool ball for WDC2 (2 per Pack)

Order number:
T0051384099



Tip Polishing bar for soldering tip cleaning

Order number:
WPB1



Replacement Sponge for WMPH/WDH tool stands

Order number:
T0052241999



Tip tinner and activator, 0.5 oz.

Order number:
T0051303199

Why Weller dry cleaning?

- Excellent cleaning results
- Soldering tip is cleaned yet remains wetted
- Aggressive flux residues are removed
- Prevents oxidation of the soldering tip
- Low temperature shock-vs-wet sponge
- Helps extend soldering tip lifetime



Weller®



Weller WDC/WDC2 Dry Cleaner



Dry cleaner with brass wool is recommended for dry cleaning of soldering tips using the WDC dry cleaner with brass wool. The solder tip is cleaned and flux residues are removed while tip remains wetted.

Order number: T0051512499-WDC
T0051512599-WDC2

Weller Hot-Tip Activator



For re-activation or re-wetting of dark, oxidized soldering tip, clean the tip in the activator while the tip is still HOT. Order number: T0051303199

WHP200 Preheating Plate



Supplies additional heat energy to the PCB being soldered. This protects the board from partial overheating and allows the use of much lower, safer solder tip temperatures. Extended tip lifetime is the cost benefit. Order number: WHP200

WPB1 Cold-Tip Polishing Bar



Cleans and renews the soldering tip surface. Clean the tip only when it is COLD to prevent tip damage. Order number: WPB1

Tip Recycle Box



Weller Tip Recycling Box for two pounds of used tips. Order number: T550729



Find out how to use the WDC dry cleaner correctly on our youtube channel: visit www.youtube.com/wellersoldering

YouTube

Resources for the future.

CARE ABOUT THE ENVIRONMENT?

Weller does and we want you to work with us to make it better.

Weller is a committed supporter of actions that help to protect our environment and to conserve its natural resources.

To this end, Weller is launching a recycling initiative for old, used soldering tips. By recycling the copper and iron from used tips, we can make a real contribution towards helping the environment and preserving its natural resources.

HOW IT WORKS:

In the United States? We want you to collect your worn out soldering tips, all types from all manufacturers, send them to us and we will arrange for their environmentally safe recycling.

This will benefit the environment but it will also benefit you because for every 2 lbs. of worn out tips you send to us you will receive a \$75.00 voucher to be used against your next purchase of Weller Brand tips.

Get involved with Weller and the environment will profit and so will you.

Please send the full TIP RECYCLING BOX to the address on the box or to:

Weller Tools
1000 Lufkin Road
Apex, NC 27539 USA



Need a new box? Contact us.



Weller®

USA

Apex Tool Group, LLC
1000 Lufkin Road
Apex, NC 27539
Tel: +1 (800) 688 8949
Fax: +1 (800) 234 0472

CANADA

Apex Tools - Canada
7361 Bath Road
Mississauga, Ontario L4X 3T1
Tel: +1 (905) 673 4400
Fax: +1 (905) 673 4408

GERMANY

Weller Tools GmbH
Carl-Benz-Strasse 2
74354 Remigheim
Tel: +49 (0)7143 580-0
Fax: +49 (0)7143 580-108

GREAT BRITAIN

Apex Tool Group (UK Operations)
Ltd
4th Floor Pennine House
Washington, Tyne & Wear
NE17 1LJ
Tel: +44 (0) 191 419 7700
Fax: +44 (0) 191 417 9421

FRANCE

Apex Tool Group S.R.L.
25 Avenue Maurice Chevalier B.P. 46
77832 Ozol-la-Fermière Cedex
Tel: +33 (0) 1 64 43 22 00
Fax: +33 (0) 1 64 43 21 82

ITALY

Apex Tool S.r.l.
Viale Summa 80
20090 Cusago (MI)
Tel: +39 (02)9033101
Fax: +39 (02)90394231

SWITZERLAND

Apex Tool Switzerland Sarl
Rue de la Roselière 12
1400 Yverdon-les-Bains
Tel: +41 (0) 24 425 12 06
Fax: +41 (0) 24 425 09 77

CHINA

Apex Tool Group
A-B building
No. 38 Dongshang Road
Heping Industrial Park, Pudong
Shanghai PRC 201201
Tel: +86 (21)60880288
Fax: +86 (21)60880289

AUSTRALIA

Apex Tools
P.O. Box 359
519 Harington Street
Albury, N.S.W. 2640
Australia
Tel: +61 (2)6058 0300
Fax: +61 (2)6021 7403

SOUTH EAST ASIA

Apex Power Tools India Pvt Ltd
Gate No. 1, Plot No. 5
S.No. 234, 235 & 245
Indi-land Global Industrial Park
(Next to Tata Johnson Control)
Taluka-Mulshi, Phase -1
Hinjawadi, Pune (411057)
Maharashtra, India
india@apextoolgroup.com

