

Features

- Universal Input 90~264VAC 50/60Hz
- Output Voltages: 12-48V DC
- IEC/UL/EN 60950-1
- Meets the latest Safety Standards and Approvals
- Single Output to 100W
- High Efficiency
- 100% Full load burn-in Test
- Low Ripple & Noise
- Class II
- Protection: Overload/Over voltage/Short circuit
- Dimensions: 58 x 70 x 90mm
- Weight: 270g



The 100W Series is a cost-effective, energy efficient DIN-rail mount AC-DC converter. The products offers cULus, LVD 60950-1 & EMC EN 55032 compliant products. These AC-DC converters come in at 270g meaning they are light and compact. They are ideal for applications such as Industrial automation, control equipment and electronic systems as well as many other applications.

Models			
Model Number	Output Voltage	Output Current	Output Power
56YSD100S-1207100	12V DC	7.1A	85W
56YSD100S-2403800	24V DC	3.8A	91.2W
56YSD100S-4802000	48V DC	2A	96W

General Specification

DIN Rail Power Supply	
AC	
DC	
1	
Din Rail Mount	
Screw Terminal Type	
>130%-200% rated output power (Protection type: Hiccup mode, recovers automatically after fault condition is removed)	
110% - 180%	
Protection to Zero Voltage	
110~145% (Protection Type: Clamp by zener diode)	



56YSD100S 100W DIN Rail Series

Mechanical Specifications

Housing Material	Fully Enclosed Plastic Case		
Overall Dimensions	58mm x 70mm x 90mm		
Overall Length	90mm		
Overall Depth	58mm		
Overall Width	70mm		
Weight	270g		

Input Specifications

Input Electrical Phase	Single	
Line Frequency	47-63Hz	
Inrush Current	35Amps max. at 115VAC/60Hz,full load & 70Amps max. at 240VAC/50Hz,full load	
AC Current	3A/115VAC 1.6A/230VAC	
Efficiency Type	88~91% Depending on Model	
Leakage Current	<0.25mA/240VAC	

Output Specifications

Output Voltage Adjustment	+/- 10% Depending on Model	
Ripple and Noise	120~240 mV Depending on Model	
Line Regulation	± 1%	
Load Regulation	± 1%	
Isolation Resistance	I/P-O/P:100M Ohms / 500VDC / 25 / 70% RH	
Setup, Rise, Hold Up time	500mS/60mS/12mS(115V/60HZ MAX ROAD), 500mS/60mS/30mS(230V/50HZ MAX ROAD)	
MTBF	200000 h	

Operational Environment

Operating Humidity	20% ~ 90% RH non-condensing	
Operating Temperature Range	-20°C to 50°C,Full load, Normal operation.	
Storage Temperature Range	-40°C to 80°C	
Storage Humidity	10% ~ 95% RH	
Cooling	Cooling	

Protection Category

IP Rating	IP20	



56YSD100S 100W DIN Rail Series

Approvals


Safety StandardUL60950-1, UL508, , BSMI CNS14336-1,TUV EN61558-2-16 IEC60950-1, EAC TPTC 004,TUV EN60950-1


EMC Emissions

EN55032(CISPR32), CNS13438 Class B ,EN61000-3-2 ClassA ,EN61000-3-3,EN61000-4-2,3,4,5,6,8,11, EN55024, EN55035, EN61000-6-2, EN61204-3

Mechanical Drawing


■ Dimensions and Installation:






■ Deduction curve and temperature:

■ Minus output and input voltage curves:



Environment temperature(°C)



Input voltage(VAC)