
SFVL Series

0.5MM PITCH ZIF RIGHT ANGLE FFC-FPC CONNECTOR

FFC-FPC connectors with Zero Insertion Force (ZIF), which allows for easy cable insertion. SFVL series offer a back side flip actuator with top and bottom contact types. These connectors feature a height of 0.9mm and are offered in 4 to 13 contacts. SFVL series connectors are being used in small rugged devices like handhelds; HMI's; camera's and display modules in various devices.

- Low profile for maximum space savings
- Back side flip actuator design makes cable insertion easy
- Cable locking feature provides high retention force



FEATURES

- 0.9mm low-profile and small footprint
- ZIF mechanism with a back side flip actuator
- The large flip actuator on the small housing provides a secure cable lock
- Design against solder and flux wicking
- High-temperature, dimensional stable thermoplastic housing
- 4 to 13 positions available
- High cable retention force
- Lead and halogen-free

BENEFITS

- Save maximum space on small devices and mobile applications
- Provides a high number of mating cycles with stress-free mating and easy assembly
- Prevents un-intentional cable release
- Ensures high solderability
- Covers general operating temperature range of -55°C to +105°C
- Supports many applications as a general-purpose product
- Vibration and Mechanical Shock Testing per USCAR-2 has been passed
- Meet environmental, healthy and safety requirement

TECHNICAL INFORMATION

MATERIAL

Housing: LCP, Black color (UL94V-0)

■ Actuator for Bottom: PPS, Black color (UL94V-0)

Actuator for Top: PPS, White color (UL94V-0)

• Contact: Copper Alloy

■ Tab: Brass

MECHANICAL PERFORMANCE

• Durability: 10 mating cycles

 Vibration and Mechanical Shock Testing per USCAR-2 has been passed

ELECTRICAL PERFORMANCE

Voltage Rating: 50VAC./VDC

Current Rating: 0.4A AC/DC

Contact Resistance: 30mΩ max.(initial value)

• Insulation Resistance: $100M\Omega$ min.

 Dielectric Withstanding Voltage: No short or breakdown after 200VAC, 1min. (2mA max.)

ENVIRONMENTAL

■ Operating Temperature Range: -55°C to +105°C

APPROVALS & CERTIFICATION

• RoHS compliant

• Halogen-free

PACKAGING

■ Tape & Reel

SPECIFICATIONS

• Orientation: Right angle

- Cable Termination: ZIF

- Cable Type: FPC

• Board Termination: Surface mount

Contact Location: Top and bottom options

■ Height: 0.9mm

· Lead free with Gold plating

• Halogen-free

Accommodated Cable Thickness: 0.2mm

TARGET MARKETS/APPLICATIONS



Car Multimedia Car Navigation Dashboard Lighting



Gaming LCD & OLED Displays



Base Station Switches Controllers Storage




Controllers HMI Vending Machines PLC Drives



Ultrasonic Patient Monitor MRI

Infusion Pump Hospital Bed


PART NUMBER SELECTOR







Bottom Contact:



Top Contact:

