



**RG402 Type .141 Semi-Rigid Equivalent Coax Cable with
a Tin Plated Copper Outer Conductor in Coiled Sections**


Stock No.: 9212781B0105

FEATURES

- 50 Ohms
- RG402 Type .141 Semi-Rigid
- Solid

General Specifications

Attribute	Value
Flex Type	Semi-Rigid
Impedance	50 Ohm
Dielectric Type	PTFE
No. of Shields	0
Attenuation at 1 Ghz.	12 dB
Frequency, Max	36 GHz
Max Operating Temperature	125 deg C
Center Conductor Type	Solid
Minimum Bend Radius, One Time	1 in



Dimensions: Millimeters (Inches)

Important Notice: This data sheet and its contents (the "Information") belong to the members of the EASE group of companies (the "Group") or are licensed to it. No license is granted for the use of it other than for information purposes in connection with the products to which it relates. No license of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate, but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. EASE is the registered trademark of Ease Electronics Co., Limited 2019.