



6U Overall, VME64x J1/J2 (without J0) with 5-row, 160 positions DIN 4161 connectors

Features

- VME64J1 Extender on top & VME64J2 Extender on Bottom attached with mending plate to create VME64J1J2 Extender
- Excellent performance with a multi layer design
- Individual signal tracking with interruption jumpers
- Voltage & Current measuring facilities
- Full ground plane
- Signal pin-out identification silkscreen onto outer PCB layers
- Jumper Blocks provided to allow signal line interrogation
- Max. current per contact @ nominal 50°C = 1.75A
- Controlled impedance, Signal trace shielding
- Voltage rating 200 RMS or 300 VDC

Mechanical specifications

- Board Height 6U (9.00")
- Board Length 11.75"
- PCB Thickness 0.062"
- Card Extender bracket (P/N : 5210211, may)

Board specifications

- Material : FR-4 Epoxy
- PCB UL94V-0, PCB R
- 6 Internal 1oz. copper
- PCB exposed Copper

Ordering Info

- Part Number : **VME64J1J2**