IS15SBFP4RGB

Version (2)



DISTINCTIVE CHARACTERISTICS

Advanced LED Illumination with:


- Broad and even light distribution
- Consistent bright backlighting
- Low energy consumption

Programmable LC Display

RGB LED Backlighting

Rubber Dome

Epoxy Sealed Straight PC Terminals



Compact model saves space and accommodates smaller form factor design requirements.

RGB Backlighting provides infinite color availability.

Programmable to display graphics, alphanumeric characters, and animated sequences.

Integrated liquid crystal display provides wide viewing angle with high contrast and clarity.

Viewing area 13.0mm x 10.7mm (horizontal x vertical) at 36 x 24 pixels.

Dome gives crisp tactile feedback to positively indicate circuit transfer.

High reliability and long life of one million actuations minimum.

Epoxy sealed terminals prevent entry of solder flux and other contaminants.

SWITCH SPECIFICATIONS

Circuit	SPST normally open
Electrical Capacity (Resistive Load)	100mA @ 12V DC
Contact Resistance	200 milliohms maximum @ 20mV 10mA
Insulation Resistance	100 megohms minimum @ 100V DC
Dielectric Strength	125V AC for 1 minute minimum
Mechanical Endurance	1,000,000 operations minimum
Electrical Endurance	1,000,000 operations minimum
Operating Force	2.2 ± 0.5 Newtons
Total Travel	1.8mm (.071")
Operating Temperature Range	0°C ~ +40°C (+32°F ~ +104°F)
Storage Temperature Range	-10°C ~ +60°C (+14°F ~ +140°F)

TM

LCD SPECIFICATIONS

Characteristics of Display

Display Operation Mode FSTN positive	
Display Condition	Transflective with built-in LED backlight
Viewing Angle	Adjustable
Driving Method	1/24 duty. 1/5 bias (built-in driving circuit)
Viewing Area	13.0mm x 10.7mm (horizontal x vertical)
Pixel Format	36 x 24 dots (horizonal x vertical)
Pixel Size	0.32mm x 0.32mm (horizontal x vertical)
Backlight LED	Red/Green/Blue



RGB LED with Black & White LCD Mode

Absolute Maximum Ratings (Temperature at 25°C)			Recommended Operating Conditions (Temperature at 25°C)				
ltems	Symbols	Ratings	ltems	Symbols	Minimum	Typical	Maximum
Supply Voltage for Logics	V_{DD}	-0.3V to +7.0V	Supply Voltage for Logics	V_{DD}	4.5V	5.0V	5.5V
Supply Voltage for LCD	V_{LC}	-0.3V to +12.0V	Supply Voltage Black/White	V_{LC}		7.3V	
Input Voltage	V	$-0.3V$ to V_{DD} +0.3V	Input Voltage	V_1	0V		V _{DD}
Output Voltage	Vo	-0.3V to V _{DD} +0.3V	Driving Frequency	\mathbf{f}_{FLM}		150Hz	. —


DC Characteristics of LCD Drive IC (Temperature at 0°C to 40°C and $V_{DD} = 5.0V \pm 10\%$)

ltems	Symbols	Test Conditions	Minimum	Typical	Maximum	Unit
High Level Input Voltage	V _{IH}		$0.7 V_{\text{DD}}$		V _{DD}	V
Low Level Input Voltage	VIL		0		0.3 V _{DD}	V
High Level Input Leakage Current	I _{UH}	$V_1 = V_{DD}$			10	μA
Low Level Input Leakage Current	I	$V_1 = 0V$			-10	μA
High Level Output Voltage	V _{OH}	I _{он} = -500µА	V _{DD} -0.5			V
Low Level Output Voltage	V _{OL}	I _{OL} = 500μA			0.5	V
High Level Output Leakage Current	I _{LOH}	$V_{\rm O} = V_{\rm DD}$			10	μA
Low Level Output Leakage Current	ILOL	$V_{\odot} = 0V$			-10	μA
Supply Current	I _{DD}	$f_{SCP} = 1.0MHz$			500	μA
LCD Drive Current	I _{LC}	$f_{LP} = 2.4 \text{kHz} V_{LC} = 7.3 \text{V} \sim 7.$	5V	500	2,000	μA

Timing Characteristics of LCD Drive IC

(Temperature at 0°C to 40°C and $V_{DD} = 5.0V \pm 10\%$)					
ltems	Symbols	Minimum	Maximum		
Clock Operation Frequency	f_{SCP}		6.0MHz		
Latch Pulse Frequency	f_{LP}		50kHz		
Clock High Level Pulse Width	t _{CWH}	70ns			
Clock Low Level Pulse Width	t _{CWL}	70ns			
Data Setup Time	t _{DSD}	45ns			
Data Hold Time	t _{DHD}	50ns			
Data Output Delay Time	t _{PDO}		25ns		
Latch Setup Time	t _{DSL}	50ns			
Latch Hold Time	t _{DHL}	50ns			
Latch High Level Width	t_{LWH}	200ns			
FLM Setup Time	t _{DSF}	50ns			
FLM Hold Time	t _{DHF}	50ns			
SCP, LP Rise/Fall Time	t _r /t _f		15ns		

Timing Diagram




*3 Location of LP signal on first line

<u>SMARTSWITCH</u>[™]



BLOCK DIAGRAM & PIN CONFIGURATIONS



<u>Pin No.</u>	<u>Symbol</u>	Name	Function
\bigcirc	SW	Terminal of Switch	Normally open
1 2 3	SW	Terminal of Switch	Normally open
3	BL-LED ()	Terminal of Backlight LED	Cathode for red
4	BL-LED ()	Terminal of Backlight LED	Cathode for blue
5	Dout	Data Output	Display serial output. Can be used to connect to Din of the next SMARTSWITCH. As a result, many SMARTSWITCHES can be controlled with one clock and data signal.
6	FLM	First Line Marker	The marking signal for the first line data of LCD display. The first line of LCD will be selected by the falling edge of LP signal during the high level (FLM).
7	LP	Latch Pulse	Line data latch pulse will latch content of internal 40-bit shift register at falling edge for one line of display. LP will also increment the display line by one.
8	SCP	Serial Clock Pulse	Clock used by 40-bit internal shift register of the switch, shifting the display data bit presented at Din at falling edge.
9	Din	Data Input	Display serial data bit. Note: to map the display data, because of the difference between the number of internal shift register data (40) and the single line of LCD pixels (36), the first four bits of data shifted will be dummy bits.
10	GND	Ground	
1	V_{dd}	Power	Power source for logic circuit
12	VLC	Power	Power source for LCD drive
13	BL-LED (+)	Terminal of Backlight LED	Anode for common
14	BL-LED ()	Terminal of Backlight LED	Cathode for green

SMARTSWITCH



SUPER BRIGHT LED SPECIFICATIONS

Typical Electrical Characteristics (Temperature at 25°C)

Backlight Color	Symbols	Red	Green	Blue	Unit
Forward Current	I _F	10	10	10	mA
Forward Voltage	V _F	2.1	3.3	3.3	V


ABSOLUTE MAXIMUM FOR LEDS

Electrical Characteristics (Temperature at 25°C)

Symbols	Red/Green/Blue	Unit
I _F	20	mA
V _R	4.0	V
∆I _F (DC)	-0.27 per chip	mA/°C
P _D	135 maximum	mW
	I_{F} V_{R} $\Delta I_{F}(DC)$	I _F 20 V _R 4.0 ΔI _F (DC) -0.27 per chip

For uniform light emission, Power Dissipation should not exceed the Absolute Maximum Rating.

TYPICAL SWITCH DIMENSIONS



PRECAUTIONS FOR HANDLING & STORAGE

Handling

- 1. The VLC voltage should not be applied before logic voltage. If VLC voltage is present before logic voltage, it may cause the driver logic to freeze and damage the LCD, and the driver logic itself may become damaged.
- 2. The IS Series devices are electrostatic sensitive.
- 3. Limit operating force to keytop to 100.0N maximum, as excessive pressure may damage LCD device.
- 4. Recommended soldering time and temperature limits are 5 seconds maximum @ 270°C maximum.
- 5. Do not exceed 60°C at the LCD level.
- 6. The IS series devices are not process sealed.
- 7. If the LCD is accidentally broken, avoid contact with the liquid and wash off any liquid spills to the skin or clothing.
- 8. Clean cap surface with dry cloth. If further cleaning is needed, wipe with dampened cloth using neutral cleanser and dry with clean cloth. Do not use organic solvent.

Storage

- 1. Store away from direct sunlight.
- 2. Keep away from static electricity.
- 3. Avoid extreme temperatures, high humidity, gaseous substances, and all forms of chemical contamination.

