

_		1		2 3			4 5
	PRODUCT NO.	NO OF POS	DIM L	DIM J	DIM K	DIM D	
	65817-001LF	2 X 8	.700/17.78	1.05/26.7	1.30/33.0	.805/20.45	
Ī	65817-002LF	2 X 10	.900/22.86	1.25/31.8	1.50/38.1	1.005/25.53	NOTES
	65817-003LF	2 X 13	1.200/30.48	1.55/39.4	1.80/45.7	1.305/33.15	NOTES (1.) MOLDING MATERIAL: MODIFIED POLYPHENYLENE ETHER,
	65817-004LF	2 X 16	1.500/38.10	1.85/47.0	2.10/53.3	1.605/40.77	COLOR: BLACK, UL 94V-0.
	65817-005LF	2 X 20	1.900/48.26	2.25/57.2	2.50/63.5	2.005/50.93	2. PIN LENGTH TO BE .210/5.33 MIN. RECOMMENDED PIN LENGTH IS .225±.015/5.72±0.38.
	65817-006LF	2 X 22	2.100/53.34	2.45/62.2	2.70/68.6	2.205/56.01	, ,
	65817-007LF	2 X 2	.100/2.54	.45/11.4	.70/17.8	.205/5.21	3. TO REMOVE TERM PUSH TERM FORWARD, LIFT LATCH WITH HAND TOOL AS SHOWN IN FIGURES 2 & 3 ON TA-531. DAMAGE TO LATCH CAN OCCUR IF LIFTED MORE THAN A 25° ANGLE TO TOP OF HOUSING.
	65817-008LF	2 X 3	.200/5.08	.55/14.0	.80/20.3	.305/7.75	
ľ	65817-009LF	2 X 4	.300/7.62	.65/16.5	.90/22.9	.405/10.29	4. TERMINAL MUST BE CRIMPED PROPERLY FOR SATISFACTORY LATCHING. SEE TA-75 FOR CRIMPING INSTRUCTIONS.
	65817-010LF	2 X 5	.400/10.16	.75/19.1	1.00/25.4	.505/12.83	PRODUCT SECIFICATION: BUS-12-067.
ľ	65817-011LF	2 X 6	.500/12.70	.85/21.6	1.10/27.9	.605/15.37	5. THE HOUSING IS INTENDED FOR USE WITH MINI PV™
ľ	65817-012LF	2 X 7	.600/15.24	.95/24.1	1.20/30.5	.705/17.91	TERMINALS WITH 22-32 GAUGE WIRE.
	65817-013LF	2 X 9	.800/20.32	1.15/29.2	1.40/35.6	.905/22.99	(6.) MOLD CORING HOLES (FOR MANUFACTURING PURPOSES ONLY.)
	65817-014LF	2 X 11	1.000/25.40	1.35/34.3	1.60/40.6	1.105/28.07	(7.) ALL MARKINGS FOR MILITARY PART NUMBERS ARE TO BE PER MIL—STD—1285. SEE TABULATION.
_	65817-015LF	2 X 12	1.100/27.94	1.45/36.8	1.70/43.2	1.205/30.61	(8.) PLACE DESC P/N AND CAGE NO. ON PACKAGING LABEL.
	65817-016LF	2 X 14	1.300/33.02	1.65/41.9	1.90/48.3	1.405/35.69	PRODUCT LENGTH IS TO SMALL TO MARK PART.
	65817-017LF	2 X 15	1.400/35.56	1.75/44.5	2.00/50.8	1.505/38.23	9. PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
	65817-018LF	2 X 17	1.600/40.64	1.95/49.5	2.20/55.9	1.705/43.31	COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
	65817-019LF	2 X 18	1.700/43.18	2.05/52.1	2.30/58.4	1.805/45.85	10. THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO MANUFACTURING SOLDER PROCESS.
	65817-020LF	2 X 19	1.800/45.72	2.15/54.6	2.40/61.0	1.905/48.39	
	65817-021LF	2 X 21	2.000/50.80	2.35/59.7	2.60/66.0	2.105/53.47	
	65817-022LF	2 X 23	2.200/55.88	2.55/64.8	2.80/71.1	2.305/58.55	
4	65817-023LF	2 X 24	2.300/58.42	2.65/67.3	2.90/73.7	2.405/61.09	
	65817-024LF	2 X 25	2.400/60.96	2.75/69.9	3.00/76.2	2.505/63.63	
L	65817-025LF	2 X 26	2.500/63.50	2.85/72.4	3.10/78.7	2.605/66.17	mat'l. code surface / tolerance projection product family
	65817-026LF	2 X 27	2.600/66.04	2.95/74.9	3.20/81.3	2.705/68.71	SEE NOTE 1 PV HOUSINGS It ecn no dr date tolerances unless otherwise specified fittle
	65817-027LF	2 X 28	2.700/68.58	3.05/77.5	3.30/83.8	2.805/71.25	R angles linear XXX+001/X+3 INCH/MM MINI LATCH HOUSING D
	65817-028LF	2 X 29	2.800/71.12	3.15/80.01	3.40/86.36	2.905/73.79	0°±2°
							engr C. TREXLER 1991-02-14
L	form: A3	1		2		3	index sheet 4 5

