





1 2

3

4

PRODUCT NUMBER
SEE SHEET 2



mat'l. code 3/4 HD BRASS CDA NO. 260				surface	tolerance	projection	product family PV TERMINAL		
ltr	ecn no	dr	date	tolerances unless otherwise specified			title		
D	V41703	SAR	1994-11-30	angles	XX ±.01/XX±.3		CTW MALE PIN		
E	V80946	LSS	1998-06-03		XXX ±.005/XX±.13	INCH/MM			
F	V04-0056	VS	2004-02-17	0° ±2°	XXXX ±.0020/XXX±.051	scale 4/1	dwg no sheet 1 of 3 size		
G	V05-0467	HTB	2005-05-23	dr	S ROYER	1994-11-30	75653		
H	V06-0623	HTB	2006-06-28	engr	T.HANNA	1994-11-30	CUSTOMER Drawing		
J	V07-0218	HTB	2007-03-16	chr	T.HANNA	1994-11-30			
K	V08-0440	HTB	2008-10-09	appd	T.HANNA	1994-11-30	type		
sheet	revision	K	K	K					
index	sheet	1	2	3					

form: A4mmXlc




1

2

3

4

PRODUCT NO. AS REELED FOR APPLICATION MACHINES NOTE 5		WIRE AWG	WIRE BARREL			INSULATION BARREL			
RIGHT TO LEFT FEED	LEFT TO RIGHT FEED		A	B	C	D	E	F	
75653-001	75653-004	28-32	.054/1.37	.058/1.47	.011/0.28	.115/2.92	.105/2.67	.040/1.02	OBSOLETE
75653-001LF	75653-004LF	28-32	.054/1.37	.058/1.47	.011/0.28	.115/2.92	.105/2.67	.040/1.02	NOTE 7
75653-002	75653-005	22-26	.070/1.78	.065/1.65	.017/0.43	.139/3.53	.120/3.05	.050/1.27	OBSOLETE
75653-002LF	75653-005LF	22-26	.070/1.78	.065/1.65	.017/0.43	.139/3.53	.120/3.05	.050/1.27	NOTE 7
75653-003	75653-006	18-20	.104/2.64	.104/2.64	.021/0.53	.139/3.53	.120/3.05	.050/1.27	OBSOLETE
75653-003LF	75653-006LF	18-20	.104/2.64	.104/2.64	.021/0.53	.139/3.53	.120/3.05	.050/1.27	NOTE 7


 SECTION A-A
SCALE 2:1

 SECTION B-B
SCALE 2:1

 SECTION C-C
SCALE 5:1


NOTES:

1. PLATING: 100 μ "/2.54 μ SnPb MINIMUM PRE-PLATED (OBSOLETE)
P/N WITH LF SUFFIX: 100 μ "/2.54 μ Sn MINIMUM PRE-PLATED
2. FOR MANUFACTURING PURPOSES ONLY.
3. PART MAY BE USED WITH MINI-LATCH HSG.
4. APPLICABLE SPECIFICATIONS:
A. BUS-12-098: PRODUCT SPECIFICATION
B. TA-211: CRIMP SPECIFICATION
5. PART NUMBERS WITH AN LF SUFFIX MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
6. THIS PRODUCT IS NOT INTENDED TO BE EXPOSED TO MANUFACTURING SOLDER PROCESSES.
7. THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS.
8. PACKAGE QUANTITY: 8000 PER REEL


mat'l. code 3/4 HD BRASS CDA NO. 260				surface ☒ tolerance		projection 		product family PV TERMINAL			
ltr	ecn no	dr	date	tolerances unless otherwise specified				title CTW MALE PIN			
K				angles	learn XX ±.01/X±3 XXX ±.005/XX±13	INCH/MM		dwg no 75653			
				0° ±2°	XXXX ±.0020/XXX±.051	scale 4/1					
				dr	S ROYER	1994-11-30			sheet 2 of 3		size
				engr	T.HANNA	1994-11-30			A		
				chr	T.HANNA	1994-11-30					
				appd	T.HANNA	1994-11-30					
sheet index		revision sheet							type CUSTOMER Drawing		

PRODUCT NUMBER

SEE SHEET 2



Unreeling Direction
Left to Right Into
Applicator



Unreeling Direction
Right to Left Into
Applicator

mat'l. code 3/4 HD BRASS CDA NO. 260				surface ☒	tolerance	projection 	product family PV TERMINAL	
ltr	ecm no	dr	date	tolerances unless otherwise specified				title
k				angles	$\frac{XX}{1000} \pm 0.1 / X \pm 3$	INCH/MM 	CTW MALE PIN	
					$XXX \pm 0.05 / XX \pm 13$			
				$0^\circ \pm 2^\circ$	$XXXX \pm 0.020 / XXX \pm 0.051$	scale 1:1	dwg no	
				dr	H. SUNDY	2004-02-17	sheet 3 of 3	
				engr	H. SUNDY	2004-02-17	75653	
				chr	H. SUNDY	2004-02-17	CUSTOMER Drawing	
				appd	H. SUNDY	2004-02-17		
sheet index	revision sheet							size
								A4