


A		B	C	D	E
CAT. NO.	COLOR			REV	DESCRIPTION
109 - 250I - 001	BLACK				
109 - 250I - 002	WHITE/NATURAL				DATE



RoHS Compliant

NOTE:

1. FLAMMBILITY RATING: UL94V-2
2. MAX BUNDLE DIA. : 65 mm (2.56 inch)
3. MIN TENSILE STRENGTH : 40 lbs (18 kgs)
4. COLOR: SEE CHART

DRAWN: RYAN	Tolerance Unless Otherwise Specified
CHECKED: SCOTT	MATERIAL: PA66
	UNIT: mm
	SCALE: 1/2
APPROVAL: JEFF	SHEET: 1-0
	DATE: 2024/06/08

CnC Tech

Industrial Cable and Connector Technology

DESCRIPTION:

CABLES TIES

PART NO:

109 - 250I - X X X (SEE CHART)

1

2

3

4