


REVISION T






TABLE 2

(SEE NOTE 4)

"B"

2.54 [.100]

7.62 [.300]

12.70 [.500]

17.78 [.700]

22.86 [.900]

27.94 [1.100]




FIG 13 ET60T-D04-5-03-A04-X-RX-S-H SHOWN (DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 12)

Г				-
L	TABLE 1			TA
L	(SEE NOTE 3)			(SEE
L	POWER POS	"A"		SIGNAL POS
l	(LEFT)	DC POWER	AC POWER	(-3 ROWS)
L	01	N/A	N/A	-02
L	-02	5.50 [.217]	7.50 [.295]	-04
L	-03	11.00 [.433]	15.00 [.591]	-06
L	-04	16.50 [.650]	22.50 [.886]	-08
L	-05	22.00 [.866]	30.00 [1.181]	-10
L	-06	27.50 [1.083]	37.50 [1.476]	-12
L	-07	33.00 [1.299]	/]
L	-08	38.50 [1.516]	/	
L	-09	44.00 [1.732]	/	
	-10	49.50 [1.949]	/	

	TABLE 3				
	(SEE NOTE 3)				
POWER POS	"C"				
(RIGHT)	DC POWER	AC POWER			
01	N/A	N/A			
-02	5.50 [.217]	7.50 [.295]			
-03	11.00 [.433]	15.00 [.591]			
-04	16.50 [.650]	22.50 [.886]			
-05	22.00 [.866]	30.00 [1.181]			
-06	27.50 [1.083]	37.50 [1.476]			
-07	33.00 [1.299]	/			
-08	38.50 [1.516]	/			
-09	44.00 [1.732]	/			
-10	49.50 [1.949]	1			

TAD		1
TAB (SEE N	-	
SIGNAL POS (-5 ROWS)	"D"	NO
-01	N/A	POW
-02	2.00 [.079]	
-03	4.00 [.157]	1
-04	6.00 [.236]	1
-05	8.00 [.315]	
-06	10.00 [.394]	
-07	12.00 [.472]	
-08	14.00 [.551]	
		NO POWE

*

TABLE 7 (SEE NOTE 3)		
NO OF SPLIT POWER (LEFT)	"G"	
-01	N/A	
-02	8.00 [.315]	
-03	16.00 [.630]	
-04	24.00 [.945]	
TABLE 8 (SEE NOTE 3)		
NO OF SPLIT POWER (RIGHT)	"H"	
-01	N/A	
-02	8.00 [.315]	
-03	16.00 [.630]	
-04	24.00 [.945]	







TABLE 5 "E" "F" TAIL -R1 2.84 [.112] 2.84 [.112] -R2 3.61 [.142] 3.41 [.134] -RP 3.28 [.129] 2.50 [.098]

F:\DWG\MISC\MKTG\ET60T-XXX-X-XX-XXX-X-RX-X-MKT.SLDDRW









F:\DWG\MISC\MKTG\ET60T-XXX-X-XX-XX-X-RX-X-MKT.SLDDRW