



# Final Product/Process Change Notification

Document #:FPCN25572Z32

Issue Date:05 Aug 2024

<b>Title of Change:</b>	Update to <b>FPCN25572Z</b> - To include the Reliability Data of 5 V MiniGate Logic in US8 for Qualification of Vanguard Fab and Assembly Related Changes for Logic Parts.
<b>Proposed Changed Material First Ship Date:</b>	12 Feb 2025 or earlier if approved by customer
<b>Current Material Last Order Date:</b>	20 Nov 2023 <i>Orders received after the Current Material Last Order Date expiration are to be considered as orders for new changed material as described in this PCN. Orders for current (unchanged) material after this date will be per mutual agreement and current material inventory availability.</i>
<b>Current Material Last Delivery Date:</b>	N/A <i>The Current Material Last Delivery Date may be subject to change based on build and depletion of the current (unchanged) material inventory</i>
<b>Product Category:</b>	Active components – Integrated circuits
<b>Contact information:</b>	Contact your local onsemi Sales Office or <a href="mailto:logic.fpcn@onsemi.com">logic.fpcn@onsemi.com</a>
<b>PCN Samples Contact:</b>	Contact your local onsemi Sales Office to place sample order. Sample requests are to be submitted no later than 45 days after publication of this change notification. Samples delivery timing will be subject to request date, sample quantity and special customer packing/label requirements.
<b>Sample Availability Date:</b>	12 Jul 2024
<b>PPAP Availability Date:</b>	12 Aug 2024
<b>Additional Reliability Data:</b>	Contact your local onsemi Sales Office or <a href="mailto:ChangKit.Mok@onsemi.com">ChangKit.Mok@onsemi.com</a>
<b>Type of Notification:</b>	This is a Final Product/Process Change Notification (FPCN) sent to customers. The change will be implemented at 'Proposed Change Material First Ship Date' in compliance to J-STD-46 or ZVEI, or earlier upon customer approval, or per our signed agreements. onsemi will consider this proposed change and it's conditions acceptable, unless an inquiry is made in writing within 45 days of delivery of this notice. To do so, contact <a href="mailto:PCN.Support@onsemi.com">PCN.Support@onsemi.com</a> .
<b>Change Category</b>	
<b>Category</b>	<b>Type of Change</b>
Process - Wafer Production	Move of all or part of wafer fab to a different location/site/subcontractor, New wafer diameter
Equipment	Production from a new equipment/tool which uses a different basic technology or which due to its unique form or function can be expected to influence the integrity of the final product
Data Sheet	Change of datasheet parameters/electrical specification (min./max./typ. values) and/or AC/DC specification
Process - Assembly	Die attach material, Change of lead frame finishing material / area (internal), Change of wire bonding, Change of lead and heat slug plating material/plating thickness (external)

**Description and Purpose:**

With respect to FPCN25572Z, this represents information for 5 V MiniGate Logic in US8 only.

	From	To
<b>Fab</b>	Tower	Vanguard
<b>Wafer Diameter</b>	6 inch	8 inch
<b>Assembly Site</b>	onsemi Seremban	onsemi Seremban
<b>Bond Wire</b>	Au	PCC
<b>LeadFrame Plating</b>	Full Cu with Ag Stripe Over (Cu Ag)	Ni-Pd-Au-Ag (PPF)
<b>Die Attach</b>	8900NC	8006NS

**Datasheet Changes :**

NLV17SZxx, NLV27WZxx, NLV37WZxx, NLV7SZxx to NL17SZxx-Q, NL27WZxx-Q, NL37WZxx-Q, NL7SZxx-Q Family

Absolute Maximum Ratings and Recommended Operating Conditions - NLV17SZU04, NLV27SZU04 to NL17SZU04A-Q, NL27WZU04A-Q

**Existing Datasheet**

MAXIMUM RATINGS				
Symbol	Characteristics	Value	Unit	
V <sub>CC</sub>	DC Supply Voltage	-0.5 to +7.0	V	
V <sub>IN</sub>	DC Input Voltage	-0.5 to V <sub>CC</sub> + 0.5	V	
V <sub>OUT</sub>	DC Output Voltage	-0.5 to V <sub>CC</sub> + 0.5	V	
I <sub>IK</sub>	DC Input Diode Current	±50	mA	

  

RECOMMENDED OPERATING CONDITIONS					
Symbol	Characteristics	Min	Max	Unit	
V <sub>CC</sub>	Positive DC Supply Voltage	1.65	5.5	V	
V <sub>IN</sub>	DC Input Voltage	0	5.5	V	
V <sub>OUT</sub>	DC Output Voltage	0	V <sub>CC</sub>	V	
T <sub>A</sub>	Operating Temperature Range	-55	+125	°C	
t <sub>r</sub> , t <sub>f</sub>	Input Rise and Fall Time	V <sub>CC</sub> = 3.0 V to 3.6 V V <sub>CC</sub> = 4.5 V to 5.5 V	0	100 20	ns/V

**New**

MAXIMUM RATINGS				
Symbol	Characteristics	Value	Unit	
V <sub>CC</sub>	DC Supply Voltage	-0.5 to +6.5	V	
V <sub>IN</sub>	DC Input Voltage	-0.5 to +6.5	V	
V <sub>OUT</sub>	DC Output Voltage	-0.5 to V <sub>CC</sub> + 0.5	V	
I <sub>IK</sub>	DC Input Diode Current	V <sub>IN</sub> < GND	-50	mA

  

RECOMMENDED OPERATING CONDITIONS					
Symbol	Characteristics	Min	Max	Unit	
V <sub>CC</sub>	Positive DC Supply Voltage	1.65	5.5	V	
V <sub>IN</sub>	DC Input Voltage	0	5.5	V	
V <sub>OUT</sub>	DC Output Voltage	0	V <sub>CC</sub>	V	
T <sub>A</sub>	Operating Temperature Range	-55	+125	°C	
t <sub>r</sub> , t <sub>f</sub>	Input Rise and Fall Time	V <sub>CC</sub> = 1.65 V to 1.95 V V <sub>CC</sub> = 2.3 V to 2.7 V V <sub>CC</sub> = 3.0 V to 3.6 V V <sub>CC</sub> = 4.5 V to 5.5 V	0	20 20 10 5	ns/V

Absolute Maximum Ratings and Recommended Operating Conditions – All other devices

**Existing Datasheet**

MAXIMUM RATINGS				
Symbol	Characteristics	Value	Unit	
V <sub>CC</sub>	DC Supply Voltage	-0.5 to +7.0	V	
V <sub>IN</sub>	DC Input Voltage	-0.5 to +7.0	V	
V <sub>OUT</sub>	DC Output Voltage	Active-Mode (High or Low State) Tri-State Mode (Note 1) Power-Down Mode (V <sub>CC</sub> = 0 V)	-0.5 to V <sub>CC</sub> + 0.5 -0.5 to +7.0 -0.5 to +7.0	V
I <sub>IK</sub>	DC Input Diode Current	V <sub>IN</sub> < GND	-50	mA
I <sub>OK</sub>	DC Output Diode Current	V <sub>OUT</sub> < GND	-50	mA
	DC Output Diode Current	(NL17SZ32P5T5G-L22088 Only)	±50	

  

RECOMMENDED OPERATING CONDITIONS					
Symbol	Characteristics	Min	Max	Unit	
V <sub>CC</sub>	Positive DC Supply Voltage	1.65	5.5	V	
V <sub>IN</sub>	DC Input Voltage	0	5.5	V	
V <sub>OUT</sub>	DC Output Voltage	Active-Mode (High or Low State) Tri-State Mode (Note 1) Power-Down Mode (V <sub>CC</sub> = 0 V)	0 0 0	V <sub>CC</sub> 5.5 5.5	
	DC Output Voltage	(NL17SZ32P5T5G-L22088 Only)	0	V <sub>CC</sub>	
T <sub>A</sub>	Operating Temperature Range	-55	+125	°C	
t <sub>r</sub> , t <sub>f</sub>	Input Rise and Fall Time	V <sub>CC</sub> = 3.0 V to 3.6 V V <sub>CC</sub> = 4.5 V to 5.5 V	0	100 20	ns/V

**New**

MAXIMUM RATINGS				
Symbol	Characteristics	Value	Unit	
V <sub>CC</sub>	DC Supply Voltage	-0.5 to +6.5	V	
V <sub>IN</sub>	DC Input Voltage	-0.5 to +6.5	V	
V <sub>OUT</sub>	DC Output Voltage	Active-Mode (High or Low State) Tri-State Mode (Note 1) Power-Down Mode (V <sub>CC</sub> = 0 V)	-0.5 to V <sub>CC</sub> + 0.5 -0.5 to +6.5 -0.5 to +6.5	V
I <sub>IK</sub>	DC Input Diode Current	V <sub>IN</sub> < GND	-50	mA
I <sub>OK</sub>	DC Output Diode Current	V <sub>OUT</sub> < GND	-50	mA

  

RECOMMENDED OPERATING CONDITIONS					
Symbol	Characteristics	Min	Max	Unit	
V <sub>CC</sub>	Positive DC Supply Voltage	1.65	5.5	V	
V <sub>IN</sub>	DC Input Voltage	0	5.5	V	
V <sub>OUT</sub>	DC Output Voltage	Active-Mode (High or Low State) Tri-State Mode (Note 1) Power-Down Mode (V <sub>CC</sub> = 0 V)	0 0 0	V <sub>CC</sub> 5.5 5.5	
T <sub>A</sub>	Operating Temperature Range	-55	+125	°C	
t <sub>r</sub> , t <sub>f</sub>	Input Rise and Fall Time	V <sub>CC</sub> = 1.65 V to 1.95 V V <sub>CC</sub> = 2.3 V to 2.7 V V <sub>CC</sub> = 3.0 V to 3.6 V V <sub>CC</sub> = 4.5 V to 5.5 V	0	20 20 10 5	ns/V

DC Input Characteristics - NLV17SZ14, NLV17SZ17, NLV27WZ14, NLV27WZ17, NLV37WZ14, NLV37WZ17 to NL17SZ14-Q, NL17SZ17-Q, NL27WZ14-Q, NL27WZ17-Q, NL37WZ14-Q, NLV37WZ17-Q

### Existing Datasheet

DC ELECTRICAL CHARACTERISTICS

Symbol	Parameter	Condition	V <sub>CC</sub> (V)	T <sub>A</sub> = 25°C			-55°C ≤ T <sub>A</sub> ≤ 125°C		Units
				Min	Typ	Max	Min	Max	
V <sub>T+</sub>	Positive Input Threshold Voltage		1.65	0.6	1.0	1.4	0.6	1.4	V
			2.3	1.0	1.5	1.8	1.0	1.8	
			2.7	1.2	1.7	2.0	1.2	2.0	
			3.0	1.3	1.9	2.2	1.3	2.2	
			4.5	1.9	2.7	3.1	1.9	3.1	
			5.5	2.2	3.3	3.6	2.2	3.6	
V <sub>T-</sub>	Negative Input Threshold Voltage		1.65	0.2	0.5	0.8	0.2	0.8	V
			2.3	0.4	0.75	1.15	0.4	1.15	
			2.7	0.5	0.87	1.4	0.5	1.4	
			3.0	0.6	1.0	1.5	0.6	1.5	
			4.5	1.0	1.5	2.0	1.0	2.0	
			5.5	1.2	1.9	2.3	1.2	2.3	

### New

DC ELECTRICAL CHARACTERISTICS

Symbol	Parameter	Condition	V <sub>CC</sub> (V)	T <sub>A</sub> = 25°C			-55°C ≤ T <sub>A</sub> ≤ 125°C		Units
				Min	Typ	Max	Min	Max	
V <sub>T+</sub>	Positive Input Threshold Voltage		1.65	-	1.0	1.4	-	1.4	V
			2.3	-	1.5	1.8	-	1.8	
			2.7	-	1.7	2.0	-	2.0	
			3.0	-	1.9	2.2	-	2.2	
			4.5	-	2.7	3.1	-	3.1	
			5.5	-	3.3	3.6	-	3.6	
V <sub>T-</sub>	Negative Input Threshold Voltage		1.65	0.2	0.5	-	0.2	-	V
			2.3	0.4	0.75	-	0.4	-	
			2.7	0.5	0.87	-	0.5	-	
			3.0	0.6	1.0	-	0.6	-	
			4.5	1.0	1.5	-	1.0	-	
			5.5	1.2	1.9	-	1.2	-	

DC Input Characteristics - NLV7SZ57, NLV7SZ58, NLV7SZ97, NLV7SZ98, NLV7SZ99 to NL7SZ57-Q, NL7SZ58-Q, NL7SZ97-Q, NL7SZ98-Q, NLSZ99-Q

### Existing Datasheet

DC ELECTRICAL CHARACTERISTICS

Symbol	Parameter	Condition	V <sub>CC</sub> (V)	T <sub>A</sub> = 25°C			-40°C ≤ T <sub>A</sub> ≤ 85°C		-55°C ≤ T <sub>A</sub> ≤ 125°C		Unit
				Min	Typ	Max	Min	Max	Min	Max	
V <sub>T+</sub>	Positive Input Threshold Voltage		1.65	0.79	-	1.18	-	1.16	-	1.16	V
			2.3	1.11	-	1.56	-	1.56	-	1.56	
			3.0	1.5	-	1.87	-	1.87	-	1.87	
			4.5	2.16	-	2.74	-	2.74	-	2.74	
			5.5	2.61	-	3.33	-	3.33	-	3.33	
V <sub>T-</sub>	Negative Input Threshold Voltage		1.65	0.35	-	0.62	0.35	-	0.35	-	V
			2.3	0.58	-	0.87	0.58	-	0.58	-	
			3.0	0.64	-	1.19	0.64	-	0.64	-	
			4.5	1.41	-	1.9	1.41	-	1.41	-	
			5.5	1.78	-	2.2	1.78	-	1.78	-	
V <sub>HI</sub>	Negative Input Threshold Voltage		1.65	0.3	-	0.62	0.3	0.62	0.3	0.62	V
			2.3	0.4	-	0.8	0.4	0.8	0.4	0.8	
			3.0	0.53	-	0.87	0.53	0.87	0.53	0.87	
			4.5	0.71	-	1.04	0.71	1.04	0.71	1.04	
			5.5	0.8	-	1.2	0.8	1.2	0.8	1.2	

### New

DC ELECTRICAL CHARACTERISTICS

Symbol	Parameter	Condition	V <sub>CC</sub> (V)	T <sub>A</sub> = 25°C			-40°C ≤ T <sub>A</sub> ≤ 85°C		-55°C ≤ T <sub>A</sub> ≤ 125°C		Unit
				Min	Typ	Max	Min	Max	Min	Max	
V <sub>T+</sub>	Positive Input Threshold Voltage		1.65	-	-	1.4	-	1.4	-	1.4	V
			2.3	-	-	1.8	-	1.8	-	1.8	
			3.0	-	-	2.2	-	2.2	-	2.2	
			4.5	-	-	3.1	-	3.1	-	3.1	
			5.5	-	-	3.6	-	3.6	-	3.6	
V <sub>T-</sub>	Negative Input Threshold Voltage		1.65	0.2	-	-	0.2	-	0.2	-	V
			2.3	0.4	-	-	0.4	-	0.4	-	
			3.0	0.6	-	-	0.6	-	0.6	-	
			4.5	1.0	-	-	1.0	-	1.0	-	
			5.5	1.2	-	-	1.2	-	1.2	-	
V <sub>HI</sub>	Negative Input Threshold Voltage		1.65	0.1	0.1	0.9	0.46	0.9	0.1	0.9	V
			2.3	0.25	0.25	1.1	0.75	1.1	0.25	1.1	
			3.0	0.4	0.4	1.2	0.93	1.2	0.4	1.2	
			4.5	0.6	0.6	1.5	1.2	1.5	0.6	1.5	
			5.5	0.7	0.7	1.7	1.4	1.7	0.7	1.7	

DC Input Characteristics - All other devices:

### Existing Datasheet

DC ELECTRICAL CHARACTERISTICS

Symbol	Parameter	Condition	V <sub>CC</sub> (V)	T <sub>A</sub> = 25°C			-55°C ≤ T <sub>A</sub> ≤ 125°C		Units
				Min	Typ	Max	Min	Max	
V <sub>HI</sub>	High-Level Input Voltage		1.65 to 1.95	0.75 × V <sub>CC</sub>	-	-	0.75 × V <sub>CC</sub>	-	V
			2.3 to 5.5	0.70 × V <sub>CC</sub>	-	-	0.70 × V <sub>CC</sub>	-	
V <sub>LI</sub>	Low-Level Input Voltage		1.65 to 1.95	-	-	0.25 × V <sub>CC</sub>	-	0.25 × V <sub>CC</sub>	V
			2.3 to 5.5	-	-	0.30 × V <sub>CC</sub>	-	0.30 × V <sub>CC</sub>	

### New

DC ELECTRICAL CHARACTERISTICS

Symbol	Parameter	Condition	V <sub>CC</sub> (V)	T <sub>A</sub> = 25°C			-55°C ≤ T <sub>A</sub> ≤ 125°C		Units
				Min	Typ	Max	Min	Max	
V <sub>HI</sub>	High-Level Input Voltage		1.65 to 1.95	0.65 × V <sub>CC</sub>	-	-	0.65 × V <sub>CC</sub>	-	V
			2.3 to 5.5	0.70 × V <sub>CC</sub>	-	-	0.70 × V <sub>CC</sub>	-	
V <sub>LI</sub>	Low-Level Input Voltage		1.65 to 1.95	-	-	0.35 × V <sub>CC</sub>	-	0.35 × V <sub>CC</sub>	V
			2.3 to 5.5	-	-	0.30 × V <sub>CC</sub>	-	0.30 × V <sub>CC</sub>	

AC Characteristics - No change

Reason / Motivation for Change:

Supply disruption

Anticipated impact on fit, form, function, reliability, product safety or manufacturability:

The device has been qualified and validated based on the same Product Specification. The device has successfully passed the qualification tests. Potential impacts can be identified, but due to testing performed by onsemi in relation to the PCN, associated risks are verified and excluded.

No anticipated impacts.

<b>Sites Affected:</b>	
<b>onsemi Sites</b>	<b>External Foundry/Subcon Sites</b>
onsemi Seremban, Malaysia	Vanguard International Semiconductor, Taiwan

<b>Marking of Parts/ Traceability of Change:</b>	Custom source on label will show TW instead of US/JP to indicate new die source from Vanguard. Changed material may be identified by plant code or lot code too.
--	--

**Reliability Data Summary:**

**QV DEVICE NAME : NC7WZ132K8X**  
**RMS : S94843**  
**PACKAGE : US8**

Test	Specification	Condition	Interval	Results
High Temperature Operating Life	JESD22-A108	Ta=125°C, 100 % max rated Vcc	1008 hrs	0/77
High Temperature Storage Life	JESD22-A103	Ta=150°C	1008 hrs	0/77
Preconditioning	J-STD-020 / JESD-A113	MSL 1 @ 260°C, Pre TC, uHAST, HAST for surface mount pkgs only	-	0/231
Temperature Cycling	JESD22-A104	Ta= -65°C to +150°C	500 cyc	0/77
Highly Accelerated Stress Test	JESD22-A110	130°C, 85% RH, 18.8psig, bias	96 hrs	0/77
Unbiased Highly Accelerated Stress Test	JESD22-A118	130°C, 85% RH, 18.8psig, unbiased	96 hrs	0/77
Resistance to Solder Heat	JESD22- B106	Ta = 265°C, 10 sec Required for through hole devices only	-	0/10

**QV DEVICE NAME : NLV37WZ14USG**  
**RMS : S94844**  
**PACKAGE : US8**

Test	Specification	Condition	Interval	Results
High Temperature Operating Life	JESD22-A108	Ta=125°C, 100 % max rated Vcc	1008 hrs	0/77

**Note: AEC-1pager is attached.**

To view attachments:

1. Download pdf copy of the PCN to your computer
2. Open the downloaded pdf copy of the PCN
3. Click on the paper clip icon available on the menu provided in the left/bottom portion of the screen to reveal the Attachment field
4. Then click on the attached file.

**Electrical Characteristics Summary:**

Electrical characteristics available upon request.



# Final Product/Process Change Notification

Document #:FPCN25572Z32

Issue Date:05 Aug 2024

## List of Affected Parts:

**Note:** Only the standard (off the shelf) part numbers are listed in the parts list. Any custom parts affected by this PCN are shown in the customer specific PCN addendum in the PCN email notification, or on the **PCN Customized Portal**.

Current Part Number	New Part Number	Qualification Vehicle
NLV17SZ74USG	NL17SZ74USG-Q	NC7WZ132K8X, NLV37WZ14USG
NLV17SZ74USG-22523Z	NL17SZ74USG-Q	NC7WZ132K8X, NLV37WZ14USG
NLV27WZ00USG	NL27WZ00USG-Q	NC7WZ132K8X, NLV37WZ14USG
NLV27WZ08USG	NL27WZ08USG-Q	NC7WZ132K8X, NLV37WZ14USG
NLV27WZ08USG-22523Z	NL27WZ08USG-Q	NC7WZ132K8X, NLV37WZ14USG
NLV27WZ32USG	NL27WZ32USG-Q	NC7WZ132K8X, NLV37WZ14USG
NLV27WZ86USG	NL27WZ86USG-Q	NC7WZ132K8X, NLV37WZ14USG
NLV37WZ04USG	NL37WZ04USG-Q	NC7WZ132K8X, NLV37WZ14USG
NLV27WZ126USG	NL27WZ126USG-Q	NC7WZ132K8X, NLV37WZ14USG
NLV27WZ125USG	NL27WZ125USG-Q	NC7WZ132K8X, NLV37WZ14USG
NLV37WZ17USG	NL37WZ17USG-Q	NC7WZ132K8X, NLV37WZ14USG
NLV37WZ16USG	NL37WZ16USG-Q	NC7WZ132K8X, NLV37WZ14USG
NLV37WZ14USG	NL37WZ14USG-Q	NC7WZ132K8X, NLV37WZ14USG
NLV37WZ07USG	NL37WZ07USG-Q	NC7WZ132K8X, NLV37WZ14USG