

**Industrial Ethernet  
IE-C5DB4RE0100MSSMCS-E**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Assembled IE cables, railway cable, Cat. 5, PUR, black,  
M12

**General ordering data**

Type	IE-C5DB4RE0100MSSMCS-E
Order No.	<a href="#">1059340100</a>
Version	System cable, M12 D-code – IP 67 straight pin, M12 D-code – IP 67 straight socket, Cat.5 (ISO/ IEC 11801) / Cat.5e (TIA T568-B), Radox GKW S, 10 m
GTIN (EAN)	4032248806669
Qty.	1 pc(s).

**Industrial Ethernet  
IE-C5DB4RE0100MSSMCS-E**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**
**Dimensions and weights**

Length	10 m	Length (inches)	0.394 inch
Net weight	804 g	Insulation cross-section	1.95 mm

**Temperatures**

Operating temperature, max.	90 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	90 °C	Storage temperature, min.	-40 °C
Operating temperature	-40 °C...90 °C	Storage temperature	-40 °C...90 °C
Installation temperature	-25 °C...90 °C		

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Standards**

Fire safety for railway vehicles	According to DIN 5510-2 fire safety levels 1,2,3,4, According to BS 6853, According to EN50288-2-2, According to EN 45545, HL1 - HL3	Fire protection in buses	according to ISO 6722-1 5.22 (UN ECE-R 118.01)
Flames propagate vertically on bundled cables	According to BS4066-3, DIN EN 50266-2-5, According to IEC 60332-3-25 D	Impervious to smoke	According to BS 6853 Appendix D, in accordance with EN 50268-2, According to IEC 61034-2
Corrosiveness of fumes	to IEC 60754-2	Hydrogen halide content	According to EN-50267-2-1, According to IEC 60754-1
Poisonous gases	According to BS 6853 Appendix B	Fluorine content	According to EN 60684-2 Section 45.2
Multi-wire metallic data and control cable	According to EN50288-2-2	Connector standard	IEC 61076-2-101
Certificate no. (cULus)	E316369		

**Cable structure**

Strands	7	Cross-section	2*2*AWG 22/7 - 2*2*0.36 mm <sup>2</sup>
Insulation cross-section	1.95 mm	Shielding	SF/UTP
Material sheath	Radox GKW S	Sheath diameter, min.	6.95 mm
Sheath diameter, max.	7.55 mm	Sheathing colour	black

**Electrical properties of cable**

Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)
----------	---

**Mechanical and material properties of cable**

Min. bending radius, repetitive	6 * diameter	Abrasion resistance	very good
Resistance to oils	in accordance with EN 50306-3	Halogen	halogen-free, according to IEC 60754-2
Corrosiveness of fumes	to IEC 60754-2	Impervious to smoke	According to BS 6853 Appendix D, in accordance with EN 50268-2, According to IEC 61034-2

Creation date March 7, 2019 10:59:26 AM CET

**Industrial Ethernet  
IE-C5DB4RE0100MSSMCS-E**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****plug**

Connector left	M12 D-code – IP 67 straight pin	Connector right	M12 D-code – IP 67 straight socket
----------------	------------------------------------	-----------------	---------------------------------------

**Classifications**

ETIM 3.0	EC000830	ETIM 4.0	EC000830
ETIM 5.0	EC000830	ETIM 6.0	EC002599
eClass 6.2	27-06-91-90	eClass 7.1	27-06-91-90
eClass 8.1	27-06-91-90	eClass 9.0	27-06-03-08
eClass 9.1	27-06-03-08		

**Approvals**

Approvals



ROHS Conform

**Downloads**


Brochure/Catalogue	<a href="#">CAT 9 IETH 15/16 EN</a> <a href="#">CAT 8 SAI 15/16 EN</a> <a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a>
Engineering Data	<a href="#">WSCAD</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>

**Data sheet****Industrial Ethernet  
IE-C5DB4RE0100MSSMCS-E**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings****Detailed drawing**

M12		M12
1	yellow	1
2	white	2
3	orange	3
4	blue	4



**Industrial Ethernet  
IE-C5DB4RE0100MSSMCS-E**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Accessories**

**Screwty® cable gland tool**



**The ideal tool for any application**

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
Screwty- M12	<a href="#">1900000000</a>	Tools, Cable gland tool for moulded M12 lines	4032248375868	1 pc(s).
Screwty Set	<a href="#">1910000000</a>	Tools, Bolting tool	4032248436842	1 pc(s).

**Tool**



Tools for stripping the sheathing from uncut power lines and outlet lines, plus screwdrivers for installing Pick-to-Light components.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
Screwty-M12- DM	<a href="#">1900001000</a>	Tools, Cable gland tool for moulded M12 lines	4032248436408	1 pc(s).
Screwty Set - DM	<a href="#">1920000000</a>	Tools, Bolting tool	4032248436859	1 pc(s).

**Industrial Ethernet  
IE-C5DB4RE0100MSSMCS-E**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**

**Blank**



TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are five different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the SMark laser printer, PrintJet ADVANCED, plotter, MC-Mobilo or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
TM-I 12 MC	<a href="#">1718411687</a>	TM-I, Insert markers, 12 x 4	4008190348984	320 pc(s).
NE GE		mm, yellow		

**Industrial Ethernet  
IE-C5DB4RE0100MSSMCS-E**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**

**Blank**



TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are five different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the SMark laser printer, PrintJet ADVANCED, plotter, MC-Mobilo or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
TM-I 18 MC	<a href="#">1718431687</a>	TM-I, Insert markers, 18 x 4	4008190349028	320 pc(s).
NE GE		mm, yellow		