

# APPROVAL SHEET

**MULTILAYER CERAMIC CAPACITORS**

**Soft Termination High Voltage Series**  
**(SH\_200V to 3000V)**

**NP0 & X7R Dielectrics**  
**0603 to 1812 Sizes, 200V to 3000V**  
**Halogen Free & RoHS Compliance**



\*Contents in this sheet are subject to change without prior notice.

## Multilayer Ceramic Capacitors

### 1. INTRODUCTION

WTC Multilayer Ceramic Chip Capacitors supplied in tape & reel package are ideally suitable for thick-film hybrid circuits and automatic surface mounting on any printed circuit boards. All of WTC's MLCC products meet RoHS directive.

SH series use a special material between nickel-barrier and ceramic body. It provides excellent performance to against bending stress occurred during process and provide more security for PCB process.

The nickel-barrier terminations are consisted of a nickel barrier layer over the silver metallization and then finished by electroplated solder layer to ensure the terminations have good solderability. The nickel barrier layer in terminations prevents the dissolution of termination when extended immersion in molten solder at elevated solder temperature.

### 2. FEATURES

- a. Withstanding 5mm of substrate bending.
- b. High Voltage in a given case size.
- c. High reliability and stability

### 3. APPLICATIONS

- a. DC to DC converter.
- b. High voltage coupling/DC blocking.
- c. Back-lighting inverters.
- d. Snubbers in high frequency power convertors

### 4. HOW TO ORDER

<b>SH</b>	<b>21</b>	<b>B</b>	<b>102</b>	<b>K</b>	<b>102</b>	<b>C</b>	<b>I</b>
<b>Series</b>	<b>Size</b>	<b>Dielectric</b>	<b>Capacitance</b>	<b>Tolerance</b>	<b>Rated voltage</b>	<b>Termination</b>	<b>Packaging</b>
SH=Soft termination	18=0603 (1608)	N=NP0 (C0G)	Two significant digits followed by no. of zeros.	B=±0.1pF C=±0.25pF D=±0.5pF F=±1% G=±2% J=±5% K=±10% M=±20% Z=−20/+80%	Two significant digits followed by no. of zeros. And R is in place of decimal point.	C= Ag Polymer /Ni/Sn	T=7" reeled G=13" reeled
High Voltage	21=0805 (2012)	B=X7R	Eg. 102=10x10 <sup>2</sup> =1000pF		201=200 VDC 251=250 VDC 401=400 VDC 451=450 VDC 501=500 VDC 631=630 VDC 102=1000 VDC 152=1500 VDC 202=2000 VDC 302=3000 VDC		
	31=1206 (3216)						
	32=1210 (3225)						
	42=1808 (4520)						
	43=1812 (4532)						

Note 1: Please see below product range to find right termination code.

Multilayer Ceramic Capacitors

## 5. EXTERNAL DIMENSIONS

Size Inch (mm)	L (mm)	W (mm)	T (mm)/Symbol	Remark	M <sub>B</sub> (mm)
0603(1608)	1.60±0.20	0.80±0.10	0.80±0.07 S		0.40±0.15
	1.60±0.30	0.80±0.30	0.80±0.30 X		
0805 (2012)	2.00±0.20	1.25±0.10	0.60±0.10 A		0.50±0.20
			0.80±0.10 B		
			1.25±0.10 D	#	
	2.00±0.30	1.25±0.30	1.25±0.30 I	#	
1206 (3216)	3.20+0.4/-0.1	1.60±0.15	0.80±0.10 B		0.60±0.20 (0.5±0.25)*
			0.95±0.10 C	#	
			1.25±0.10 D	#	
	3.20+0.4/-0.1	1.60±0.20	1.60±0.20 G	#	
	3.20±0.50	1.60±0.50	1.60±0.50 P	#	
1210 (3225)	3.20±0.40	2.50±0.20	0.95±0.10 C	#	0.75±0.25
			1.25±0.10 D	#	
	3.20±0.60	2.50±0.50	1.60±0.20 G	#	
			2.00±0.20 K	#	
			2.50±0.50 M	#	
1808 (4520)	4.50+0.6/-0.4	2.03±0.25	1.25±0.10 D	#	0.50±0.25
			2.00±0.20 K	#	
1812 (4532)	4.50+0.6/-0.4	3.20±0.30	1.25±0.10 D	#	0.50±0.25
			1.60±0.20 G	#	
			2.00±0.20 K	#	
	3.20±0.40	2.50±0.50 M	2.50±0.50 M	#	

# Reflow soldering only is recommended.

\* For 1210(100V)/Cap>1μF or 1210(250V)/Cap>0.47μF or 1210(400V~630V)/Cap>0.22μF




Fig. 1 The outline of MLCC

## 6. GENERAL ELECTRICAL DATA

Dielectric	NP0		X7R
Size	0603, 0805, 1206, 1210, 1808, 1812		
Capacitance*	0.5pF to 0.01μF		100pF to 1.0μF
Capacitance tolerance***	Cap≤5pF: C (±0.25pF) 5pF<Cap<10pF: D (±0.5pF) Cap≥10pF: F (±1%), G (±2%), J (±5%), K (±10%)		K (±10%), M (±20%)
Rated voltage (WVDC)	200V to 3000V		
Q/DF*	Cap<30pF: Q≥400+20C Cap≥30pF: Q≥1000		DF≤2.5%
Insulation resistance at Ur**	Ur=200~630V: ≥10GΩ or RxC≥100Ω·F whichever is smaller Ur=1000~3000V: ≥10GΩ		
Dielectric strength	200~300V: ≥2 x WVDC 400V~450V: ≥1.2 x WVDC 500~999V: ≥1.5 x WVDC 1000~3000V: ≥1.2 x WVDC		
Operating temperature	-55 to +125°C		
Capacitance characteristic	±30ppm		±15%
Termination	Ni/Sn (lead-free termination)		

\* Measured at the condition of 30~70% related humidity.

NP0: Apply 1.0±0.2Vrms, 1.0MHz±10% for Cap≤1000pF and 1.0±0.2Vrms, 1.0kHz±10% for Cap>1000pF, 25°C at ambient temperature  
X7R, X5R: Apply 1.0±0.2Vrms, 1.0kHz±10%, at 25°C am bient temperature.

Y5V: Apply 1.0±0.2Vrms, 1.0kHz±10%, at 20°C ambient temperature.

\*\* Preconditioning for Class II MLCC: Perform a heat treatment at 150±10°C for 1 hour, then leave in a mbient condition for 24±2 hours before measurement.

Multilayer Ceramic Capacitors

**7. CAPACITANCE RANGE (MIDDLE VOLTAGE - 200V to 630V)**

**7-1 NP0 Dielectric**

DIELECTRIC	NP0																							
	SIZE		0603				0805				1206				1210				1808		1812			
	RATED VOLTAGE	200	250	200	250	500	630	200	250	500	630	200	250	500	630	500	630	200	250	500	630			
Capacitance	0.5pF (0R5)	S	S	A	A	A	A																	
	1.0pF (1R0)	S	S	A	A	A	A																	
	1.2pF (1R2)	S	S	A	A	A	A																	
	1.5pF (1R5)	S	S	A	A	A	A	B	B	B	B													
	1.8pF (1R8)	S	S	A	A	A	A	B	B	B	B					D	D							
	2.2pF (2R2)	S	S	A	A	A	A	B	B	B	B					D	D							
	2.7pF (2R7)	S	S	A	A	A	A	B	B	B	B					D	D							
	3.3pF (3R3)	S	S	A	A	A	A	B	B	B	B					D	D							
	3.9pF (3R9)	S	S	A	A	A	A	B	B	B	B					D	D							
	4.7pF (4R7)	S	S	A	A	A	A	B	B	B	B					D	D							
	5.6pF (5R6)	S	S	A	A	A	A	B	B	B	B					D	D							
	6.8pF (6R8)	S	S	A	A	A	A	B	B	B	B					D	D							
	8.2pF (8R2)	S	S	A	A	A	A	B	B	B	B					D	D							
	10pF (100)	S	S	A	A	A	A	B	B	B	B	C	C	C	C	D	D	D	D	D	D			
	12pF (120)	S	S	A	A	A	A	B	B	B	B	C	C	C	C	D	D	D	D	D	D			
	15pF (150)	S	S	A	A	A	A	B	B	B	B	C	C	C	C	D	D	D	D	D	D			
	18pF (180)	S	S	A	A	A	A	B	B	B	B	C	C	C	C	D	D	D	D	D	D			
	22pF (220)	S	S	A	A	A	A	B	B	B	B	C	C	C	C	D	D	D	D	D	D			
	27pF (270)	S	S	A	A	A	A	B	B	B	B	C	C	C	C	D	D	D	D	D	D			
	33pF (330)	S	S	A	A	A	A	B	B	B	B	C	C	C	C	D	D	D	D	D	D			
	39pF (390)	S	S	A	A	A	A	B	B	B	B	C	C	C	C	D	D	D	D	D	D			
	47pF (470)	S	S	A	A	A	A	B	B	B	B	C	C	C	C	D	D	D	D	D	D			
	56pF (560)	S	S	A	A	A	A	B	B	B	B	C	C	C	C	D	D	D	D	D	D			
	68pF (680)	S	S	A	A	A	A	B	B	B	B	C	C	C	C	D	D	D	D	D	D			
	82pF (820)	S	S	A	A	B	B	B	B	B	B	C	C	C	C	D	D	D	D	D	D			
	100pF (101)	S	S	A	B	B	B	B	B	B	B	C	C	C	C	D	D	D	D	D	D			
	120pF (121)	S	S	A	B	D	D	B	B	B	B	C	C	C	C	D	D	D	D	D	D			
	150pF (151)	S	S	B	D	D	D	B	B	B	B	C	C	C	C	D	D	D	D	D	D			
	180pF (181)	S	S	B	D	D	D	B	B	B	B	C	C	C	C	D	D	D	D	D	D			
	220pF (221)	S	S	D	D	D	D	B	B	B	B	C	C	C	C	D	D	D	D	D	D			
	270pF (271)	X	X	D	D	D	D	B	C	C	C	C	C	C	C	K	K	K	D	D	D			
	330pF (331)	X	X	D	D	D	D	B	C	C	C	C	C	C	C	K	K	D	D	D	D			
	390pF (391)	X	X	D	D	D	D	B	C	C	C	C	C	C	C	K	K	D	D	D	D			
	470pF (471)	X	X	D	D	I	I	C	C	C	C	C	C	C	C	K	K	D	D	D	D			
	560pF (561)	D	D	I	I	C	D	D	D	C	C	C	C	C	C	K	K	D	D	D	D			
	680pF (681)	D	D	I	I	C	D	D	D	C	C	C	C	C	C	K	K	D	D	D	D			
	820pF (821)	D	D	I	I	C	G	G	G	C	C	C	C	C	C	K	K	D	D	D	D			
	1,000pF (102)	D	D	I	I	C	G	G	G	D	D	D	D	K	K	D	D	D	D	D	D			
	1,200pF (122)	D	D			C	G	G	G	D	D	D	D	K	K	D	D	D	D	D	D			
	1,500pF (152)	D	D			D	G	G	G	D	D	D	D	K	K	D	D	D	D	D	D			
	1,800pF (182)	D	D			D	G	G	G	D	D	D	D	K	K	D	D	D	D	D	D			
	2,200pF (222)	D	D			D	G	G	G	D	D	D	D	K	K	D	D	D	D	D	D			
	2,700pF (272)					D	G			D	D	D	D			D	D	D	D	D	D			
	3,300pF (332)					D	G			D	D	D	D			D	D	D	D	D	D			
	3,900pF (392)					D	G			D	D	D	D			D	D	D	D	D	D			
	4,700pF (472)					D	G			G	G					D	D	D	D	D	D			
	5,600pF (562)									G	G					D	D	D	D	D	D			
	6,800pF (682)									G	G					D	D	D	D	D	D			
	8,200pF (822)									G	G					D	D	D	D	D	D			
	0.010μF (103)									G	G					D	D	D	D	D	D			
	0.015μF (153)															G	G							
	0.018μF (183)															K	K							
	0.022μF (223)															K	K							

1. The letter in cell is expressed the symbol of product thickness.

2. For more information about products with special capacitance or other data, please contact WTC local representative.

Multilayer Ceramic Capacitors

**7-2 X7R Dielectric**

Capacitance	DIELECTRIC	X7R																	
	SIZE	0603			0805			1206			1210			1808			1812		
	RATED VOLTAGE (VDC)	200	250	200	250	500	630	200	250	400	450	500	630	200	250	400	450	500	630
	100pF (101)	X	X	D	D	B	B	D	D			D	D						
	120pF (121)	X	X	D	D	B	B	D	D			D	D						
	150pF (151)	X	X	D	D	B	B	D	D			D	D					D	D
	180pF (181)	X	X	D	D	B	B	D	D			D	D					D	D
	220pF (221)	X	X	D	D	B	B	D	D			D	D					D	D
	270pF (271)	X	X	D	D	B	B	D	D			D	D					D	D
	330pF (331)	X	X	D	D	B	B	D	D			D	D					D	D
	390pF (391)	X	X	D	D	B	B	D	D			D	D					D	D
	470pF (471)	X	X	D	D	B	B	D	D			D	D					D	D
	560pF (561)	X	X	D	D	B	B	D	D			D	D					D	D
	680pF (681)	X	X	D	D	B	B	D	D			D	D					D	D
	820pF (821)	X	X	D	D	B	B	D	D			D	D					D	D
	1,000pF (102)	X	X	D	D	B	B	D	D			D	D	C	C			D	D
	1,200pF (122)	X	X	D	D	B	B	D	D			D	D	C	C			D	D
	1,500pF (152)	X	X	D	D	B	B	D	D			D	D	C	C			D	D
	1,800pF (182)	X	X	D	D	B	B	D	D			D	D	C	C			D	D
	2,200pF (222)	X	X	D	D	B	B	D	D			D	D	C	C			D	D
	2,700pF (272)	X	X	D	D	B	B	D	D			D	D	C	C			D	D
	3,300pF (332)	X	X	D	D	B	B	D	D			D	D	C	C			D	D
	3,900pF (392)	X	X	D	D	B	B	D	D			D	D	C	C			D	D
	4,700pF (472)	X	X	D	D	D	D	D	D			D	D	C	C			D	D
	5,600pF (562)	X	X	D	D	D	D	D	D			D	D	C	C			D	D
	6,800pF (682)	X	X	D	D	D	D	D	D			D	D	C	C			D	D
	8,200pF (822)	X	X	D	D	D	D	D	D			D	D	C	C			D	D
	0.010μF (103)	X	X	D	D	D	D	D	D			D	D	C	C			D	D
	0.012μF (123)			D	D	D	D	D	D			D	D	C	C			D	D
	0.015μF (153)			D	D	D	D	D	D			D	D	C	C			D	D
	0.018μF (183)			D	D	D	D	D	D			D	D	C	C			D	D
	0.022μF (223)			D	D	D	D	D	D			G	G	C	C			D	D
	0.027μF (273)			D	D	D	D	D	D			G	G	C	C			G	G
	0.033μF (333)			D	D	D	G	G	G			G	G	C	C			G	G
	0.039μF (393)			D	D	G	G	G	G			G	G	C	C			G	G
	0.047μF (473)			D	D	G	G	G	G			G	G	D	D			G	G
	0.056μF (563)			D	D	G	G	G	G			G	G	D	D			G	G
	0.068μF (683)			D	D	G	G	G	G			G	G	K	K			K	K
	0.082μF (823)			D	G	G	G	G	G			G	G	K	K			D	D
	0.10μF (104)			D	G	G	G	G	G			G	G	K	K			D	D
	0.12μF (124)											G	G	M	M	M	M	D	D
	0.15μF (154)											M	M	M	M	M	M	K	K
	0.18μF (184)											M	M	M	M	M	M	K	K
	0.22μF (224)											M	M	M	M	M	M	K	K
	0.27μF (274)											M	M	M	M	M	M	K	K
	0.33μF (334)											M	M	M	M	M	M	K	K
	0.39μF (394)											M	M					K	K
	0.47μF (474)											M	M					K	K
	0.56μF (564)											M	M					M	M
	0.68μF (684)											M	M					M	M
	0.82μF (824)											M	M					M	M
	1.0μF (105)																	M	M

1. The letter in cell is expressed the symbol of product thickness.

2. For more information about products with special capacitance or other data, please contact WTC local representative.

## 8. CAPACITANCE RANGE (HIGH VOLTAGE - 1kV to 3kV)

### 8-1 NP0 Dielectric

Capacitance	DIELECTRIC	NP0														
	SIZE	0805			1206			1210			1808			1812		
	RATED VOLTAGE	1000	1000	1500	2000	1000	1500	2000	1000	1500	2000	3000	1000	1500	2000	3000
	0.5pF (0R5)	D														
	1.0pF (1R0)	D														
	1.2pF (1R2)	D														
	1.5pF (1R5)	D	B	B	B											
	1.8pF (1R8)	D	B	B	B											
	2.0pF (2R0)	D	B	B	B				D	D	D	D				
	2.2pF (2R2)	D	B	B	B				D	D	D	D				
	2.7pF (2R7)	D	B	B	B				D	D	D	D				
	3.3pF (3R3)	D	B	B	B				D	D	D	D				
	3.9pF (3R9)	D	B	B	B				D	D	D	D				
	4.7pF (4R7)	D	B	B	B				D	D	D	D				
	5.6pF (5R6)	D	B	B	B				D	D	D	D				
	6.8pF (6R8)	D	B	B	B				D	D	D	D				
	8.2pF (8R2)	D	B	B	B				D	D	D	D				
	10pF (100)	D	B	B	B	C	C	C	D	D	D	D	D	D	D	
	12pF (120)	D	B	B	B	C	C	C	D	D	D	D	D	D	D	
	15pF (150)	D	B	B	B	C	C	C	D	D	D	D	D	D	D	
	18pF (180)	D	B	B	B	C	C	C	D	D	D	D	D	D	D	
	22pF (220)	D	B	B	B	C	C	C	D	D	D	D	D	D	D	
	27pF (270)	D	B	B	B	C	C	C	D	D	D	D	D	D	D	
	33pF (330)	D	B	C	C	C	C	C	D	D	D	D	D	D	D	
	39pF (390)	D	B	C	C	C	C	C	D	D	D	D	D	D	D	
	47pF (470)	D	C	C	C	C	C	C	D	D	D	D	D	D	D	
	56pF (560)	D	C	D	D	C	D	D	D	D	D	D	D	D	D	
	68pF (680)	D	C	D	D	C	D	D	D	D	D	D	D	D	D	
	82pF (820)	D	D	D	D	C	D	D	D	D	D	D	D	D	D	
	100pF (101)	D	D	D	D	D	D	D	D	K	K	K	D	D	D	
	120pF (121)	D	D	G	G	D	D	D	D	D	K	K	D	D	D	
	150pF (151)	D	D	G	G	D	G	G	D	K	K	K	D	D	D	
	180pF (181)	D	G	G	G	D	G	G	D	K	K	K	D	D	K	
	220pF (221)	D	G	G	G	G	G	G	D	K	K	K	D	D	K	
	270pF (271)	D	G	P	P	G	K	K	K	K	K	K	D	K	K	
	330pF (331)	D	G	P	P	G	K	K	K	K	K	K	D	K	K	
	390pF (391)	D	G	P	P	G	M	M	K	K	K	K	D	K	K	
	470pF (471)	G				G	M	M	K	K	K	K	K	K	K	
	560pF (561)	G				G			K	K	K	K	K	K	K	
	680pF (681)	G				G			K	K	K	K	K	K	K	
	820pF (821)	G				G			K				K	K	K	
	1,000pF (102)	G				G			K				K	K	K	
	1,200pF (122)					G							K			
	1,500pF (152)					K							K			
	1,800pF (182)					M							K			
	2,200pF (222)					M							K			
	2,700pF (272)					M							K			
	3,300pF (332)					M							K			
	3,900pF (392)					M							M			

1. The letter in cell is expressed the symbol of product thickness.

2. For more information about products with special capacitance or other data, please contact WTC local representative.

Multilayer Ceramic Capacitors

**8-2 X7R Dielectric**

DIELECTRIC	X7R														
	0805		1206			1210			1808			1812			
RATED VOLTAGE	1000	1000	1500	2000	1000	1500	2000	1000	1500	2000	3000	1000	1500	2000	3000
Capacitance	100pF (101)	B	D	D	D	D	D								
	120pF (121)	B	D	D	D	D	D								
	150pF (151)	B	D	D	D	D	D	D	D	D	D				
	180pF (181)	B	D	D	D	D	D	D	D	D	D				
	220pF (221)	B	D	D	D	D	D	D	D	D	D				
	270pF (271)	B	D	D	D	D	D	D	D	D	D	D	D	K	
	330pF (331)	B	D	D	D	D	D	D	D	D	K	D	D	K	
	390pF (391)	B	D	D	D	D	D	D	D	D	K	D	D	K	
	470pF (471)	B	D	D	D	D	D	D	D	D	K	D	D	K	
	560pF (561)	B	D	D	D	D	D	D	D	D	K	D	D	K	
	680pF (681)	B	D	D	D	D	D	D	D	D	K	D	D	K	
	820pF (821)	B	D	G	G	D	D	D	D	D	K	D	D	K	
	1,000pF (102)	B	D	G	G	D	D	D	K	K	K	D	D	K	
	1,200pF (122)	B	D	G	G	D	M	M	D	K	K	D	D	K	
	1,500pF (152)	D	D	G	G	D	M	M	D	K	K	D	D	K	
	1,800pF (182)	D	D	G	G	D	M	M	D	K	K	D	G	M	
	2,200pF (222)	D	D	G	G	D	M	M	D	K	K	D	G	M	
	2,700pF (272)	D	D	G	G	D	M	M	D	K	K	D	G	M	
	3,300pF (332)	D	D	G	G	D	M	M	D	K	K	D	K	M	
	3,900pF (392)	D	D	G		G	M	M	D	K	K	D	K	M	
	4,700pF (472)	D	D	G		G	M	M	D	K	K	D	K	M	
	5,600pF (562)	D	D	G		G	M	M	K	K	K	D	M	M	
	6,800pF (682)	D	D	G		G	M	M	K	K	K	D	M	M	
	8,200pF (822)	D	D	G		G	M	M	K			D	M	M	
	0.010μF (103)		D	G		G		K				D	M	M	
	0.012μF (123)		G			G		K				K			
	0.015μF (153)		G			G		K				K			
	0.018μF (183)					G		K				M			
	0.022μF (223)					G		K				M			
	0.033μF (333)					G		K				M			
	0.039μF (393)					K		K				M			
	0.047μF (473)						M		K			M			
	0.056μF (563)						M		K			M			
	0.068μF (683)						M					M			
	0.10μF (104)											M			

1. The letter in cell is expressed the symbol of product thickness.

2. For more information about products with special capacitance or other data, please contact WTC local representative.

Multilayer Ceramic Capacitors

**9. PACKAGING DIMENSION AND QUANTITY**

Size	Thickness/Symbol (mm)	Paper tape		Plastic tape	
		7" reel	13" reel	7" reel	13" reel
0603	0.80±0.07	S	4k	15k	-
	0.80 ±0.30	X	4k	15k	-
0805	0.60±0.10	A	4k	15k	-
	0.80±0.10	B	4k	15k	-
	1.25±0.10	D	-	-	3k
	1.25±0.30	I	-	-	3k
1206	0.80±0.10	B	4k	15k	-
	0.95±0.10	C	-	-	3k
	1.25±0.10	D	-	-	3k
	1.60±0.20	G	-	-	2k
	1.60±0.50	P	-	-	2k
1210	0.95±0.10	C	-	-	3k
	1.25±0.10	D	-	-	3k
	1.60±0.20	G	-	-	2k
	2.00±0.20	K	-	-	1k
	2.50±0.50	M	-	-	1k
1808	1.25±0.10	D	-	-	2k
	2.00±0.20	K	-	-	1k
1812	1.25±0.10	D	-	-	1k
	1.60±0.20	G	-	-	1k
	2.00±0.20	K	-	-	1k
	2.50±0.50	M	-	-	0.5k

Unit: pieces



Multilayer Ceramic Capacitors

## 10. RELIABILITY TEST CONDITIONS AND REQUIREMENTS

No.	Item	Test Condition	Requirements																
1.	Visual and Mechanical	--	* No remarkable defect. * Dimensions to conform to individual specification sheet.																
2.	Capacitance	Class I: (NP0)	* Shall not exceed the limits given in the detailed spec.																
3.	Q/D.F. (Dissipation Factor)	Cap $\leq$ 1000pF, 1.0 $\pm$ 0.2Vrms, 1MHz $\pm$ 10% Cap $>$ 1000pF, 1.0 $\pm$ 0.2Vrms, 1KHz $\pm$ 10% Class II: (X7R, Y5V) 1.0 $\pm$ 0.2Vrms, 1kHz $\pm$ 10%	NP0: Cap $\geq$ 30pF, Q $\geq$ 1000; Cap $<$ 30pF, Q $\geq$ 400+20C X7R: $\leq$ 2.5% Y5V: $\leq$ 5.0%																
		* Before initial measurement (Class II only): To apply de-aging at 150°C for 1hr then set for 24 $\pm$ 2 hrs at room temp .																	
4.	Dielectric Strength	* To apply voltage: 200V~300V $\geq$ 2 times VDC 400V~450V $\geq$ 1.2 times VDC 500V~999V $\geq$ 1.5 times VDC 1000V~3000V $\geq$ 1.2 times VDC 4000V $\geq$ 1.1 times VDC  * Duration: 1 to 5 sec. * Charge & discharge current less than 50mA.	* No evidence of damage or flash over during test.																
5.	Insulation Resistance	Rated voltage: 200~630V      To apply rated voltage (500V max.) for 60 sec. Rated voltage: $\geq$ 630V      To apply 500V for 60 sec.	$\geq$ 10G $\Omega$ or Rx $C\geq$ 100 $\Omega$ -F whichever is smaller																
6.	Temperature Coefficient	With no electrical load. <table border="1"> <tr> <td>T.C.</td> <td>Operating Temp</td> </tr> <tr> <td>NP0</td> <td>-55~125°C at 25°C</td> </tr> <tr> <td>X7R</td> <td>-55~125°C at 25°C</td> </tr> <tr> <td>Y5V</td> <td>-25~85°C at 20°C</td> </tr> </table>	T.C.	Operating Temp	NP0	-55~125°C at 25°C	X7R	-55~125°C at 25°C	Y5V	-25~85°C at 20°C	<table border="1"> <tr> <td>T.C.</td> <td>Capacitance Change</td> </tr> <tr> <td>NP0</td> <td>Within <math>\pm</math>30ppm/°C</td> </tr> <tr> <td>X7R</td> <td>Within <math>\pm</math>15%</td> </tr> <tr> <td>Y5V</td> <td>Within +30%/-80%</td> </tr> </table> * Before initial measurement (Class II only): To apply de-aging at 150°C for 1hr then set for 24 $\pm$ 2 hrs at room temp .	T.C.	Capacitance Change	NP0	Within $\pm$ 30ppm/°C	X7R	Within $\pm$ 15%	Y5V	Within +30%/-80%
T.C.	Operating Temp																		
NP0	-55~125°C at 25°C																		
X7R	-55~125°C at 25°C																		
Y5V	-25~85°C at 20°C																		
T.C.	Capacitance Change																		
NP0	Within $\pm$ 30ppm/°C																		
X7R	Within $\pm$ 15%																		
Y5V	Within +30%/-80%																		
7.	Adhesive Strength of Termination	* Pressurizing force : 5N (0603) and 10N (>0603) * Test time: 10 $\pm$ 1 sec.	* No remarkable damage or removal of the terminations.																
8.	Vibration Resistance	* Vibration frequency: 10~55 Hz/min. * Total amplitude: 1.5mm * Test time: 6 hrs. (Two hrs each in three mutually perpendicular directions.)  * Before initial measurement (Class II only): To apply de-aging at 150°C for 1hr then set for 24 $\pm$ 2 hrs at room temp . * Cap./DF(Q) Measurement to be made after de-aging at 150°C for 1hr then set for 24 $\pm$ 2 hrs at room temp.	* No remarkable damage. * Cap change and Q/D.F.: To meet initial spec.																
9.	Solderability	* Solder temperature: 235 $\pm$ 5°C * Dipping time: 2 $\pm$ 0.5 sec.	75% min. coverage of all metallized area.																
10.	Bending Test	* The middle part of substrate shall be pressurized by means of the pressurizing rod at a rate of about 1 mm per second until the deflection becomes : 5 mm and then the pressure shall be maintained for 5 $\pm$ 1 sec.  * Measurement to be made after keeping at room temp. for 24 $\pm$ 2 hrs..	* No remarkable damage. * Cap change : NP0: within $\pm$ 5.0% or $\pm$ 0.5pF whichever is larger. X7R: within $\pm$ 12.5% Y5V: within $\pm$ 30%  (This capacitance change means the change of capacitance under specified flexure of substrate from the capacitance measured before the test.)																
11.	Resistance to Soldering Heat	* Solder temperature: 260 $\pm$ 5°C * Dipping time: 10 $\pm$ 1 sec * Preheating: 120 to 150°C for 1 minute before immerse the capacitor in a eutectic solder.  * Before initial measurement (Class II only): To apply de-aging at 150°C for 1hr then set for 24 $\pm$ 2 hrs at room temp . * Cap. / DF(Q) / I.R. Measurement to be made after de-aging at 150°C for 1hr then set for 24 $\pm$ 2 hrs at room temp .	* No remarkable damage. * Cap change: NP0: within $\pm$ 2.5% or $\pm$ 0.25pF whichever is larger. X7R: within $\pm$ 7.5% Y5V: within $\pm$ 20% * Q/D.F., I.R. and dielectric strength: To meet initial requirements. * 25% max. leaching on each edge.																



Multilayer Ceramic Capacitors

No.	Item	Test Condition	Requirements															
12.	Temperature Cycle	<p>* Conduct the five cycles according to the temperatures and time.</p> <table border="1"> <thead> <tr> <th>Step</th><th>Temp. (°C)</th><th>Time (min.)</th></tr> </thead> <tbody> <tr> <td>1</td><td>Min. operating temp. +0/-3</td><td>30±3</td></tr> <tr> <td>2</td><td>Room temp.</td><td>2~3</td></tr> <tr> <td>3</td><td>Max. operating temp. +3/-0</td><td>30±3</td></tr> <tr> <td>4</td><td>Room temp.</td><td>2~3</td></tr> </tbody> </table> <p>* Before initial measurement (Class II only): To apply de-aging at 150°C for 1hr then set for 24±2 hrs at room temp .</p> <p>* Cap. / DF(Q) / I.R. Measurement to be made after de-aging at 150°C for 1hr then set for 24±2 hrs at room temp .</p>	Step	Temp. (°C)	Time (min.)	1	Min. operating temp. +0/-3	30±3	2	Room temp.	2~3	3	Max. operating temp. +3/-0	30±3	4	Room temp.	2~3	<p>* No remarkable damage.</p> <p>Cap change :</p> <p>NP0: within ±2.5% or ±0.25pF whichever is larger.</p> <p>X7R: within ±7.5%</p> <p>Y5V: within ±20%</p> <p>* Q/D.F., I.R. and dielectric strength: To meet initial requirements.</p>
Step	Temp. (°C)	Time (min.)																
1	Min. operating temp. +0/-3	30±3																
2	Room temp.	2~3																
3	Max. operating temp. +3/-0	30±3																
4	Room temp.	2~3																
13.	Humidity (Damp Heat) Steady State	<p>* Test temp.: 40±2°C</p> <p>* Humidity: 90~95% RH</p> <p>* Test time: 500+24/-0hrs.</p> <p>* Before initial measurement (Class II only): To apply de-aging at 150°C for 1hr then set for 24±2 hrs at room temp .</p> <p>* Cap. / DF(Q) / I.R. Measurement to be made after de-aging at 150°C for 1hr then set for 24±2 hrs at room temp .</p>	<p>* No remarkable damage.</p> <p>* Cap change: NP0: within ±5.0% or ±0.5pF whichever is larger.</p> <p>X7R: within ±12.5%</p> <p>Y5V: within ±30%</p> <p>* Q/D.F. value:</p> <p>NP0: Cap≥30pF, Q≥350; 10pF≤Cap&lt;30pF, Q≥275+2.5C</p> <p>Cap&lt;10pF; Q≥200+10C</p> <p>X7R: ≤3.0%</p> <p>Y5V: ≤7.5%</p> <p>I.R.: ≥1GΩ or RxC≥50Ω·F whichever is smaller.</p>															
14.	Humidity (Damp Heat) Load	<p>* Test temp.: 40±2°C</p> <p>* Humidity: 90~95%RH</p> <p>* Test time: 500+24/-0 hrs.</p> <p>* To apply voltage : rated voltage (Max. 500V)</p> <p>* Before initial measurement (Class II only): To apply de-aging at 150°C for 1hr then set for 24±2 hrs at room temp .</p> <p>* Cap. / DF(Q) / I.R. Measurement to be made after de-aging at 150°C for 1hr then set for 24±2 hrs at room temp .</p>	<p>* No remarkable damage.</p> <p>* Cap change: NP0: within ±7.5% or ±0.75pF whichever is larger.</p> <p>X7R: within ±12.5%</p> <p>Y5V: within ±30%</p> <p>* Q/D.F. value:</p> <p>NP0: Cap≥30pF, Q≥200; Cap&lt;30pF, Q≥100+10/3C</p> <p>X7R: ≤3.0%</p> <p>Y5V: ≤7.5%</p> <p>* I.R.: ≥500MΩ or RxC≥25Ω·F whichever is smaller.</p>															
15.	High Temperature Load (Endurance)	<p>* Test temp.:</p> <p>NP0, X7R: 125±3°C</p> <p>Y5V: 85±3°C</p> <p>* To apply voltage:</p> <p>(1) 1206/NP0 (3kV) ≥1.5pF: 100% of rated voltage.</p> <p>(2) 200V~300V: 200% of rated voltage.</p> <p>(3) 400V~450V: 120% of rated voltage.</p> <p>(4) 500V: 150% of rated voltage.</p> <p>(5) 630V~3000V: 120% of rated voltage.</p> <p>(6) 4000V: 110% of rated voltage.</p> <p>* Test time: 1000+24/-0 hrs.</p> <p>* Before initial measurement (Class II only): To apply de-aging at 150°C for 1hr then set for 24±2 hrs at room temp .</p> <p>* Cap. / DF(Q) / I.R. Measurement to be made after de-aging at 150°C for 1hr then set for 24±2 hrs at room temp .</p>	<p>* No remarkable damage.</p> <p>* Cap change: NP0: within ±3.0% or ±0.3pF whichever is larger.</p> <p>X7R: within ±12.5%</p> <p>Y5V: within ±30%</p> <p>* Q/D.F. value:</p> <p>NP0: Cap≥30pF, Q≥350</p> <p>10pF≤Cap&lt;30pF, Q≥275+2.5C</p> <p>Cap&lt;10pF, Q≥200+10C</p> <p>X7R: ≤3.0%</p> <p>Y5V: ≤7.5%</p> <p>I.R.: ≥1GΩ or RxC≥50Ω·F whichever is smaller.</p>															


Multilayer Ceramic Capacitors

## APPENDIXES

### □ Tape & reel dimensions




Size	0402	0603	0805			1206			1210		1808	1812	
Thickness	E	S, X	A	B	C, D, I	B	C, J, D	G, P	C,D,G,K	M	D, G, K	D, G, K	M, U
<b>A<sub>0</sub></b>	0.70 +/-0.20	1.05 +/-0.30	1.50 +/-0.20	1.50 +/-0.20	< 1.80	1.90 +/-0.50	< 2.00	<2.30	< 3.05	< 3.05	< 3.20	< 2.50	< 3.90
<b>B<sub>0</sub></b>	1.20 +/-0.20	1.80 +/-0.30	2.30 +/-0.20	2.30 +/-0.20	< 2.70	3.50 +/-0.50	< 3.70	< 4.00	< 3.80	< 3.80	< 4.00	< 5.30	< 5.30
<b>T</b>	$\leq 0.80$	$\leq 1.20$	$\leq 1.15$	$\leq 1.20$	$0.23$ $+/-0.1$	$\leq 1.20$	$0.23$ $+/-0.1$	$0.23$ $+/-0.1$	$0.23$ $+/-0.1$	$0.23$ $+/-0.1$	$0.23$ $+/-0.1$	$0.25$ $+/-0.1$	$0.25$ $+/-0.1$
<b>K<sub>0</sub></b>	-	-	-	-	< 2.50	-	< 2.50	< 2.50	< 1.50	< 2.50	< 3.20	< 2.50	< 2.50
<b>W</b>	8.00 +/-0.30	8.00 +/-0.30	8.00 +/-0.30	8.00 +/-0.30	8.00 +/-0.30	8.00 +/-0.30	8.00 +/-0.30	8.00 +/-0.30	8.00 +/-0.30	8.00 +/-0.30	12.00 +/-0.30	12.00 +/-0.30	12.00 +/-0.30
<b>P<sub>0</sub></b>	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10
<b>10xP<sub>0</sub></b>	40.00 +/-0.10	40.00 +/-0.20	40.00 +/-0.20	40.00 +/-0.20	40.00 +/-0.20	40.00 +/-0.20	40.00 +/-0.20	40.00 +/-0.20	40.00 +/-0.20	40.00 +/-0.20	40.00 +/-0.20	40.00 +/-0.20	40.00 +/-0.20
<b>P<sub>1</sub></b>	2.00 +/-0.05	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10	4.00 +/-0.10	8.00 +/-0.10
<b>P<sub>2</sub></b>	2.00 +/-0.05	2.00 +/-0.05	2.00 +/-0.05	2.00 +/-0.05	2.00 +/-0.05	2.00 +/-0.05	2.00 +/-0.05	2.00 +/-0.05	2.00 +/-0.05	2.00 +/-0.05	2.00 +/-0.10	2.00 +/-0.10	2.00 +/-0.10
<b>D<sub>0</sub></b>	1.50 +0.1/-0	1.50 +0.1/-0	1.50 +0.1/-0	1.50 +0.1/-0	1.50 +0.1/-0	1.50 +0.1/-0	1.50 +0.1/-0	1.50 +0.1/-0	1.50 +0.1/-0	1.50 +0.1/-0	1.50 +0.1/-0	1.50 +0.1/-0	1.50 +0.1/-0
<b>D<sub>1</sub></b>	-	-	-	-	1.00 +/-0.10	-	1.00 +/-0.10	1.00 +/-0.10	1.00 +/-0.10	1.00 +/-0.10	1.00 +/-0.10	1.50 +/-0.10	1.50 +/-0.10
<b>E</b>	1.75 +/-0.10	1.75 +/-0.10	1.75 +/-0.10	1.75 +/-0.10	1.75 +/-0.10	1.75 +/-0.10	1.75 +/-0.10	1.75 +/-0.10	1.75 +/-0.10	1.75 +/-0.10	1.75 +/-0.10	1.75 +/-0.10	1.75 +/-0.10
<b>F</b>	3.50 +/-0.05	3.50 +/-0.05	3.50 +/-0.05	3.50 +/-0.05	3.50 +/-0.05	3.50 +/-0.05	3.50 +/-0.05	3.50 +/-0.05	3.50 +/-0.05	3.50 +/-0.05	3.50 +/-0.05	5.50 +/-0.10	5.50 +/-0.10



Size	0402, 0603, 0805, 1206, 1210			1808, 1812
Reel size	7"	10"	13"	7"
<b>C</b>	13.0+0.5/-0.2	13.0+0.5/-0.2	13.0+0.5/-0.2	13.0+0.5/-0.2
<b>W<sub>1</sub></b>	8.4+1.5/-0	8.4+1.5/-0	8.4+1.5/-0	12.4+2.0/-0
<b>A</b>	178.0±1.0	250.0±1.0	330.0±1.0	178.0±1.0
<b>N</b>	60.0+1.0/-0	100.0±1.0	100±1.0	60.0+1.0/-0

## Multilayer Ceramic Capacitors


### □ Description of customer label



- a. Customer name
- b. WTC order series and item number
- c. Customer P/O
- d. Customer P/N
- e. Description of product
- f. Quantity
- g. Bar code including quantity & WTC P/N or customer
- h. WTC P/N
- i. Shipping date
- j. Order bar code including series and item numbers
- k. Serial number of label

### □ Constructions

No.	Name	NPO	X7R
①	Ceramic material	CaZrO <sub>3</sub> based	BaTiO <sub>3</sub> based
②	Inner electrode		Ni
③	Inner layer	Cu + Ag Polymer	
④	Termination	Middle layer	Ni
⑤		Outer layer	Sn



### □ Storage and handling conditions

- (1) To store products at 5 to 40°C ambient temperature and 20 to 70% related humidity conditions.
- (2) The product is recommended to be used within one year after shipment. Check solderability in case of shelf life extension is needed.

#### Cautions:

- a. The corrosive gas reacts on the terminal electrodes of capacitors, and results in the poor solderability. Do not store the capacitors in the ambience of corrosive gas (e.g., hydrogen sulfide, sulfur dioxide, chlorine, ammonia gas etc.)
- b. In corrosive atmosphere, solderability might be degraded, and silver migration might occur to cause low reliability.
- c. Due to the dewing by rapid humidity change, or the photochemical change of the terminal electrode by direct sunlight, the solderability and electrical performance may deteriorate. Do not store capacitors under direct sunlight or dewing condition. To store products on the shelf and avoid exposure to moisture.

Multilayer Ceramic Capacitors

**□ Recommended soldering conditions**

The lead-free termination MLCCs are not only to be used on SMT against lead-free solder paste, but also suitable against lead-containing solder paste. If the optimized solder joint is requested, increasing soldering time, temperature and concentration of N<sub>2</sub> within oven are recommended.




Fig. 6 Recommended reflow soldering profile for SMT process with SnAgCu series solder paste.




Fig. 7 Recommended wave soldering profile for SMT process with SnAgCu series solder.

