

PWR173024L

Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image



Our small industrial contactors of the PWR are particularly suitable for switching larger load currents.

- 1 NO contact (30 A) and 2 NO contacts (25 A)
- AgSnO Contact material
- Double contact to increase contact opening
- Direct mounting on DIN rail TS35
- With integrated status LED

General ordering data

Version	D-SERIES PWR, Relay module, Number of contacts: 1, NO contact AgSnO2, Rated control voltage: 24 V DC, Continuous current: 30 A
Order No.	1219480000
Type	PWR173024L
GTIN (EAN)	4032248998937
Qty.	10 pc(s).

Creation date December 24, 2020 9:59:03 AM CET

Catalogue status 08.12.2020 / We reserve the right to make technical changes.

PWR173024L

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	55 mm	Depth (inches)	2.165 inch
Height	34 mm	Height (inches)	1.339 inch
Net weight	119.1 g	Width	50.5 mm
Width (inches)	1.988 inch		

Temperatures

Storage temperature	-25 °C...55 °C	Operating temperature	-25 °C...55 °C
Humidity	35...85 % rel. humidity, no condensation		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Rated data UL

Certificate No. (cURus)	E312083
-------------------------	---------

Control side

Coil resistance	303 Ω \pm 10 %	Power rating	1.9 W
Pull-in/drop-out voltage, typ.	18 V / 3.6 V DC	Rated control voltage	24 V DC
Rated current DC	79.2 mA	Status indicator	Green LED

Load side

AC switching capacity (resistive), max.	8300 VA
Continuous current	Current 30 A
DC switching capacity (resistive), max.	720 W @ 24 V
Inrush current	150 A / 50 ms
Max. switching frequency at rated load	0.1 Hz
Max. switching voltage, AC	277 V
Min. switching power	100 mA @ 12 V
Rated switching voltage	Voltage type AC max. 277
Switch-off delay	< 10 ms
Switch-on delay	< 20 ms

Contact data

Contact type	1 NO contact (AgSnO ₂)	Contact resistance	≤ 50 m Ω
--------------	------------------------------------	--------------------	-----------------

General data

Rail	TS 35	Test button	No
Mechanical switch position indicator	No	Colour	beige

PWR173024L

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Insulation coordination

Creepage and clearance distance input – output	≥ 5.5 mm	Dielectric strength of open contact	2 kV _{eff} / 1 min
Dielectric strength, Input/Output	4 kV _{eff} / 1 min	Impulse withstand voltage	6 kV (1.2/50 μs)
Insulating material group	IIIa	Pollution severity	3
Protection degree	IP10	Rated voltage	250 V
Surge voltage category	III		

Further details of approvals / standards

Standards	IEC 61810-1, EN 60664-1:2007, EN 61000-6-2:2005, EN 61000-6-4:2007 + A1:2011, UL 508	Certificate No. (cURus)	E312083
-----------	--	-------------------------	---------

Connection data (control side)

Wire connection method (control side)	Screw connection	Min. rated connection clamping range (control side)	0.5 mm ²
Max. rated connection clamping range (control side)	2.5 mm ²	Min. tightening torque (control side)	0.5 Nm
Max. tightening torque (control side)	1.2 Nm	Blade size (control side)	Gr. PH2

Connection data (load side)

Wire connection method (load side)	Screw connection	Min. rated connection clamping range (load side)	0.5 mm ²
Max. rated connection clamping range (load side)	4 mm ²	Min. tightening torque (load side)	0.5 Nm
Max. tightening torque (load side)	1.2 Nm	Blade size (load side)	Gr. PH2

Classifications

ETIM 6.0	EC001437	ETIM 7.0	EC001437
ECLASS 9.0	27-37-16-01	ECLASS 9.1	27-37-16-01
ECLASS 10.0	27-37-16-01	ECLASS 11.0	27-37-16-01

Approvals

Approvals



ROHS	Conform
UL File Number Search	E312083

Downloads

Approval/Certificate/Document of Conformity	EU Konformitätserklärung / EU Declaration of Conformity
Brochure/Catalogue	CAT 4.2 ELECTR 18/19 EN
Engineering Data	EPLAN, WSCAD


PWR173024L

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany


www.weidmueller.com

Drawings

Wiring diagram




Graph




DC load limit curve
Resistive load

Graph




Electrical service life
Resistive load

Graph



DC operational voltage range

Dimensional drawing



Data sheet


PWR173024L

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Drawings

Miscellaneous



Type codes