


**W-Series  
WFS 4 30-70V DB**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image****Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	WFS 4 30-70V DB
Order No.	<a href="#">2561980000</a>
Version	W-Series, Fuse terminal, Rated cross-section: 4 mm <sup>2</sup> , Screw connection
GTIN (EAN)	4050118570458
Qty.	50 pc(s).

**W-Series**  
**WFS 4 30-70V DB**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	6.1 mm	Width (inches)	0.24 inch
Height	62.5 mm	Height (inches)	2.461 inch
Depth	75 mm	Depth (inches)	2.953 inch
Depth including DIN rail	75.5 mm	Net weight	17.686 g

**Temperatures**

Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C
----------------------------------	--------	----------------------------------	--------

**Material data**

Material	Wemid	Colour code	dark beige
UL 94 flammability rating	V-0		

**System specifications**

Version	Screw connection, Fuse isolator	Tightening torque (clamping screw for copper conductors)	0.5...0.6 Nm
End cover plate required	Yes	Number of potentials	1
Number of levels	1	No. of clamping points per level	2
Number of potentials per tier	1	Levels cross-connected internally	No
PE connection	No	Rail	TS 35
N-function	No	PE function	No
PEN function	No		

**2 clampable conductors (H05V/H07V) with equal cross-section (rated connection)**

Wire connection cross section, finely stranded, two clampable wires, min.	0.5 mm <sup>2</sup>	Wire cross-section, finely stranded, two clampable wires, max.	1.5 mm <sup>2</sup>
Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, 2 clampable wires, min.	0.5 mm <sup>2</sup>	Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, 2 clampable wires, max.	1.5 mm <sup>2</sup>

**Additional technical data**

Open sides	right	Type of mounting	Snap-on
------------	-------	------------------	---------

**W-Series**  
**WFS 4 30-70V DB**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Conductors for clamping (rated connection)**

Blade size	0.6 x 3.5 mm	Clamping range, max.	6 mm <sup>2</sup>
Clamping range, min.	0.22 mm <sup>2</sup>	Clamping screw	M 3
Connection cross-section, stranded, max.	6 mm <sup>2</sup>	Connection cross-section, stranded, min.	1.5 mm <sup>2</sup>
Connection direction	on side	Gauge to IEC 60947-1	A4
Number of connections	2	Stripping length	13 mm
Tightening torque, max.	0.6 Nm	Tightening torque, min.	0.5 Nm
Torque level with DMS electric screwdriver	2	Type of connection	Screw connection
Wire connection cross section AWG, max.	AWG 10	Wire connection cross section AWG, min.	AWG 26
Wire connection cross section, finely stranded, max.	4 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	4 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	4 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded, min.	0.5 mm <sup>2</sup>
Wire connection cross-section, solid core, max.	6 mm <sup>2</sup>	Wire connection cross-section, solid core, min.	0.5 mm <sup>2</sup>

**Display element**

Current	6.3 A	Type of voltage for indicator	AC/DC
---------	-------	-------------------------------	-------

**Fuse terminals**

Cartridge fuse	G-Si. 5 x 20	Current	6.3 A
Display	LED	Fuse holder (cartridge holder)	Pivoting
Operating voltage, max.	70 V	Permitted power loss for fuse with semiconductor protection	
Power loss, 1-pole ; 2-pole ; 3-pole		Type of voltage for indicator	AC/DC

**Rating data**

Rated cross-section	4 mm <sup>2</sup>	Rated voltage	70 V
Rated voltage to adjoining terminal	400 V	Rated current	6.3 A
Current at maximum wires	6.3 A	Standards	IEC 60947-7-3
Volume resistance according to IEC 60947-7-x	1 mΩ	Rated impulse withstand voltage	6 kV
Pollution severity	3		

**UL rating data**

Certificate No. (cURus)	E60693	Conductor size Factory wiring max. (cURus)	10 AWG
Conductor size Factory wiring min. (cURus)	22 AWG	Conductor size Field wiring max. (cURus)	10 AWG
Conductor size Field wiring min. (cURus)	22 AWG	Current size B (cURus)	10 A
Current size D (cURus)	10 A	Voltage size B (cURus)	300 V
Voltage size D (cURus)	300 V		

**Data sheet****W-Series**  
**WFS 4 30-70V DB****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com**Technical data****Classifications**

ETIM 6.0	EC000899	eClass 6.2	27-14-11-16
eClass 9.0	27-14-11-16	eClass 9.1	27-14-11-16

**Approvals**

Approvals

**Downloads**


Approval/Certificate/Document of Conformity	<a href="#">Declaration of Conformity</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**W-Series**  
**WFS 4 30-70V DB**


**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



**W-Series**  
**WFS 4 30-70V DB**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**
**Custom printing**


The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
DEK 5/6 PLUS MC SDR	<a href="#">1038650000</a>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, To customer specification	4032248767908	200 pc(s).
DEK 5/6 MC SDR	<a href="#">1609830000</a>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, To customer specification	4008190456603	200 pc(s).

**Marking Holder**

**Spring connection with tension clamp Technology**


Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
BZT 1 WS 10/5	<a href="#">1805490000</a>	Accessories, Marker holder	4032248270231	100 pc(s).
BZT 1 ZA WS 10/5	<a href="#">1805520000</a>	Accessories, Marker holder	4032248270248	100 pc(s).

**W-Series**  
**WFS 4 30-70V DB**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories****Blank**

The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
DEK 5/6 MC NE BL	<a href="#">1238290000</a>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, blue	4050118267327	1,000 pc(s).
DEK 5/6 MC NE GR	<a href="#">1238330000</a>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, grey	4050118323306	1,000 pc(s).
DEK 5/6 MC NE GE	<a href="#">1238280000</a>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, yellow	4050118038750	1,000 pc(s).
DEK 5/6 MC NE OR	<a href="#">1912090000</a>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, orange	4032248540525	1,000 pc(s).
DEK 5/6 MC NE BR	<a href="#">1454900000</a>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, brown	4050118323313	1,000 pc(s).
DEK 5/6 MC NE WS	<a href="#">1609820000</a>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, white	4008190203436	1,000 pc(s).
DEK 5/6 MC NE GN	<a href="#">1238310000</a>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, green	4050118271812	1,000 pc(s).

**W-Series  
WFS 4 30-70V DB**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**
**End plates**


**Klippon® Connect with clamping yoke Technology**  
 The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
WAP 2.5-10 BL	<a href="#">1050080000</a>	W-Series, End plate	4008190136611	50 pc(s).
WAP 2.5-10	<a href="#">1050000000</a>	W-Series, End plate	4008190103149	50 pc(s).
WAP 2.5-10 RT	<a href="#">1050040000</a>	W-Series, End plate	4008190406783	50 pc(s).
WAP 2.5-10 GR	<a href="#">1050050000</a>	W-Series, End plate	4008190455484	50 pc(s).
WAP 2.5-10 OR	<a href="#">1050060000</a>	W-Series, End plate	4008190406769	50 pc(s).
WAP 2.5-10 WS	<a href="#">1050090000</a>	W-Series, End plate	4008190406790	50 pc(s).
WAP 2.5-10 VI	<a href="#">1072210000</a>	W-Series, End plate	4008190455460	50 pc(s).
WAP 2.5-10 GN	<a href="#">1072200000</a>	W-Series, End plate	4008190455491	50 pc(s).
WAP 2.5-10 GE	<a href="#">1050020000</a>	W-Series, End plate	4008190406776	50 pc(s).
WAP 2.5-10 BR	<a href="#">1050070000</a>	W-Series, End plate	4008190455507	50 pc(s).
WAP 2.5-10 SW	<a href="#">1050010000</a>	W-Series, End plate	4008190406806	50 pc(s).

**Markers**


Extensive range of accessories for the FieldPower® boxes.  
 Cable seals, plug-in connectors, locking elements and much more.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
WS 12/6 MC NE WS	<a href="#">1609900000</a>	WS, Terminal marker, 12 x 6 mm, Pitch in mm (P): 6.00	4008190203467	600 pc(s).



**W-Series  
WFS 4 30-70V DB**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**

	Weidmueller, Allen-Bradley, white
WS 12/6 MC <a href="#">1773551693</a> NE BL	WS, Terminal marker, 12 x 4032248143269 600 pc(s). 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, blue
WS 12/6 MC <a href="#">1773551688</a> NE GN	WS, Terminal marker, 12 x 4032248141944 600 pc(s). 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, green

**End brackets**



**Klippon® Connect with clamping yoke Technology**  
 The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
WEW 35/2 SW	<a href="#">1061210000</a>	W-Series, End bracket	4032248136278	100 pc(s).
WEW 35/2 VO GF SW	<a href="#">1479000000</a>	W-Series, End bracket	4050118286779	100 pc(s).
WEW 35/2	<a href="#">1061200000</a>	W-Series, End bracket	4008190030230	100 pc(s).
WEW 35/2 GR 7042	<a href="#">1859200000</a>	W-Series, End bracket	4032248411658	100 pc(s).

## W-Series WFS 4 30-70V DB

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Accessories

### Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
WS 12/6 MC NE BR	<a href="#">1773551692</a>	WS, Terminal marker, 12 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, brown	4032248143252	600 pc(s).
WS 12/6 MC NE GE	<a href="#">1773551687</a>	WS, Terminal marker, 12 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, yellow	4032248141937	600 pc(s).
WS 12/6 PLUS MC NE WS	<a href="#">1927530000</a>	WS, Terminal marker, 12 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, white	4032248574209	600 pc(s).
WS 12/6 MC NE OR	<a href="#">1773551690</a>	WS, Terminal marker, 12 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, orange	4032248143245	600 pc(s).
WS 12/6 MC NE VI	<a href="#">1773551689</a>	WS, Terminal marker, 12 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, violet	4032248143238	600 pc(s).
WS 12/6 MC NE RT	<a href="#">1773551686</a>	WS, Terminal marker, 12 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, red	4032248141920	600 pc(s).

## W-Series WFS 4 30-70V DB

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Accessories

### Custom printing



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
WS 10/6 MC M SDR	<a href="#">1818410000</a>	WS, Terminal marker, 10 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, To customer specification	4032248310883	120 pc(s).
WS 10/6 MC SDR	<a href="#">1828460000</a>	WS, Terminal marker, 10 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, To customer specification	4032248367399	120 pc(s).
WS 10/6 M PLUS MC SDR	<a href="#">2007780000</a>	WS, Terminal marker, 10 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, To customer specification	4050118393187	120 pc(s).
WS 10/6 PLUS MC SDR	<a href="#">1046330000</a>	WS, Terminal marker, 10 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, To customer specification	4032248782031	120 pc(s).

**W-Series  
WFS 4 30-70V DB**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**

**WS 12/6**



**WS/ DEK**

MultiMark DEK/WS connector markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.


**Your benefits with MultiMark**

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
WS 12/6 MM	<a href="#">2007200000</a>	WS, Terminal marker, 12 x 6 mm, Weidmueller, white	4050118391886	600 pc(s).

**Blank**



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
WS 8/6 PLUS	<a href="#">1951880000</a>	WS, Terminal marker, 8 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, white	4032248632114	600 pc(s).

**W-Series  
WFS 4 30-70V DB**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**

**WS 8/6**



**WS/ DEK**

MultiMark DEK/WS connector markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

**Your benefits with MultiMark**

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
WS 8/6 MM	<a href="#">2007160000</a>	WS, Terminal marker, 8 x 6	4050118391879	600 pc(s).
WS		mm, Weidmueller, white		

**Custom printing**



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
WS 12/6 MC	<a href="#">1609910000</a>	WS, Terminal marker, 12 x	4008190456658	120 pc(s).
SDR		6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, To customer specification		

**W-Series**  
**WFS 4 30-70V DB**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**

WS 12/6 [1927540000](#)  
 PLUS MC SDR

WS, Terminal marker, 12 x 4032248574711 120 pc(s).  
 6 mm, Pitch in mm (P): 6.00  
 Weidmueller, Allen-Bradley,  
 To customer specification

**ZQV 4N**

**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

**General ordering data**

Type	Order No.	GTIN (EAN)	Qty.
ZQV 4N/30	<a href="#">2561600000</a>	4050118569964	5 pc(s).
RD			
ZQV 4N/9 RD	<a href="#">2460750000</a>	4050118476170	20 pc(s).
ZQV 4N/10	<a href="#">1528230000</a>	4050118333138	20 pc(s).
BL			
ZQV 4N/30	<a href="#">2561580000</a>	4050118570113	5 pc(s).
ZQV 4N/6 BL	<a href="#">1528170000</a>	4050118332926	20 pc(s).
ZQV 4N/8	<a href="#">1528030000</a>	4050118332841	20 pc(s).
ZQV 4N/5	<a href="#">1527980000</a>	4050118332759	60 pc(s).
ZQV 4N/4	<a href="#">1527970000</a>	4050118332889	60 pc(s).
ZQV 4N/50	<a href="#">1528240000</a>	4050118333121	5 pc(s).
BL			
ZQV 4N/3 RD	<a href="#">2460810000</a>	4050118476231	60 pc(s).
ZQV 4N/6	<a href="#">1527990000</a>	4050118332919	20 pc(s).
ZQV 4N/7 BL	<a href="#">1528180000</a>	4050118333114	20 pc(s).
ZQV 4N/10	<a href="#">2460740000</a>	4050118476163	20 pc(s).
RD			
ZQV 4N/5 BL	<a href="#">1528140000</a>	4050118333015	60 pc(s).
ZQV 4N/10	<a href="#">1528090000</a>	4050118332896	20 pc(s).
ZQV 4N/2 BL	<a href="#">1528040000</a>	4050118332773	60 pc(s).
ZQV 4N/7 RD	<a href="#">2460770000</a>	4050118476194	20 pc(s).
ZQV 4N/2 RD	<a href="#">2460450000</a>	4050118476149	60 pc(s).
ZQV 4N/4 RD	<a href="#">2460800000</a>	4050118476224	60 pc(s).
ZQV 4N/30	<a href="#">2561610000</a>	4050118569971	5 pc(s).
BL			
ZQV 4N/7	<a href="#">1528020000</a>	4050118332780	20 pc(s).
ZQV 4N/9	<a href="#">1528070000</a>	4050118332797	20 pc(s).
ZQV 4N/5 RD	<a href="#">2460790000</a>	4050118476217	60 pc(s).
ZQV 4N/50	<a href="#">2460730000</a>	4050118476156	5 pc(s).
RD			
ZQV 4N/32	<a href="#">2561670000</a>	4050118570175	5 pc(s).
ZQV 4N/50	<a href="#">1528130000</a>	4050118332902	5 pc(s).
ZQV 4N/3	<a href="#">1527940000</a>	4050118332865	60 pc(s).
ZQV 4N/6 RD	<a href="#">2460780000</a>	4050118476200	20 pc(s).

Creation date April 9, 2019 11:34:58 AM CEST

## W-Series WFS 4 30-70V DB

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Accessories

ZQV 4N/9 BL <a href="#">1528220000</a>	4050118333107	20 pc(s).
ZQV 4N/3 BL <a href="#">1528080000</a>	4050118333008	60 pc(s).
ZQV 4N/8 RD <a href="#">2460760000</a>	4050118476187	20 pc(s).
ZQV 4N/2 <a href="#">1527930000</a>	4050118332766	60 pc(s).
ZQV 4N/4 BL <a href="#">1528120000</a>	4050118332872	60 pc(s).
ZQV 4N/8 BL <a href="#">1528190000</a>	4050118332858	20 pc(s).

## Plus



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
DEK 5/6 PLUS	<a href="#">1011320000</a>	Dekafix, Terminal marker,	4032248717644	1,000 pc(s).
MC NE WS		5 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, white		

**W-Series  
WFS 4 30-70V DB**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**

**DEK 5/6**



**WS/ DEK**

MultiMark DEK/WS connector markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

**Your benefits with MultiMark**

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
DEK 5/6 MM	<a href="#">2007120000</a>	Dekafix, Terminal marker, 5	4050118392104	600 pc(s).
WS		x 6 mm, Weidmueller, white		

**Blank**



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
WS 10/6 MC	<a href="#">1828450000</a>	WS, Terminal marker, 10 x	4032248350513	600 pc(s).
NE WS		6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, white		



## W-Series WFS 4 30-70V DB

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Accessories

WS 10/6 M MC NE WS	<a href="#">1818400000</a>	WS, Terminal marker, 10 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, white	4032248310876 600 pc(s).
WS 10/6 MC M NE GE	<a href="#">1917430000</a>	WS, Terminal marker, 10 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, yellow	4032248551637 600 pc(s).
WS 10/6 PLUS MC NE WS	<a href="#">1046390000</a>	WS, Terminal marker, 10 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, white	4032248782109 600 pc(s).
WS 10/6 MC M NE RT	<a href="#">1917440000</a>	WS, Terminal marker, 10 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, red	4032248551644 600 pc(s).
WS 10/6 MC M NE GN	<a href="#">1917420000</a>	WS, Terminal marker, 10 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, green	4032248551620 600 pc(s).
WS 10/6 M PLUS MC NE WS	<a href="#">2003780000</a>	WS, Terminal marker, 10 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, white	4050118424461 600 pc(s).
WS 10/6 MC M NE BL	<a href="#">1069080000</a>	WS, Terminal marker, 10 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, Allen-Bradley, blue	4032248824618 600 pc(s).

## Custom printing



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
WS 8/6 PLUS MC SDR	<a href="#">1038820000</a>	WS, Terminal marker, 8 x 6 mm, Pitch in mm (P): 6.00	4032248768073	120 pc(s).

**Data sheet**

**W-Series**  
**WFS 4 30-70V DB**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Accessories**

Weidmueller, To customer  
specification