

# Product datasheet

Specifications



## Modicon Managed Switch - 8 ports for copper + 2 ports for fiber optic single-mode - Harsh

MCSESM103F2CS0H

### Main

<b>Range of product</b>	Modicon
<b>Product or component type</b>	Ethernet TCP/IP managed switch
<b>Product specific application</b>	For severe environments
<b>Concept</b>	Transparent Ready
<b>Communication port protocol</b>	Ethernet TCP/IP SSH HTTP HTTPS SNMP RS232 SFTP SCP LLDP Telnet SNTP
<b>Port Ethernet</b>	100BASE-FX - 2 port(s) fiber optic 10/100BASE-TX - 8 port(s) copper cable
<b>Maximum number of switches in cascade</b>	Unlimited
<b>Cybersecurity</b>	Port hardening IP-based port security MAC-based port security Port-based access control Role-based access control RADIUS assignment HTTPS DoS prevention VLAN-based ACL Audit trail SNMP logging Pre-login banner

### Complementary

<b>Integrated connection type</b>	Duplex SC fiber optic Shielded RJ45 copper cable
<b>Transmission support medium</b>	Single mode optical fiber for fiber optic Twisted shielded pairs cable CAT 5E for copper cable
<b>Maximum cable distance between devices</b>	100 m copper cable
<b>Optic fiber length</b>	32.5 km 9/125 µm
<b>Attenuation</b>	0...16 dB (9/125 µm)
<b>Ethernet service</b>	Configuration via web server VLAN Multicast filtering Data stream control IGMP Snooping SNMP-Traps and SYSLOG

<b>communication service</b>	TFTP Quality of Service (QoS) Port monitoring Port mirroring Address conflict detection
<b>Diagnostics run time</b>	Signal contact Self test MAC notification
<b>Maximum number of switches in a ring</b>	50
<b>Redundancy</b>	HiPER ring RSTP Link aggregation Link backup Redundant network coupling MRP
<b>[Us] rated supply voltage</b>	12...24 V
<b>Supply voltage limits</b>	9.6...32 V DC SELV
<b>Power consumption in W</b>	8 W
<b>Electrical connection</b>	Removable connector 6 ways power supply
<b>mounting support</b>	35 mm symmetrical DIN rail
<b>marking</b>	CE CULus RCM
<b>Function available</b>	Security status Alarms (Traps) System information Report
<b>Local signalling</b>	1 dual colour LED (green/yellow) for P1 P2 power supplies 1 dual colour LED (green/red) for device status 1 dual colour LED (green/yellow) for memory key status 1 dual colour LED (green/yellow) for channel diagnostic
<b>Alarm output</b>	1 voltfree contact 1 A
<b>Alarm function</b>	Power supply fault Data link status Switch fault Temperature threshold Redundancy ring fault Incorrect configuration External memory removed
<b>Ethernet cabling system</b>	TF switches
<b>Width</b>	73 mm
<b>Height</b>	142.8 mm
<b>Depth</b>	117.6 mm
<b>Net weight</b>	0.57 kg

## Environment

<b>Ambient air temperature for operation</b>	-40...70 °C
<b>Relative humidity</b>	1...95 % non-condensing
<b>IP degree of protection</b>	IP30
<b>protective treatment</b>	Conformal coating
<b>Directives</b>	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility

---

<b>Standards</b>	UL 61010-2-201 EN/IEC 61131-2 EN/IEC 62368-1
------------------	--

---

<b>Product certifications</b>	CE UL RCM DNV ATEX
-------------------------------	--------------------------------

---

## Packing Units

---

<b>Unit Type of Package 1</b>	PCE
-------------------------------	-----

---

<b>Number of Units in Package 1</b>	1
-------------------------------------	---

---

<b>Package 1 Height</b>	16.0 cm
-------------------------	---------

---

<b>Package 1 Width</b>	13.0 cm
------------------------	---------

---

<b>Package 1 Length</b>	23.5 cm
-------------------------	---------

---

<b>Package 1 Weight</b>	570.0 g
-------------------------	---------

---

## Contractual warranty

---

<b>Warranty</b>	18 months
-----------------	-----------

---

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

Mercury Free

RoHS Exemption Information Yes

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu RoHS Directive Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation [China RoHS declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile [End of Life Information](#)

Dimensions Drawings

Dimensions

---




Image of product / Alternate images

Alternative

---

