


- Endurance: 6.0V 65°C 1000 hours
- High capacitance and small size
- Low ESR
- Long cycle life
- UL recognized
- RoHS compliant



## Specifications

Part Number	EC6R015508020M	
Rated Voltage	V	6.0
Capacitance	F	1.5
ESR, 1kHz	mΩ	90
ESR, DC	mΩ	150
LC(72hr)	mA	0.015
Specific Energy	Wh/kg	2.50
Specific Power	kW/kg	20.00
Max. Peak Current	A	3.67
Weight	g	3.00

- Capacitance and Equivalent Series Resistance (ESR) measured according to IEC62391-1 at +25°C, with current in milliamps (mA) = 10°C
- Leakage Current at 25°C after 72 hour charge and hold
- Specific Energy (Wh/kg) =  $(\frac{1}{2} \cdot C \cdot V^2 / 3600) / \text{weight}$
- Specific Power (kW/kg) =  $(V^2 / 4 \cdot \text{ESR}) / \text{weight}$
- Max Peak Current in Amps (A), 1 second discharge from rated voltage to half rated voltage =  $(\frac{1}{2} \cdot C \cdot V) / (1 + \text{ESR} \cdot C)$

## Characteristics

Operating Temperature Range	-40 ~ +65°C	
Rated Voltage	6.0 VDC	
Capacitance Tolerance	-10% ~ +20%	
Temperature Characteristics	Capacitance change	Within ±5% of initial value at +25°C
	Internal resistance	Within ±50% of initial value at +25°C
Endurance	Duration	1000 hours
	Capacitance change	Within ≤30% of initial value
	Internal resistance	Within ≤100% of initial specified value
Shelf Life	After 1000 hours no load test same as endurance	
Lifetime at RT <sup>(1)</sup>	10 years	
Cycle Life(25°C) <sup>(2)</sup>	500,000 cycles	

(1)  $|\Delta C| \leq 30\%$  of initial value and  $|\text{ESR}| \leq 100\%$  of initial specified value.

(2) Cycle : between rated voltage and half rated voltage under constant current at 25°C.

## Dimensions Unit:mm

L	22.0	
W	16.0	
D	8.5	
P	Type-C	4.9
	Type-S	12.0
	Type-H	8.5
Φd	0.6	
Single Cell Size	ΦD x L	
	8 x 20	

