


Vishay High Power Products

Schottky Rectifier, 2 x 20 A



PRODUCT SUMMARY				
I _{F(AV)} 2 x 20 A				
V _R 80/100 V				

FEATURES

- 175 °C T_J operation
- Center tap configuration
- · Low forward voltage drop
- High purity, high temperature epoxy encapsulation for enhanced mechanical strength and moisture resistance
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability
- Designed and qualified for AEC-Q101 level

DESCRIPTION

This center tap Schottky rectifier series has been optimized for low reverse leakage at high temperature. The proprietary barrier technology allows for reliable operation up to 175 °C junction temperature. Typical applications are in switching power supplies, freewheeling diodes, and reverse battery protection.

MAJOR RATINGS AND CHARACTERISTICS					
SYMBOL	CHARACTERISTICS	CHARACTERISTICS VALUES			
I _{F(AV)}	Rectangular waveform	40	А		
V _{RRM}		80/100	V		
I _{FSM}	$t_p = 5 \mu s sine$	850	Α		
V _F	20 Apk, T _J = 125 °C (per leg)	0.67	V		
T _J	Range	- 55 to 175	°C		

VOLTAGE RATINGS				
PARAMETER SYMBOL		43CTQ080S 43CTQ080-1	43CTQ100S 43CTQ100-1	UNITS
Maximum DC reverse voltage	V_R	80	100	V
Maximum working peak reverse voltage	V_{RWM}	60	100	V

ABSOLUTE MAXIMUM RATINGS					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum average per leg		50 % duty cycle at T_C = 135 °C, rectangular waveform		20	
See fig. 5 per device	I _{F(AV)}			40	A
Maximum peak one cycle non-repetitive surge current per leg	1	5 μs sine or 3 μs rect. pulse	Following any rated load condition and with rated V _{RRM} applied	850	
See fig. 7	I _{FSM}	10 ms sine or 6 ms rect. pulse		275	
Non-repetitive avalanche energy per leg	E _{AS}	$T_J = 25 ^{\circ}\text{C}$, $I_{AS} = 0.50 \text{A}$, $L = 60 \text{mH}$		7.50	mJ
Repetitive avalanche current per leg	I _{AR}	Current decaying linearly to zero in 1 μ s Frequency limited by T _J maximum V _A = 1.5 x V _R typical		0.50	Α

Document Number: 93346 Revision: 04-Mar-09

43CTQ...S, 43CTQ...-1

Vishay High Power Products

Schottky Rectifier, 2 x 20 A



ELECTRICAL SPECIFICATIONS					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum forward voltage drop per leg See fig. 1	V _{FM} ⁽¹⁾	20 A	T _J = 25 °C	0.81	
		40 A		0.98	V
		20 A	T _J = 125 °C	0.67	
		40 A		0.81	
Maximum reverse leakage current per leg	I _{RM} ⁽¹⁾	T _J = 25 °C	V Datad V	1	A
See fig. 2	IRM ('')	$V_R = Rated V_R$	11	mA	
Threshold voltage	V _{F(TO)}	$T_{J} = T_{J}$ maximum		0.71	V
Forward slope resistance	r _t			0.43	mΩ
Maximum junction capacitance per leg	C _T	$V_R = 5 V_{DC}$ (test signal range 100 kHz to 1 MHz) 25 °C		1480	pF
Typical series inductance per leg	L _S	Measured lead to lead 5 mm from package body 8.0		nH	
Maximum voltage rate of change	dV/dt	Rated V _R 10 000		V/µs	

Note

 $^{^{(1)}\,}$ Pulse width < 300 $\mu s,$ duty cycle < 2 %

THERMAL - MECHANICAL SPECIFICATIONS					
PARAMETER		SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction and storage temperature range		T _J , T _{Stg}		- 55 to 175	°C
Maximum thermal resistance, junction to case per leg		D	DC operation	2.0	
Maximum thermal resistance, junction to case per package		R_{thJC}		1.0	°C/W
Typical thermal resistance, case to heatsink		R _{thCS}	R _{thCS} Mounting surface, smooth and greased (Only for TO-220)		
				2	g
Approximate weight				0.07	oz.
Mounting torque	minimum			6 (5)	kgf · cm
Mounting torque -	maximum			12 (10)	(lbf · in)
Marking device		Case style D ² PAK Case style TO-262	43CTQ080S		
			43CTQ100S		
			43CTQ080-1		
				43CTQ100-1	



Schottky Rectifier, 2 x 20 A

Vishay High Power Products




Fig. 1 - Maximum Forward Voltage Drop Characteristics (Per Leg)




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage (Per Leg)




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage (Per Leg)





Fig. 4 - Maximum Thermal Impedance Z_{thJC} Characteristics (Per Leg)

Vishay High Power Products


Schottky Rectifier, 2 x 20 A





I_{F(AV)} - Average Forward Current (A)

Fig. 5 - Maximum Allowable Case Temperature vs. Average Forward Current (Per Leg)



I_{F(AV)} - Average Forward Current (A)

Fig. 6 - Forward Power Loss Characteristics (Per Leg)




Fig. 7 - Maximum Non-Repetitive Surge Current (Per Leg)




Fig. 8Unclamped Inductive Test Circuit

Note

 $^{(1)}$ Formula used: T_C = T_J - (Pd + Pd_{REV}) x R_{thJC}; Pd = Forward power loss = I_{F(AV)} x V_{FM} at (I_{F(AV)}/D) (see fig. 6); Pd_{REV} = Inverse power loss = V_{R1} x I_R (1 - D); I_R at V_{R1} = 10 V




Schottky Rectifier, 2 x 20 A

Vishay High Power Products

ORDERING INFORMATION TABLE

Device code



1 - Current rating (40 A)

2 - Circuit configuration:

C = Common cathode

3 - T = TO-220

4 - Schottky "Q" series

5 - Voltage ratings — 080 = 80 V 100 = 100 V

6 - • S = D²PAK

• -1 = TO-262

7 - • None = Tube (50 pieces)

• TRL = Tape and reel (left oriented - for D²PAK only)

• TRR = Tape and reel (right oriented - for D²PAK only)

8 - • None = Standard production

• PbF = Lead (Pb)-free

LINKS TO RELATED DOCUMENTS				
Dimensions www.vishay.com/doc?95014				
Part marking information	www.vishay.com/doc?95008			
Packaging information	www.vishay.com/doc?95032			
SPICE model	www.vishay.com/doc?95065			



Vishay

Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Revision: 18-Jul-08

Document Number: 91000 www.vishay.com