
SPECIFICATIONS

RoHS

Model Number: CR1225HA2BMT Part Number:17002089A COMAIR ROTRON

Mechanical Drawing:



Motor:

Normal Voltage	= 220/240 VAC
Operating Voltage Range	= 198~264VAC
Operating Frequency	= 50/60Hz
Rated Current	= 0.08/0.07A
Input Power	= 15/14Watt
Average Speed	= 2100/2200RPM
Bearings	= Ball
Airflow	= 60/63CFM
(Measuring at zero static pressure)	
Static Pressure	= 0.15/0.16'' H ₂ O
(Measuring at zero air flow)	
Noise Level	$= 38 \mathrm{dB}(\mathrm{A})$
Net Weight	= 320 gram.

Construction:

Venturi: High quality magnesium alloy die-casting frame with ED coating and powder coating, Black. Propeller: Magnesium alloy ED coating and painting.

Life Expectancy:

This fan is designed for continuous duty life of 50,000 hours at 40° C.

Additional Features:

Version: 00

Sep 01, 2023

Insulation Resistance: $100M\Omega$ or more at 500 V megger. Dielectric strength: 2 seconds at 1800 VAC/ 50-60 Hz. Thermal Shock: Test per MIL-STD-202F, method 107G, condition D.

Operating Temperature: -10°C to 70°C Storage Temperature: -40°C to 85°C

Termination: 0.120" Wide Terminals

Agency Approvals: UL, CE



