

			5 j							6	
8	14.99	11.09	5.85	55.07	13.31	1.50	1.0	2.76	3.05	17.35	
2	14.99	11.21	6.05	55.07	13.31	1.10	0.8	2.76	2.85	17.44	
5	12.17	11.09	5.85	57.45	10.46	1.50	1.0	2.76	3.05	17.35	
	12.17	11.21	6.05 5.85	57.45 41.02	10.46 10.46	1.10	0.8 0.8	2.76	2.85	17.44 17.35	
,	12.17	11.21	6.05	41.02	10.46	1.10	0.8	2.76	2.85	17.44	
;	12.17	10.99	5.85	27.25	10.46	1.10	0.8	2.74	2.85	17.35	
′	12.17	11.21	6.05	27.25	10.46	1.10	0.8	2.74	2.85	17.44	
5	12.17	10.99	5.85	19.02	10.46	1.10	0.8	2.74	2.85	17.35	
/ >=	12.17	11.21	6.05	19.02	10.46	1.10	0.8	2.74	2.85	17.44	
$25 \begin{bmatrix} +0.76 \\ -0 \end{bmatrix} F MAX \begin{vmatrix} +0.15 \\ -0 \end{bmatrix} + 0.51 \begin{vmatrix} +0.51 \\ -0 \end{vmatrix} + 0.51 \begin{vmatrix} +0.51 \\ -0 \end{vmatrix} \times 10^{-22} M \pm 0.06 NMAX PMAX$											
OF MALE AND OUTSIDE DIM. OF THE FEMALE CONNECTOR.											
ORDERING INFORMATION											
5	0 25	5 P	Ļ	<u>х т</u>	Х	XXX	LF				٨
									AD FR	_	<u> </u>
SPECIAL CODES											
X-ON MALE CONNECTORS ONLY											
								SHELL	PLATI	NG	
BLANK-ZINC PLTG.											
T-STD. TIN/Zinc Cr3 PLTG.											
								OP	TIONS	-2	
						BLANK	-STD. V	V/O ACC	ESSOR	IES	
OPTIONAL											
L-SUPPLIED W/O CONTACTS (OBLIGATORY)											
SPECIFICATIONS											
: TIN/CADMIUM/ZINC PLATED STEEL											В
: SELF EXTINGUISHING THERMOPLASTIC- TO UL CLASS 94 V0											
THE HOUSING WILL WITHSTAND EXPOSURE TO 260-265°C											
IF WE USE PROTECTIVE ADHESIVE (type Kapton or Teflon)											
OR PROTECTIVE METALLIC DEVICE : Ø1 MM.											
: COPPER ALLOY											
: GOLD / GXT OVER NICKEL (ACTIVE ZONE) : TIN OVER NICKEL (TERMINATION ZONE)											
: 2μ MIN.MATTE TIN TOP OVER 1.27 μ MIN.NICKEL UNDER PLATE(ON TERMINATION ZONE)											
:		1 MIN.NIC		DER PL	ATE(UN	IERMINA	TION ZO	INE)			
:	5 A I	PER CON									
:	≼10m										
:	-	Ο MΩ IN V.r.m.s	AMBIEN	IT CONL	IIIONS.						
:	: 200 MATINGS (CODE 64)										
:	21 DA			04/00							
:	: AWG 20/24 OR AWG 24/28 : CRIMP REMOVABLE										С
: 1.52mm (AWG 20/24) 1.02mm (AWG 24/28)											
	pro	jectio	n p	roduct	t fam	ily					
1101 D-SUB											
ifi	ified title										
	-	mm)–Sl	IR (KIMF)) ر)NNE	CIO	K	
5	sco	le 1:	1								
3/:	_	1.		wg na)		she	et 1 o	of 1	size	
, 1/	_	nph <u>e</u> i	_	2		~					
					· · ·	CILL) (\/	1 / 1		^ _ !	
1/	11	F	Ci∟				8-00			Аз	
<i>.</i> .		F	Ci∟	ype () / 1 mer	Draw	=	

STATUS:Released

D