

PRODUCT DESCRIPTION CODE :

10131934-YXXXLF

PLATING :
 ————— RoHS COMPATIBLE, SEE NOTE 3
 ————— PACKAGING : "U" : TUBE
 ————— TOTAL NUMBER OF POSITIONS 02 TO 25

1 = 0.76 μm GOLD ON CONTACT AREA
 2.00μm MIN MATTE TIN ON TAIL

2 = 0.38μm GOLD ON CONTACT AREA
 2.00μm MIN MATTE TIN ON TAIL

3 = 0.20μm GOLD ON CONTACT AREA
 2.00μm MIN MATTE TIN ON TAIL

4 = 0.76 μm GXT ON CONTACT AREA
 2.00μm MIN MATTE TIN ON TAIL

5 = 0.38μm GXT ON CONTACT AREA
 2.00μm MIN MATTE TIN ON TAIL

6 = 0.20μm GXT ON CONTACT AREA
 2.00μm MIN MATTE TIN ON TAIL

9 = 2.54μm MIN MATTE TIN ON CONTACT AREA
 2.00μm MIN MATTE TIN ON TAIL

1.27μm NICKEL MIN UNDERLAYER

NOTES :

1 - MATERIAL
 HOUSING : HIGH TEMPERATURE GLASS FILLED FLAME
 RETARDANT PER UL 94 V-0
 TERMINAL: COPPER ALLOY

2- TO DETERMINE DIMENSIONS :
 N = NUMBER OF POSITIONS PER ROW
 EXAMPLE : 8 POS N x 2 = 16mm
 UP TO N = 12 TOLERANCE : 0
 -0.10
 FROM N = 13 TOLERANCE : 0.05
 -0.10




3 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING :
 "LF" MEANS THE PRODUCT IS LEAD-FREE, 2μm MINIMUM MATTE TIN
 OVER 1.27μm MINIMUM NICKEL UNDERPLATE
 b - MANUFACTURING PROCESS COMPATIBILITY
 THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH
 TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A
 1.6mm MIN THICK CIRCUIT BOARD.

c - LABELLING :
 MEETS PACKAGING SPECS AS PER GS-14-920
 d - LEGAL STATEMENT : SEE GS-47-0004



RECOMMENDED HOLE PATTERN



spec ref	GS-12-1326	dr	Cyril Jeune	2014/12/02	projection	mm	size	A3	scale	6:1
tolerance std	ISO 406 ISO 1101	eng	Detouillon, Da	2020/12/21			ecn no	-	rel level	Released
TOLERANCES UNLESS OTHERWISE SPECIFIED		chr	-	-						
surface	linear	appr	Wollin, Severi	2020/12/21	product family	-	dwg no	10131934	rev	A
ISO 1302	angular			Amphenol FCI MINITEK RECEPTACLE 2MM ASSEMBLY VCC SR TMT www.fci.com		cat. no.	-	Product - Customer Drw	sheet 1 of 1	

Amphenol FCI

© 2016 AFCI