


HC-B 16-TMB-100/O1STM32S-EUA

Order No.: 1604434

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1604434>

HEAVYCON ADVANCE for increased environmental requirements,
sleeve housing B16, with bayonet locking, height 100 mm, with 1xM32
thread, lateral cable outlet

Commercial data	
GTIN (EAN)	 4 017918 948115
Note	Made-to-order
sales group	D201
Pack	10 pcs.
Customs tariff	85389099
Catalog page information	Page 477 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
03/01/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**General data**

Note	For contact inserts HC-B16, BB32, D40, DD72, HS6, HV6, M, K
Design	B16
Height	100 mm
Width	57 mm

Length	126 mm
Housing type	Sleeve housings
Locking type	Bayonet locking
Cable exit	Lateral
Type of the screw connection	1x M32
Degree of protection	IP65/67
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Die-cast aluminum, corrosion resistant
Housing surface material	Powder-coated, black
Seal material	Viton
Material lock	High-grade steel
Material grip body interlock	PA-GF
Length of the assembly cutout	86 mm
Width of the assembly cutout	35 mm

Accessories


Item	Designation	Description
Assembly		
1604641	HC-B-BF	Panel mounting flange for HEAVYCON ADVANCE TMB housing with bayonet locking

General

1690956	HC-B 16-TMB-SD-IP65	HEAVYCON ADVANCE IP65 protective cover B16, with bayonet locking, with retaining cord, diameter of retaining cord eyelet 3 mm
1604654	HC-B-BF-SET	Bayonet mounting-flange set, consisting of 2 mounting flanges with 4 self-tapping Torx head screws and 4 fan-type spacers

Diagrams/Drawings

Dimensioned drawing



Panel cutout

²⁾ When self-tapping Torx screws are used
(Torx20, M4)

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;