


PRODUCT NUMBER	DIM "J"	DIM "K"
76308-XXX(LF)	SEE SHEET 2/2	

WHEN NEEDED, SUFFIX LETTER "LF" INDICATES THE PRODUCT IS RoHS COMPATIBLE, SEE NOTE 5

WHEN SUFFIX "LF" IS REQUIRED, 2µm MIN MATTE TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.



NOTES:

- 1 MATERIAL HOUSING: THERMOPLASTIC POLYESTER 30 % GLASS FILLED, COLOUR BLUE, FLAME RETARDANT PER UL 94-V0.
- 2 MATERIAL BOX: BRASS ASTM B 36 C 26000-H02
- 3 MATERIAL SPRING: BERYLLIUM COPPER ASTM B 194 C 17200-TF 00.
- 4 PLATING: SEE NEXT SHEET
- 5 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.

b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.

c - LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-22-008

76308-1XXLF &-2XXLF ARE SIMILAR TO 76308-(1*2)XX, THE SUFFIX 'LF' IS ADDED FOR LEAD FREE IDENTIFICATION.

mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection 101	product family BERGCON	
ltr	ecn no	dr	date	tolerances unless otherwise specified		title		
M	F06-0216	DLE	06.07.03	angles	linear	±0.13	V. C. C. SINGLE ROW .100	
N	F-47097	TJA	23.01.24	±2'		mm	scale 5:1	
H	F80325	PNZ	98.05.06	dr	O. MATHEVON	96.01.29	dwg no	
J	F10568	DLE	01.10.25	engr	AESCHBACHER	96.01.29	sheet 1 of 2	
K	F05.0235	DLE	05.08.25	chr	O. MATHEVON	96.01.29	76308	
L	F05-0282	DLE	05.11.03	app	M. AE	96.01.29	A3	
sheet	revision	N	M			type		CUSTOMER Drawing
index	sheet	1	2					

PRODUCT NUMBER	NBR OF POS	DIM "J"	DIM "K"
76308-X02(LF)	1x02	(2.54)	(5.08)
76308-X03(LF)	1x03	(5.08)	(7.62)
76308-X04(LF)	1x04	(7.62)	(10.16)
76308-X05(LF)	1x05	(10.16)	(12.70)
76308-X06(LF)	1x06	(12.70)	(15.24)
76308-X07(LF)	1x07	(15.24)	(17.78)
76308-X08(LF)	1x08	(17.78)	(20.32)
76308-X09(LF)	1x09	(20.32)	(22.86)
76308-X10(LF)	1x10	(22.86)	(25.40)
76308-X11(LF)	1x11	(25.40)	(27.94)
76308-X12(LF)	1x12	(27.94)	(30.48)
76308-X13(LF)	1x13	(30.48)	(33.02)
76308-X14(LF)	1x14	(33.02)	(35.56)
76308-X15(LF)	1x15	(35.56)	(38.10)
76308-X16(LF)	1x16	(38.10)	(40.64)
76308-X17(LF)	1x17	(40.64)	(43.18)
76308-X18(LF)	1x18	(43.18)	(45.72)
76308-X19(LF)	1x19	(45.72)	(48.26)
76308-X20(LF)	1x20	(48.26)	(50.80)
76308-X21(LF)	1x21	(50.80)	(53.34)
76308-X22(LF)	1x22	(53.34)	(55.88)
76308-X23(LF)	1x23	(55.88)	(58.42)
76308-X24(LF)	1x24	(58.42)	(60.96)
76308-X25(LF)	1x25	(60.96)	(63.50)
76308-X26(LF)	1x26	(63.50)	(66.04)
76308-X27(LF)	1x27	(66.04)	(68.58)
76308-X28(LF)	1x28	(68.58)	(71.12)
76308-X29(LF)	1x29	(71.12)	(73.66)
76308-X30(LF)	1x30	(73.66)	(76.20)

PRODUCT NUMBER	NBR OF POS	DIM "J"	DIM "K"
76308-X31(LF)	1x31	(76.20)	(78.74)
76308-X32(LF)	1x32	(78.74)	(81.28)
76308-X33(LF)	1x33	(81.28)	(83.82)
76308-X34(LF)	1x34	(83.82)	(86.36)
76308-X35(LF)	1x35	(86.36)	(88.90)
76308-X36(LF)	1x36	(88.90)	(91.44)
76308-X37(LF)	1x37	(91.44)	(93.98)
76308-X38(LF)	1x38	(93.98)	(96.52)
76308-X39(LF)	1x39	(96.52)	(99.06)
76308-X40(LF)	1x40	(99.06)	(101.60)
76308-X41(LF)	1x41	(101.60)	(104.14)
76308-X42(LF)	1x42	(104.14)	(106.68)
76308-X43(LF)	1x43	(106.68)	(109.22)
76308-X44(LF)	1x44	(109.22)	(111.76)
76308-X45(LF)	1x45	(111.76)	(114.30)
76308-X46(LF)	1x46	(114.30)	(116.84)
76308-X47(LF)	1x47	(116.84)	(119.38)
76308-X48(LF)	1x48	(119.38)	(121.92)
76308-X49(LF)	1x49	(121.92)	(124.46)
76308-X50(LF)	1x50	(124.46)	(127.00)

2	1.0 μm Au	0.2 μm Au	1.3 μm Ni
1	0.76 μm Au	0.05 μm Au	1.3 μm Ni
PLATING CODE X	PLATING THICKNESS CONTACT AREA	PLATING THICKNESS REMAINDER	THICKNESS UNDER PLATING

mat'l. code SEE TABLE		surface ISO 1302 <input checked="" type="checkbox"/>		tolerance ISO 406 ISO 1101		projection 		product family BERGCON	
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm		title V. C. C. SINGLE ROW .100	
M	F-47097	TJA	23.01.24	angles linear		scale N/A		dwg no 76308	
G	V60456	OMA	96.03.11					sheet 2 of A3	
H	F80325	PNZ	98.05.06	dr	O. MATHEVON	96.01.30		type CUSTOMER Drawing	
J	F05-0235	DLE	05.08.25	engr	AESCHBACHER	96.01.30			
K	F05-0282	DLE	05.11.03	chr	O. MATHEVON	96.01.30			
L	F06-0216	DLE	076.07.11	app	M. AE	96.01.30			
sheet index	revision sheet								



Copyright FCI