

# G84-5200 XS

Small, flat and extremely robust



Models may vary from the image shown

The compact keyboard 'XS Complete' (G84-5200) offers a full keyboard layout complete with number block and is ideal for all applications with limited space and requiring frequent number entries.

## FUNCTION AND PERFORMANCE

- Full configuration with numeric keypad Ideal for applications where numbers need to be typed frequently
- High reliability and precise keystroke accuracy due to Gold Crosspoint contacts (Cherry ML technology) on each individual key
- Ideal for continuous use thanks to its high durability of more than 20 million keystrokes for each key
- Compact dimensions and very low overall height, making it ideal for tight spaces and 19" applications
- Uniform dimensions and dimensions are the same for the entire XS product series: the keypad can be selected to match the respective application
- Low weight: for special cases where every gram counts
- Plug & Play: compatible with standard operating system drivers
- Compatible with Code Set 3 and Unified POS
- Clamping option for permanent mounting

- Detachable support legs for individual configuration of the keyboard inclination
- Programmable keys for further time savings

## TECHNICAL DATA

Weight main product:	19 oz
Dimensions product without packaging:	14,72 in x 5,47 in x 0,79 in
Weight of product incl. packaging (g):	23.63 oz
Dimensions product incl. packaging:	15,47 in x 7,72 in x 1,3 in
Content of master carton (pieces):	21
Cable-length:	8.2 ft
Storage temperature:	-4 °F - 140 °F
Working temperature:	32 °F - 122 °F
Product approvals:	<ul style="list-style-type: none"><li>• BSMI</li><li>• RCM</li><li>• CE</li><li>• cURus</li><li>• FCC</li><li>• VCCI</li><li>• VDE</li><li>• UKCA</li></ul>
System Requirements-Hardware:	USB-A
Operating system:	<ul style="list-style-type: none"><li>• Windows 7</li><li>• Windows 8</li><li>• Windows 10</li><li>• Windows 11</li></ul>
Scope of delivery:	<ul style="list-style-type: none"><li>• Manual</li><li>• Keyboard</li></ul>
Reliability:	MTBF > 11,4 Millionen Stunden
Software support:	CHERRY KEYS
Service life per key (in million strokes):	20 mio. actuations
Switching characteristics:	tactile
Max. current consumption (mA) of keyboard:	35 mA
Keyboard format:	Compact (75%)

N-key rollover:	not specified
Anti-ghosting:	not specified
Key encryption:	no
Actuating force (cN):	50 cN
Key labeling:	Laser etching
Palm rest:	Palm rest not available
USB hub:	no
Special key functions:	FN
Illumination:	no

Adjustable feet:	sold separately
Status LEDs:	in housing
Key technology:	Mechanical
Switches:	CHERRY ML
Keycap material:	ABS
Model number:	ML5200

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

EAN & Part number	Switches	Color	Illumination	Layout
4025112072260 G84-5200LCMCH-2	CHERRY ML	black	no	CH (Switzerland)
4025112071119 G84-5200LCMDE-2	CHERRY ML	black	no	DE (Germany)
4025112073106 G84-5200LCMES-2	CHERRY ML	black	no	ES (Spain)
4025112071027 G84-5200LCMEU-2	CHERRY ML	black	no	EU (USA+ €-Symbol)
4025112072246 G84-5200LCMFR-2	CHERRY ML	black	no	FR (France)
4025112072253 G84-5200LCMGB-2	CHERRY ML	black	no	GB (United Kingdom)
4025112072277 G84-5200LCMCH-0	CHERRY ML	light-grey	no	CH (Switzerland)
4025112071126 G84-5200LCMDE-0	CHERRY ML	light-grey	no	DE (Germany)
4025112071010 G84-5200LCMEU-0	CHERRY ML	light-grey	no	EU (USA+ €-Symbol)
4025112071300 G84-5200LCMFR-0	CHERRY ML	light-grey	no	FR (France)

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.