

# STREAM KEYBOARD

THE KEYBOARD – the best STREAM of all time!



Models may vary from the image shown

CHERRY stands for the highest standards of reliability, durability and an incomparable typing feel. The CHERRY STREAM KEYBOARD improves what millions of satisfied users already appreciated in its predecessor. The classic has been updated for a new age.

Especially in the office environment, input devices are our daily companions and are in use for hours. The STREAM KEYBOARD sets new standards in this area and has the potential to become the most popular keyboard.

The mixture of conventional design, a pinch of elegance and simple purism make the keyboard the ideal companion in the office and at home that can suit many tastes. Thanks to the integrated metal plate, the STREAM KEYBOARD will impress users with its ideal torsional stiffness and stability despite its slim design. The two feet and eight rubber pads on the underside also ensure a firm stand when folded in and out.

CHERRY scissor technology has always been associated with an incomparable typing feel and uncompromising precision. During development, special attention was paid to noise created by typing. The noise development has been further reduced in comparison with the very quiet predecessor model. This makes the keyboard the first choice for offices with many workplaces or if you like to type quietly.

Our careful selection of materials ensures that the letters stand out clearly from the keys and that you can work in a fatigue-free manner. The status LEDs for CAPS LOCK, NUM and SCROLL LOCK integrated directly into the key are a unique feature that is otherwise only found in much higher price ranges. The red status LEDs show you at first glance whether the caps lock key has been pressed. Ten additional practical keys make work in Microsoft Office and multimedia applications easier. It includes six commonly used keys for controlling your multimedia player. In addition, the browser, email, and calculator functions give you easy access to frequently used commands at all times. A lock button allows users to log out at the push of a button before leaving their workstation. This is particularly invaluable in the office environment. Despite these additional keys, no separate drivers are required. The STREAM KEYBOARD is a plug&play device.

In working environments, in particular, compliance with guidelines, quality and environmental goals is obligatory. For CHERRY, these goals are also part of its corporate philosophy. This is why we have put our efforts into our successful bid to gain the "Blauer Engel" award. In addition, the GS "Safety Tested" seal certifies that the product complies with all relevant European directives and regulations relating to health protection.

Are you looking for a reliable companion who will not let you down in your daily work or your private life? The CHERRY STREAM KEYBOARD is the perfect choice.

## FUNCTION AND PERFORMANCE

- Maximum productivity: Extremely quiet keystrokes, unbeatable typing feel
- Highest quality: Durable key lettering, our own SX scissor mechanism, "Blauer Engel" eco-label
- Optimum operating comfort: 3 integrated status LEDs, perfect slip resistance, 10 Office & multimedia keys
- Very latest design: Flat overall height, focused on the essentials, GS approval

## TECHNICAL DATA

Weight main product:	32 oz
Dimensions product without packaging:	18,23 in x 6,42 in x 0,71 in
Weight of product incl. packaging (g):	38.8 oz
Dimensions product incl. packaging:	18,9 in x 8,27 in x 0,94 in
Content of master carton (pieces):	10
Weight of master carton incl. content (g):	392.6 oz
Dimensions master carton:	19.69 in x 8.78 in x 8.66 in
Cable-length:	5.91 ft
Storage temperature:	-4 °F - 140 °F
Working temperature:	32 °F - 104 °F
Product approvals:	<ul style="list-style-type: none"> <li>• cURus</li> <li>• GS</li> <li>• CE</li> <li>• FCC</li> <li>• Blauer Engel</li> <li>• UKCA</li> </ul>
System Requirements-Hardware:	USB-A
Operating system:	<ul style="list-style-type: none"> <li>• Windows 7</li> <li>• Windows 8</li> <li>• Windows 10</li> <li>• Windows 11</li> </ul>
Scope of delivery:	<ul style="list-style-type: none"> <li>• Manual</li> <li>• Keyboard</li> </ul>
Reliability:	MTBF 90: > 10 Mio.
Software support:	CHERRY KEYS
USB dongle:	no
2.4 Ghz wireless connection:	no
Connection via Bluetooth:	no
Service life per key (in million strokes):	20 mio. actuations

Switching characteristics:	standard
Max. current consumption (mA) of keyboard:	20 mA
Keyboard format:	Full-size (100%)
Integrated metal plate:	yes
Volume (dB) of keyboard:	49 db
N-key rollover:	not specified
Anti-ghosting:	not specified
Key encryption:	no
Internal memory:	no
Actuating force (cN):	65 cN
Actuating force tol.:	10 cN
Key stroke total travel path:	2,8 mm
Palm rest:	Palm rest not available
USB hub:	no
Special key functions:	<ul style="list-style-type: none"> <li>• Browser</li> <li>• e-mail program</li> <li>• Next track</li> <li>• PC lock</li> <li>• Play/Pause</li> <li>• Calculator</li> <li>• Unmute/Mute</li> <li>• Volume up</li> <li>• Volume down</li> <li>• Last track</li> </ul>
Illumination:	no
Adjustable feet:	integrated
Status LEDs:	in keys
Key technology:	Scissor
Keycap material:	ABS
Model number:	JK-85
Warranty:	1 additional year voluntary limited manufacturers warranty

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

EAN & Part number	Color	Illumination	Layout
4025112090714 JK-8500AA-2	black	no	
4025112090318 JK-8500BE-2	black	no	BE (Belgium)
4025112097072 JK-8500CF-2	black	no	
4025112090257 JK-8500CH-2	black	no	CH (Switzerland)
4025112090332 JK-8500CHADSL	black	no	
4025112092213 JK-8500CN-2	black	no	CN (China)
4025112091346 JK-8500CS-2	black	no	CS (Czech Republic / Slovak Republic)
4025112090172 JK-8500DE-2	black	no	DE (Germany)
4025112090325 JK-8500DEADSL	black	no	
4025112090363 JK-8500ES-2	black	no	ES (Spain)
4025112090233 JK-8500EU-2	black	no	EU (USA+ €-Symbol)
4025112091414 JK-8500EUADSL	black	no	
4025112090196 JK-8500FR-2	black	no	FR (France)
4025112090349 JK-8500FRADSL	black	no	
4025112090219 JK-8500GB-2	black	no	GB (United Kingdom)
4025112103810 JK-8500HU-2	black	no	HU (Hungary)
4025112090295 JK-8500IT-2	black	no	IT (Italy)
4025112090271 JK-8500PN-2	black	no	PN (PanNordic)
4025112094156 JK-8500SL-2	black	no	SL (Slovenia)

EAN & Part number	Color	Illumination	Layout
4025112092961 JK-8500TW-2	black	no	TW (Taiwan)
4025112116612 JK-8500UG-2	black	no	
4025112094705 JK-8501PN-2	black	no	
4025112090707 JK-8500AA-0	white-grey	no	
4025112090301 JK-8500BE-0	grey	no	BE (Belgium)
4025112097065 JK-8500CF-0	white-grey	no	
4025112090240 JK-8500CH-0	white-grey	no	CH (Switzerland)
4025112092206 JK-8500CN-0	white-grey	no	CN (China)
4025112091339 JK-8500CS-0	white-grey	no	CS (Czech Republic / Slovak Republic)
4025112090165 JK-8500DE-0	white-grey	no	DE (Germany)
4025112090356 JK-8500ES-0	white-grey	no	ES (Spain)
4025112090226 JK-8500EU-0	white-grey	no	EU (USA+ €-Symbol)
4025112090189 JK-8500FR-0	white-grey	no	FR (France)
4025112090202 JK-8500GB-0	white-grey	no	GB (United Kingdom)
4025112109232 JK-8500HU-0	white-grey	no	HU (Hungary)
4025112090288 JK-8500IT-0	white-grey	no	IT (Italy)
4025112090264 JK-8500PN-0	white-grey	no	PN (PanNordic)
4025112094149 JK-8500SL-0	white-grey	no	SL (Slovenia)
4025112092954 JK-8500TW-0	white-grey	no	TW (Taiwan)



Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.