


98415-104LF

RoHS COMPATIBLE, SEE NOTES 5

2±0.08
NON ACCUM.
RECOMMENDED HOLE PATTERN



NOTES:



- 1 - HOUSING MATERIAL: LCP COLOR CREAM.
- 2 - PLATING : 0.76µm GOLD/GXT OVER 1.27µm Ni MIN
- 3 - TERMINAL MATERIAL: COPPER ALLOY
- 4 - STANDARD PACKAGING IN POLYBAGS
5. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.

b - LABELLING:

- MEETS PACKAGING SPECS AS PER GS-14-920
- c - THIS PRODUCT MEETS EUROPEAN DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-47-0004



mat'l. code		surface		tolerance		projection		product family	
lfr	ecn no	dr	date	ISO 1302	ISO 406	ISO 101	mm	MINITEK	MINITEK HEADER
C	F05-0268	J00	05.10.06	tolerances unless otherwise specified	±0.2				
D	F06-0210	LMU	06.07.05	angles	linear				
E	F08-0143	ELA	08.04.15	±2°					
F	B-19190	LMU	14.10.24	dr	LMULIN	02.07.26			
				eng	JU	COMPAGNON	02.07.29		
				chr					
				appd	JM.C	02.07.29			
sheet	revision								
index	sheet								



MINITEK
HEADER 2x2

98415

sheet 1 of 1 size A3

CUSTOMER Drawing