




Tuning Fork Crystal


SMD-version

part no.	12.87126
model	KX – 327XS
frequency	32.768 kHz
operating temperature	-20° ~ +70°C
frequency tolerance at +25°C	±20 ppm
temperature tolerance (parabolic coefficient)	-0.034 ±0.006 ppm / °C ² typ., -0.042 ppm / °C ² max.
turnover temperature	+25°C ±5°C
load capacitance C _L	12.5 pF
series resistance R1 (ESR) max.	65 kOhm
aging at +25°C (first year) max.	±3 ppm
shunt capacitance C ₀ max.	2 pF
drive level max.	0.001 mW
contents of reel	3000 pcs.


Dimensions (mm):



Suggested soldering pad:



Reflow soldering condition:



Tape specification:

