


A		B	C	D	E	
CAT. NO.	COLOR	REV			DESCRIPTION	DATE
109 - 165M - 001	BLACK					
109 - 165M - 002	WHITE/NATURAL					



1

2

3

4

RoHS Compliant

NOTE:

1. FLAMMABILITY RATING: UL94V-2
2. MAX BUNDLE DIA. : 43 mm (1.69 inch)
3. MIN TENSILE STRENGTH : 18 lbs (8 kgs)
4. COLOR: SEE CHART

DRAWN: RYAN	Tolerance Unless Otherwise Specified
CHECKED: SCOTT	MATERIAL: PA66
	UNIT: mm
	SCALE: 1/2
APPROVAL: JEFF	SHEET: 1-0
	DATE: 2024/06/08

CnC Tech
Industrial Cable and Connector Technology

DESCRIPTION: **CABLES TIES**

PART NO: **109 - 165M - X X X (SEE CHART)**