

PCN Number:	20240806006.1	PCN Date:	August 06, 2024
Title:	Qualification of DFAB as an additional Wafer Fab site option for select devices		
Customer Contact:	Change Management Team	Dept:	Quality Services
Proposed 1st Ship Date:	November 04, 2024	Sample requests accepted until:	September 05, 2024*

***Sample requests received after September 05, 2024 will not be supported.**

Change Type:

<input type="checkbox"/>	Assembly Site	<input type="checkbox"/>	Design	<input type="checkbox"/>	Wafer Bump Material
<input type="checkbox"/>	Assembly Process	<input type="checkbox"/>	Data Sheet	<input type="checkbox"/>	Wafer Bump Process
<input type="checkbox"/>	Assembly Materials	<input type="checkbox"/>	Part number change	<input checked="" type="checkbox"/>	Wafer Fab Site
<input type="checkbox"/>	Mechanical Specification	<input type="checkbox"/>	Test Site	<input checked="" type="checkbox"/>	Wafer Fab Material
<input checked="" type="checkbox"/>	Packing/Shipping/Labeling	<input type="checkbox"/>	Test Process	<input type="checkbox"/>	Wafer Fab Process

PCN Details

Description of Change:

Texas Instruments is pleased to announce the addition of DFAB as an additional Wafer Fab site option for the products listed in the "Product Affected" section of this document.

Current Fab Site			Additional Fab Site		
Current Fab Site	Process	Wafer Diameter	Additional Fab Site	Process	Wafer Diameter
SFAB	J11	150 mm	DFAB	J11	200 mm

Qual details are provided in the Qual Data Section.

Reason for Change:

These changes are part of our multiyear plan to transition products from our 150-millimeter factories to newer, more efficient manufacturing processes and technologies, underscoring our commitment to product longevity and supply continuity.

Anticipated impact on Form, Fit, Function, Quality or Reliability (positive / negative):

None

Changes to product identification resulting from this PCN:

Fab Site Information:

Chip Site	Chip Site Origin Code (20L)	Chip Site Country Code (21L)	Chip Site City
SH-BIP-1	SHE	USA	Sherman
DL-LIN	DLN	USA	Dallas

Sample product shipping label (not actual product label):

TEXAS INSTRUMENTS
 MADE IN: Malaysia
 2DC: 20:
 MSL '2 /260C/1 YEAR SEAL DT
 MSL 1 /235C/UNLIM 03/29/04
 OPT:
 ITEM: 39
 LBL: 5A (L)T0:1750

(1P) SN74LS07NSR
 (Q) 2000 (D) 0336
 (31T) LOT: 3959047MLA
 (4W) TKY (1T) 7523483SI2
 (P)
 (2P) REV: (V) 6833317
 (20L) CSO: SHE (21L) CCO: USA
 (22L) ASO: MLA (23L) ACO: MYS

Product Affected:

SN74LS02DR	SN74LS151DR	SN74LS161ANSR	SN74LS251N
SN74LS02DRE4	SN74LS151N	SN74LS193DR	SN74LS251NE4
SN74LS02N	SN74LS151NE4	SN74LS193N	SN74LS251NSR
SN74LS02NE4	SN74LS151NSR	SN74LS193NE4	SN74LS393DR

SN74LS02NSR	SN74LS157DR	SN74LS193NSR	SN74LS393N
SN74LS02NSRG4	SN74LS157DRE4	SN74LS221DBR	SN74LS393NE4
SN74LS125ADBR	SN74LS157N	SN74LS221DR	SN74LS393NSR
SN74LS125ADR	SN74LS157NE4	SN74LS221N	SN74LS90DR
SN74LS125ADRE4	SN74LS157NSR	SN74LS221NE4	SN74LS90N
SN74LS125AN	SN74LS161ADR	SN74LS221NSR	SN74LS90NE4
SN74LS125ANSR	SN74LS161AN	SN74LS251DR	

For alternate parts with similar or improved performance, please visit the product page on TI.com

Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Type	#	Test Name	Condition	Duration	Qual Device: SN75C185DWR
HAST	A2	Biased HAST	130C/85%RH	96 Hours	2/154/0
UHAST	A3	Unbiased HAST	130C/85%RH	96 Hours	3/231/0
TC	A4	Temperature Cycle	-65C/150C	500 Cycles	3/231/0
HTSL	A6	High Temperature Storage Life	170C	420 Hours	3/231/0
SD	C3	PB-Free Solderability	Precondition w.155C Dry Bake (4 hrs +/- 15 minutes); PB-Free Solder;	-	1/22/0
ESD	E2	ESD CDM	-	250 Volts	1/3/0
ESD	E2	ESD HBM	-	1000 Volts	1/3/0
LU	E4	Latch-Up	Per JESD78	-	1/3/0
CHAR	E5	Electrical Characterization	Per Datasheet Parameters	-	1/30/0

- QBS: Qual By Similarity
- Qual Device SN75C185DWR is qualified at MSL1 260C
- Qual Device SN75C185DWR is qualified at MSL1 260C
- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable
- The following are equivalent HTOL options based on an activation energy of 0.7eV : 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours
- The following are equivalent HTSL options based on an activation energy of 0.7eV : 150C/1k Hours, and 170C/420 Hours
- The following are equivalent Temp Cycle options per JESD47 : -55C/125C/700 Cycles and -65C/150C/500 Cycles

Quality and Environmental data is available at TI's external Web site: <http://www.ti.com/>

TI Qualification ID: R-CHG-2202-030

For questions regarding this notice, e-mails can be sent to the Change Management team or your local Field Sales Representative.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for,

and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.