



## **Specification of Automotive MLCC**

- Supplier : Samsung electro-mechanics
- Product : Multi-layer Ceramic Capacitor
- Samsung P/N :
- CL31B154KBP5PNE
- Description : CAP, 150nF, 50V, ±10%, X7R, 1206
- AEC-Q 200 Specified

A. Samsung Part Number

|            |               |        | <u>CL</u> | <u>31</u> | <u>B</u> | <u>154</u> | <u>K</u> | <u>B</u> | <u>P</u> | <u>5</u> | <u>P</u> | N  | <u>E</u>               |
|------------|---------------|--------|-----------|-----------|----------|------------|----------|----------|----------|----------|----------|----|------------------------|
|            |               |        | 1         | 2         | 3        | 4          | 5        | 6        |          | 8        | 9        | 10 | 0                      |
|            |               |        |           |           |          |            |          |          |          |          |          |    |                        |
| 1          | Series        | Samsun | ig Multi  | -layer    | Cera     | nic Ca     | pacit    | or       |          |          |          |    |                        |
| 2          | Size          | 1206 ( | (inch co  | ode)      |          | L:         | 3.2      | ± 0.1    | 5        | mm       |          | W: | 1.6 ± 0.15 mm          |
|            |               |        |           |           |          |            |          |          |          |          |          |    |                        |
| 3          | Dielectric    | X7R    |           |           |          |            | 8        | Inner    | elec     | trode    |          |    | Ni , Open mode         |
| 4          | Capacitance   | 150    | nF        |           |          |            |          | Term     | inati    | on       |          |    | Cu , Ag-epoxy          |
| 5          | Capacitance   | ±10 '  | %         |           |          |            |          | Platir   | ng       |          |          |    | Sn 100% (Pb Free)      |
|            | tolerance     |        |           |           |          |            | 9        | Prod     | uct      |          |          |    | Automotive             |
| 6          | Rated Voltage | 50 \   | V         |           |          |            | 10       | Grad     | e cod    | le       |          |    | Standard               |
| $\bigcirc$ | Thickness     | 1.15 : | ± 0.15    | mm        |          |            | 1        | Pack     | aging    | 9        |          |    | Embossed Type, 7" reel |

## B. Reliablility Test and Judgement condition

|                      | Performance   | Test condition  |  |  |  |  |
|----------------------|---|---|--|--|--|--|
| High Temperature     | Appearance : No abnormal exterior appearance                                | Unpowered, 1000hrs@T=150℃                                 |  |  |  |  |
| Exposure             | Capacitance Change : Within ±10%  | Measurement at 24±2hrs after test conclusion              |  |  |  |  |
|                      | Tan δ: 0.03 max   |   |  |  |  |  |
|                      | IR : More than 10,000 $\Omega$ or 500 $\Omega \times \mu F$                 |   |  |  |  |  |
|                      | Whichever is Smaller  |   |  |  |  |  |
| Temperature Cycling  | Appearance : No abnormal exterior appearance                                | 1000Cycles  |  |  |  |  |
|                      | Capacitance Change : Within ±10%  | Measurement at 24±2hrs after test conclusion              |  |  |  |  |
|                      | Tan δ: 0.03 max   | 1 cycle condition :                                       |  |  |  |  |
|                      | IR : More than 10,000 $\Omega$ or 500 $\Omega \times \mu F$                 | -55+0/-3℃(15±3min) -> Room Temp(1min.)                    |  |  |  |  |
|                      | Whichever is Smaller  | -> 125+3/-0°C(15±3min) -> Room Temp(1min.)                |  |  |  |  |
| Destructive Physical | No Defects or abnormalities   | Per EIA 469   |  |  |  |  |
| Analysis             |   |   |  |  |  |  |
| Moisture Resistance  | Appearance : No abnormal exterior appearance                                | 10Cycles, t=24hrs/cycle                                   |  |  |  |  |
|                      | Capacitance Change : Within ±12.5%  | Heat (25~65 $^\circ C$ ) and humidity (80~98%), Unpowered |  |  |  |  |
|                      | Tan δ: 0.03 max   | measurement at 24±2hrs after test conclusion              |  |  |  |  |
|                      | IR : More than 10,000 $\mbox{M}\Omega$ or 500 $\mbox{M}\Omega \times \mu F$ |   |  |  |  |  |
|                      | Whichever is Smaller  |   |  |  |  |  |
| Humidity Bias        | Appearance : No abnormal exterior appearance                                | 1000hrs 85 $^\circ$ C/85%RH, Rated Voltate and 1.3~1.5V,  |  |  |  |  |
|                      | Capacitance Change : Within ±12.5%  | Add 100kohm resistor                                      |  |  |  |  |
|                      | Tan δ: 0.035 max  | Measurement at 24±2hrs after test conclusion              |  |  |  |  |
|                      | IR : More than 500MΩ or $25$ MΩ× $\mu$ F                                    | The charge/discharge current is less than 50mA.           |  |  |  |  |
|                      | Whichever is Smaller  |   |  |  |  |  |
| High Temperature     | Appearance : No abnormal exterior appearance                                | 1000hrs @ TA=125°C, 200% Rated Voltage,                   |  |  |  |  |
| Operating Life       | Capacitance Change : Within ±12.5%  | Measurement at 24±2hrs after test conclusion              |  |  |  |  |
|                      | Tan δ: 0.035 max  | The charge/discharge current is less than 50mA.           |  |  |  |  |
|                      | IR : More than 1000№ or 50№×μF  |   |  |  |  |  |
|                      | Whichever is Smaller  |   |  |  |  |  |

|                     | Performance                                     | Test condition   |  |  |  |  |  |  |
|---------------------|---|--|--|--|--|--|--|--|
| External Visual     | No abnormal exterior appearance                 | Microscope ('10)   |  |  |  |  |  |  |
| Physical Dimensions | Within the specified dimensions                 | Using The calipers   |  |  |  |  |  |  |
| Mechanical Shock    | Appearance : No abnormal exterior appearance    | Three shocks in each direction should be applied along   |  |  |  |  |  |  |
|                     | Capacitance Change : Within ±10%                | 3 mutually perpendicular axes of the test specimen (18 shocks)   |  |  |  |  |  |  |
|                     | Tan δ, IR : initial spec.                       | Peakvalue Duration Wave Velocity   |  |  |  |  |  |  |
|                     |   | 1,500G 0.5ms Half sine 4.7m/sec.   |  |  |  |  |  |  |
| Vibration           | Appearance : No abnormal exterior appearance    | 5g's for 20min., 12cycles each of 3 orientations,  |  |  |  |  |  |  |
|                     | Capacitance Change : Within ±10%                | Use 8"×5" PCB 0.031" Thick 7 secure points on one long side  |  |  |  |  |  |  |
|                     | Tan δ, IR : initial spec.                       | and 2 secure points at corners of opposite sides. Parts mounted  |  |  |  |  |  |  |
|                     |   | within 2" from any secure point. Test from $10\sim 2000 \text{Hz}$ .                                       |  |  |  |  |  |  |
| Resistance to       | Appearance : No abnormal exterior appearance    | Solder pot : 260±5°C, 10±1sec.   |  |  |  |  |  |  |
| Solder Heat         | Capacitance Change : Within ±10%                |  |  |  |  |  |  |  |
|                     | Tan δ, IR : initial spec.                       |  |  |  |  |  |  |  |
| Thermal Shock       | Appearance : No abnormal exterior appearance    | -55℃/+125℃.  |  |  |  |  |  |  |
|                     | Capacitance Change : Within ±10%                | Note: Number of cycles required-300,   |  |  |  |  |  |  |
|                     | Tan δ, IR : initial spec.                       | Maximum transfer time-20 sec, Dwell time-15min. Air-Air  |  |  |  |  |  |  |
| ESD                 | Appearance : No abnormal exterior appearance    | AEC-Q200-002   |  |  |  |  |  |  |
|                     | Capacitance Change : Within ±10%                |  |  |  |  |  |  |  |
|                     | Tan δ, IR : initial spec.                       |  |  |  |  |  |  |  |
| Solderability       | 95% of the terminations is to be soldered       | a) Preheat at 155 $^\circ\!\mathrm{C}$ for 4 hours, Immerse in solder for 5s at 245±5 $^\circ\!\mathrm{C}$ |  |  |  |  |  |  |
|                     | evenly and continuously                         | b) Steam aging for 8 hours, Immerse in solder for 5s at 245 $\pm$ 5 $^\circ$ C                             |  |  |  |  |  |  |
|                     |   | c) Steam aging for 8 hours, Immerse in solder for 120s at $260\pm5^\circ\mathrm{C}$                        |  |  |  |  |  |  |
|                     |   | solder : a solution ethanol and rosin  |  |  |  |  |  |  |
| Electrical          | Capacitance : Within specified tolerance        | The Capacitance /D.F. should be measured at $25^\circ C$ ,   |  |  |  |  |  |  |
| Characterization    | Tan δ (DF): 0.025 max.                          | 1₩z±10%, 1.0±0.2Vrms   |  |  |  |  |  |  |
|                     | IR(25℃) : More than 10,000№ or 500№×µF          | I.R. should be measured with a DC voltage not exceeding  |  |  |  |  |  |  |
|                     | IR(125℃) : More than1,000№ or 10№× <i>μ</i> F   | Rated Voltage @25°C, @125°C for 60~120 sec.  |  |  |  |  |  |  |
|                     | Whichever is Smaller                            |  |  |  |  |  |  |  |
|                     | Dielectric Strength                             | Dielectric Strength : 250% of the rated voltage for 1~5 seconds  |  |  |  |  |  |  |
| Board Flex          | Appearance : No abnormal exterior appearance    | Benaing to the limit (2mm) for 5 seconds   |  |  |  |  |  |  |
|                     | Capacitance Change : Within ±10%                |  |  |  |  |  |  |  |
| Terminal            | Appearance : No abnormal exterior appearance    | 18N, for 60±1 sec.   |  |  |  |  |  |  |
| Strength(SMD)       | Capacitance Change : Within ±10%                |  |  |  |  |  |  |  |
| Beam Load           | Destruction value should not be exceed          | Beam speed   |  |  |  |  |  |  |
|                     | Chip Length $\geq$ 3.2mm                        | 2.5±0.25mm/sec   |  |  |  |  |  |  |
|                     | a) Chip Thickness < 1.25mm : 15N                |  |  |  |  |  |  |  |
|                     | b) Chip Thickness $\geq$ 1.25mm : 54.5N         |  |  |  |  |  |  |  |
| Temperature         | X7R   |  |  |  |  |  |  |  |
| Characterisitcs     | (From -55 °C to 125 °C, Capacitance change show | ud be within ±15%)   |  |  |  |  |  |  |

## C. Recommended Soldering method :

Reflow ( Reflow Peak Temperature : 260+0/-5  $^\circ C$  , 10sec. Max ) Meet IPC/JEDEC J-STD-020 D Standard

\* For the more detail Specification, Please refer to the Samsung MLCC catalogue.