

# Vishay General Semiconductor

# **Ultrafast Plastic Rectifier**





#### **FEATURES**

- · Glass passivated chip junction
- Ultrafast reverse recovery time
- Low forward voltage drop
- · Low leakage current
- · Low switching losses, high efficiency
- High forward surge capability
- Solder dip 275 °C max. 10 s, per JESD 22-B106
- · Material categorization: For definitions of compliance please see www.vishav.com/doc?99912

PRIMARY CHARACTERISTICS			
I <sub>F(AV)</sub>	1.0 A		
$V_{RRM}$	200 V		
I <sub>FSM</sub>	35 A		
t <sub>rr</sub>	25 ns		
$V_{F}$	0.710 V		
T <sub>J</sub> max.	175 °C		
Package	DO-204AC (DO-15)		
Diode variations	Single die		

#### TYPICAL APPLICATIONS

For use in high frequency rectification and freewheeling application in switching mode converters and inverters for consumer, computer and telecommunication.

#### **MECHANICAL DATA**

Case: DO-204AC (DO-15)

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade

Terminals: Matte tin plated leads, solderable per

J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test Polarity: Color band denotes cathode end

MAXIMUM RATINGS (T <sub>A</sub> = 25 °C unless otherwise noted)			
PARAMETER	SYMBOL	MUR120	UNIT
Maximum repetitive peak reverse voltage	$V_{RRM}$	200	V
Working peak reverse voltage	V <sub>RWM</sub>	200	V
Maximum DC blocking voltage	$V_{DC}$	200	V
Maximum average forward rectified current at T <sub>A</sub> = 130 °C	I <sub>F(AV)</sub>	1.0	А
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I <sub>FSM</sub>	35	А
Operating and storage temperature range	T <sub>J</sub> , T <sub>STG</sub>	- 65 to + 175	°C



# Vishay General Semiconductor

<b>ELECTRICAL CHARACTERISTICS</b> (T <sub>A</sub> = 25 °C unless otherwise noted)					
PARAMETER	TEST CONDITIONS		SYMBOL	MUR120	UNIT
Maximum instantaneous	1.0 A	T <sub>J</sub> = 25 °C	V <sub>E</sub> (1)	0.875	- V
forward voltage	1.0 A	T <sub>J</sub> = 150 °C	VF (··/	0.710	
Maximum instantaneous reverse		T <sub>J</sub> = 25 °C	I <sub>R</sub> <sup>(1)</sup>	2.0	μΑ
current at rated DC blocking voltage		T <sub>J</sub> = 150 °C		50	
$I_F = 0.5 \text{ A}, I_R = 1.0 \text{ A}, I_{rr} = 0.25 \text{ A}$		$I_{rr} = 0.25 A$	t <sub>rr</sub>	25	ns
Maximum reverse recovery time	$I_F = 1.0 \text{ A}, \text{ dI/dt} = 50 \text{ A/}\mu\text{s},$ $V_R = 30 \text{ V}, I_{rr} = 10 \% I_{RM}$			35	
Maximum forward recovery time	$I_F = 1.0 \text{ A}$ , $dI/dt = 100 \text{ A/}\mu\text{s}$ , $I_{rec}$ to 1.0 V		t <sub>fr</sub>	25	ns

#### Note

<sup>&</sup>lt;sup>(1)</sup> Pulse test:  $t_p = 300 \mu s$  pulse, duty cycle  $\leq 2 \%$ 

THERMAL CHARACTERISTICS (T <sub>A</sub> = 25 °C unless otherwise noted)				
PARAMETER	SYMBOL	MUR120	UNIT	
Typical thermal resistance junction to ambient	R <sub>0JA</sub> (1)	27	°C/W	

#### Note

(1) Lead length = 3/8" on PCB with 1.5" x 1.5" (38.1 mm x 38.1 mm) copper surface

ORDERING INFORMATION (Example)				
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
MUR120-E3/54	0.41	54	4000	13" diameter paper tape and reel
MUR120-E3/73	0.41	73	2000	Ammo pack packaging

## **RATINGS AND CHARACTERISTICS CURVES** ( $T_A = 25$ °C unless otherwise noted)




Fig. 1 - Forward Current Derating Curve




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current



# Vishay General Semiconductor




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 5 - Typical Junction Capacitance





Fig. 4 - Typical Reverse Leakage Characteristics

### **PACKAGE OUTLINE DIMENSIONS** in inches (millimeters)

#### DO-204AC (DO-15)





## **Legal Disclaimer Notice**

Vishay

## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# **Material Category Policy**

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000