
GM5BC01200AC/GM5GC01200AC

6050 Size, 2.5mm Thickness, Leadless Chip LED


■ Outline Dimensions

(Unit: mm)



■ Directive Characteristics

(Ta=25°C)



■ Absolute Maximum Ratings

(Ta=25°C)

Model No.	Emitting color		Power dissipation P (mW)	Forward current IF (mA)	Peak forward current IFM*1 (mA)		g factor /°C)	Reverse voltage VR (V)	Operating temperature Topr (°C)	Storage temperature T_{stg} (°C)	Soldering temperature T_{sol}^{*2} (°C)
GM5BC01200AC	Blue	InGaN	330	60	70	1.00	1.17	5	-30 to +85	-40 to +85	295
GM5GC01200AC	Green	InGaN	330	60	70	0.80	0.93	5	-30 to +85	-40 to +100	295

^{*1} Duty ratio=1/10, Pulse width=0.1ms

■ Electro-optical Characteristics


 $(I_F\!\!=\!\!50mA,\!T_a\!\!=\!\!25^\circ C)$


		e Model No.			Peak emission	Dominant	т .	Spectrum radiation	D		
			Forward voltage V _F (V)		wavelength	wavelength λ _d (nm)	Luminous	bandwidth	Reverse current		Page for
	Lens type				$\lambda_{p}(nm)$		intensity Iv(mcd)	$\Delta\lambda(nm)$	I _R (µA)	V_R	V _R characteristics
			TYP	MAX	TYP	TYP	TYP	TYP	MAX	(V)	diagrams
	Colorless	GM5BC01200AC	4.6	5.5	467	470	200	27	100	4	60
	transparency	GM5GC01200AC	4.4	5.5	513	519	520	39	100	4	60


^{*2} For 3s or less at the temperature of hand soldering. Temperature of reflow soldering is shown on page 2.


Characteristics Diagrams


(GM1BC55200AC/GM1GC55200AC)



















GM5BC01200AC/GM5GC01200AC/GM5BC03200Z/GM5GC03200Z
















Note) Characteristics shown in diagrams are typical values. (not assurance value)


Internet

(Unit: mm)







GM1 40300AE series/LT1 40A series 4 000 pcs. /reel




LT1□90A series 3 000 pcs. / reel



GM5□□95200A□ series/LT1Z□95A series 2 000 pcs. /reel




GM5 \square \square 01200A series/GM5WA02200A/GM5WA06210A/GM5WA06250A 800 pcs. / reel




LT1QQ45A series/GM4QC13300AC series 3 000 pcs. /reel

Taping Specifications


(Unit:mm)



LT1 \square G7A series/GM1WA80350A/GM1ZUB 80300A/GM1ZSG80300A 4 000 pcs. /reel




LT1□□90A series 3 000 pcs. / reel




GM4□□81200A□ series 4 000 pcs. /reel

■ Shape and dimension of reel



Taping Specifications

■Lead type Chip LED (Unit: mm)



 $\textbf{GM5} \square \square \textbf{03200Z series/GM5WA06200Z/GM5WA06250Z} \quad 1 \ 000 \ \text{pcs.} \ (50 \ \text{pcs./sleeve} \times 20)$

NOTICE

- The circuit application examples in this publication are provided to explain representative applications of SHARP devices and are not intended to guarantee any circuit design or license any intellectual property rights. SHARP takes no responsibility for any problems related to any intellectual property right of a third party resulting from the use of SHARP's devices.
- Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device. SHARP reserves the right to make changes in the specifications, characteristics, data, materials, structure, and other contents described herein at any time without notice in order to improve design or reliability. Manufacturing locations are also subject to change without notice.
- Observe the following points when using any devices in this publication. SHARP takes no responsibility
 for damage caused by improper use of the devices which does not meet the conditions and absolute
 maximum ratings to be used specified in the relevant specification sheet nor meet the following
 conditions:
- (i) The devices in this publication are designed for use in general electronic equipment designs such as:
- Personal computers
- Office automation equipment
- Telecommunication equipment [terminal]
- Test and measurement equipment
- Industrial control
- Audio visual equipment
- Consumer electronics
- (ii) Measures such as fail-safe function and redundant design should be taken to ensure reliability and safety when SHARP devices are used for or in connection with equipment that requires higher reliability such as:
- Transportation control and safety equipment (i.e., aircraft, trains, automobiles, etc.)
- Traffic signals
- Gas leakage sensor breakers
- Alarm equipment
- Various safety devices, etc.
- (iii)SHARP devices shall not be used for or in connection with equipment that requires an extremely high level of reliability and safety such as:
- Space applications
- Telecommunication equipment [trunk lines]
- Nuclear power control equipment
- Medical and other life support equipment (e.g., scuba).
- If the SHARP devices listed in this publication fall within the scope of strategic products described in the Foreign Exchange and Foreign Trade Law of Japan, it is necessary to obtain approval to export such SHARP devices.
- This publication is the proprietary product of SHARP and is copyrighted, with all rights reserved. Under the copyright laws, no part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, for any purpose, in whole or in part, without the express written permission of SHARP. Express written permission is also required before any use of this publication may be made by a third party.
- Contact and consult with a SHARP representative if there are any questions about the contents of this publication.