



Part Number : 2002142410

Product Description : Insertion Tool for  
EXTreme Ten60Power Vertical Plug Assembly,  
22.00mm Width x 50.00mm Length

Series Number : 207123

Status : Active

Product Category : Application Tooling  
Accessories

---

## Documents & Resources

### Tooling Specifications

Application Tooling Specification 2002142410-000.pdf

Commercial Crimp Book TM-638000029-001.pdf

Commercial Crimp Book TM-638000029SP-001.pdf

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Application Tooling Accessories
Series	207123
Description	Insertion Tool for EXTreme Ten60Power Vertical Plug Assembly, 22.00mm Width x 50.00mm Length
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual, Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Family	Application Tooling
Product Name	EXTreme Ten60Power
Tool Type	Press-Fit Insertion Tool
UPC	198282630302
Warranty Disclaimer	<p>CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>