



**Part Number :** 395387030

**Series Number :** 39538

**Product Category :** Terminal Blocks and Barrier Strip

**Product Description :** 5.08mm Pitch Eurostyle Vertical Dual Level PCB Header, Open Ends, Green Housing, 30 Circuits

**Status :** Active

Documents & Resources

- Drawings**  
Drawing 395387030\_sd.pdf
- 3D Models and Design Files**  
3D Model 395387030\_stp.zip

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39538
Description	5.08mm Pitch Eurostyle Vertical Dual Level PCB Header, Open Ends, Green Housing, 30 Circuits
Application	N/A
Component Type	PCB Header
Product Family	Eurostyle Terminal Blocks
Product Name	Eurostyle Pluggable
Type	Euro Block
UPC	822350831192

### Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	300V

### Physical

Circuits (Loaded)	30
Entry Angle	N/A
Lock to Mating Part	Yes
Number of Rows	2
Orientation	Vertical
Panel Mount	No
PC Tail Length	3.50mm
PCB Thickness - Recommended	3.00mm
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Polarized to Mating Part	Yes
Shrouded	Open Ends
Stackable	Yes
Temperature Range - Operating	-40° to +105°C
Wire Size (AWG)	N/A

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	REFLOW
Max-Cycle	135
Max-Temp	260

---

Mates With / Use With

Mates with Part(s)

Description	Part Number
5.08mm Pitch Eurostyle Horizontal Plugs	<u>39530</u>
5.08mm Pitch Eurostyle Vertical Plugs	<u>39533</u>
Mates With	Most 5.08mm (.200") Pitch Industry Standard Plugs