


# Schottky Rectifier, 10 A






#### TO-220AC

PRODUCT SUMMARY					
Package	TO-220AC				
I <sub>F(AV)</sub>	10 A				
$V_R$	35 V, 40 V, 45 V				
V <sub>F</sub> at I <sub>F</sub>	0.49 V				
I <sub>RM</sub>	15 mA at 125 °C				
T <sub>J</sub> max.	175 °C				
Diode variation	Single die				
E <sub>AS</sub>	13 mJ				

#### **FEATURES**

- 175 °C T<sub>J</sub> operation
- · Low forward voltage drop
- High frequency operation





- · Guard ring for enhanced ruggedness and long term reliability
- Compliant to RoHS Directive 2002/95/EC
- Designed and qualified according to JEDEC-JESD47
- Halogen-free according to IEC 61249-2-21 definition (-N3 only)

### **DESCRIPTION**

The VS-10TQ... Schottky rectifier series has been optimized for low reverse leakage at high temperature. The proprietary barrier technology allows for reliable operation up to 175 °C junction temperature. Typical applications are in switching power supplies, converters, freewheeling diodes, and reverse battery protection.

MAJOR RATINGS AND CHARACTERISTICS							
SYMBOL CHARACTERISTICS VALUES UNITS							
I <sub>F(AV)</sub>	Rectangular waveform	10	А				
V <sub>RRM</sub>		35/45	V				
I <sub>FSM</sub>	t <sub>p</sub> = 5 μs sine	1050	A				
V <sub>F</sub>	10 A <sub>pk</sub> , T <sub>J</sub> = 125 °C	0.49	V				
T <sub>J</sub>	Range	- 55 to 175	°C				

VOLTAGE RATINGS									
PARAMETER	SYMBOL	VS- 10TQ035PbF	VS- 10TQ035-N3	VS- 10TQ040PbF	VS- 10TQ040-N3	VS- 10TQ045PbF	VS- 10TQ045-N3	UNITS	
Maximum DC reverse voltage	$V_R$								
Maximum working peak reverse voltage	$V_{RWM}$	35	35	40	40	45	45	V	

ABSOLUTE MAXIMUM RATINGS								
PARAMETER	SYMBOL	TEST COND	TEST CONDITIONS					
Maximum average forward current See fig. 5	I <sub>F(AV)</sub>	I <sub>F(AV)</sub> 50 % duty cycle at T <sub>C</sub> = 151 °C, rectangular waveform						
Maximum peak one cycle non-repetitive surge current		5 μs sine or 3 μs rect. pulse	Following any rated load condition and with rated	1050	Α			
See fig. 7	I <sub>FSM</sub>	10 ms sine or 6 ms rect. pulse	V <sub>RRM</sub> applied	280				
Non-repetitive avalanche energy	E <sub>AS</sub>	T <sub>J</sub> = 25 °C, I <sub>AS</sub> = 2 A, L = 6.5 mH		13	mJ			
Repetitive avalanche current	I <sub>AR</sub>		Current decaying linearly to zero in 1 $\mu$ s  Frequency limited by $T_J$ maximum $V_A = 1.5 \times V_R$ typical					



# VS-10TQ...PbF Series, VS-10TQ...-N3 Series

# Vishay Semiconductors

ELECTRICAL SPECIFICATIONS							
PARAMETER	SYMBOL	TEST CO	NDITIONS	VALUES	UNITS		
		10 A	T 05 00	0.57	V		
Maximum forward voltage drop See fig. 1	V <sub>FM</sub> <sup>(1)</sup>	20 A	T <sub>J</sub> = 25 °C	0.67			
		10 A	T 105 %C	0.49			
		20 A	T <sub>J</sub> = 125 °C	0.61			
Maximum reverse leakage current	I <sub>RM</sub> <sup>(1)</sup>	T <sub>J</sub> = 25 °C	V <sub>R</sub> = Rated V <sub>R</sub>	2	mA		
See fig. 2	'RM '''	T <sub>J</sub> = 125 °C	VR = nateu VR	15	l IIIA		
Maximum junction capacitance	C <sub>T</sub>	$V_R = 5 V_{DC}$ (test signal range 100 kHz to 1 MHz) 25 °C		900	pF		
Typical series inductance	L <sub>S</sub>	Measured lead to lead 5 mm from package body		8.0	nH		
Maximum voltage rate of change	dV/dt	Rated V <sub>R</sub>		10 000	V/μs		

#### Note

 $<sup>^{(1)}~</sup>$  Pulse width < 300  $\mu s,~duty~cycle < 2~\%$ 

THERMAL - MECHANICAL SPECIFICATIONS							
PARAMETER		SYMBOL	TEST CONDITIONS	VALUES	UNITS		
Maximum junction and storage temperature range	Э	T <sub>J</sub> , T <sub>Stg</sub>		- 55 to 175	°C		
Maximum thermal resistance, junction to case		R <sub>thJC</sub>	DC operation See fig. 4	2.0	°C/W		
Typical thermal resistance, case to heatsink		R <sub>thCS</sub>	Mounting surface, smooth and greased	0.50	C/VV		
Approximate weight				2	g		
Approximate weight				0.07	OZ.		
Mounting toyour	minimum			6 (5)	kgf · cm		
Mounting torque maximum				12 (10)	(lbf $\cdot$ in)		
Marking device			Casa at da TO 220AC	10TC	Q035		
			Case style TO-220AC	10TC	10TQ045		




Fig. 1 - Maximum Forward Voltage Drop Characteristics




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage




Fig. 4 - Maximum Thermal Impedance  $Z_{\text{thJC}}$  Characteristics




Fig. 5 - Maximum Allowable Case Temperature vs. Average Forward Current




Fig. 6 - Forward Power Loss Characteristics




Fig. 7 - Maximum Non-Repetitive Surge Current





Fig. 8 - Unclamped Inductive Test Circuit

# VS-10TQ...PbF Series, VS-10TQ...-N3 Series

Vishay Semiconductors

### **ORDERING INFORMATION TABLE**

**Device code** 



1 - Vishay Semiconductors product

2 - Current rating (10 = 10 A)

3 - Package:

T = TO-220

4 - Schottky "Q" series

035 = 35 V

5 - Voltage ratings

040 = 40 V045 = 45 V

6 - Environmental digit

• PbF = Lead (Pb)-free and RoHS compliant

• -N3 = Halogen-free, RoHS compliant, and totally lead (Pb)-free


ORDERING INFORMATION (Example)								
PREFERRED P/N	QUANTITY PER T/R	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION					
VS-10TQ035PbF	50	1000	Antistatic plastic tube					
VS-10TQ035-N3	50	1000	Antistatic plastic tube					
VS-10TQ040PbF	50	1000	Antistatic plastic tube					
VS-10TQ040-N3	50	1000	Antistatic plastic tube					
VS-10TQ045PbF	50	1000	Antistatic plastic tube					
VS-10TQ045-N3	50	1000	Antistatic plastic tube					

LINKS TO RELATED DOCUMENTS					
Dimensions <u>www.vishay.com/doc?95221</u>					
Deut erandin minfannakian	TO-220ACPbF	www.vishay.com/doc?95224			
Part marking information	TO-220AC-N3	www.vishay.com/doc?95068			



### **TO-220AC**

### **DIMENSIONS** in millimeters and inches



SYMBOL	MILLIN	IETERS	INC	HES	NOTES
STIVIBUL	MIN.	MAX.	MIN.	MAX.	NOTES
А	4.25	4.65	0.167	0.183	
A1	1.14	1.40	0.045	0.055	
A2	2.56	2.92	0.101	0.115	
b	0.69	1.01	0.027	0.040	
b1	0.38	0.97	0.015	0.038	4
b2	1.20	1.73	0.047	0.068	
b3	1.14	1.73	0.045	0.068	4
С	0.36	0.61	0.014	0.024	
c1	0.36	0.56	0.014	0.022	4
D	14.85	15.25	0.585	0.600	3
D1	8.38	9.02	0.330	0.355	
D2	11.68	12.88	0.460	0.507	6
Е	10.11	10.51	0.398	0.414	3, 6

SYMBOL	MILLIN	MILLIMETERS		INCHES		
STIVIBUL	MIN.	MAX.	MIN.	MAX.	NOTES	
E1	6.86	8.89	0.270	0.350	6	
E2	-	0.76	-	0.030	7	
е	2.41	2.67	0.095	0.105		
e1	4.88	5.28	0.192	0.208		
H1	6.09	6.48	0.240	0.255	6, 7	
L	13.52	14.02	0.532	0.552		
L1	3.32	3.82	0.131	0.150	2	
L3	1.78	2.13	0.070	0.084		
L4	0.76	1.27	0.030	0.050	2	
ØΡ	3.54	3.73	0.139	0.147		
Q	2.60	3.00	0.102	0.118		
θ	90° to 93°		90° t	o 93°		

#### Notes

- (1) Dimensioning and tolerancing as per ASME Y14.5M-1994
- (2) Lead dimension and finish uncontrolled in L1
- (3) Dimension D, D1 and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
- (4) Dimension b1, b3 and c1 apply to base metal only
- (5) Controlling dimension: inches
- (6) Thermal pad contour optional within dimensions E, H1, D2 and E1
- (7) Dimension E2 x H1 define a zone where stamping and singulation irregularities are allowed
- (8) Outline conforms to JEDEC TO-220, D2 (minimum) where dimensions are derived from the actual package outline



## **Legal Disclaimer Notice**

Vishay

### **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## **Material Category Policy**

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000