


VS-30CPQ1.0PbF Series, VS-30CPQ1.0-N3 Series

www.vishay.com

Vishay Semiconductors

Schottky Rectifier, 2 x 15 A







TO-247AC
10 11710
2 x 15 A
140 V, 150 V
0.78 V
15 mA at 125 °C
175 °C
Common cathode
11.25 mJ

FEATURES

- 175 °C T_J operation
- Low forward voltage drop
- · High frequency operation







 Material categorization: For definitions of compliance please see <u>www.vishay.com/doc?99912</u>







FREE

DESCRIPTION

The VS-30CPQ... center tap Schottky rectifier series has been optimized for low reverse leakage at high temperature. The proprietary barrier technology allows for reliable operation up to 175 °C junction temperature. Typical applications are in switching power supplies, converters, freewheeling diodes, and reverse battery protection.

MAJOR RATINGS AND CHARACTERISTICS							
SYMBOL	CHARACTERISTICS	VALUES	UNITS				
I _{F(AV)}	Rectangular waveform	30	A				
V _{RRM}		150	V				
I _{FSM}	t _p = 5 µs sine	1000	A				
V _F	15 A _{pk} , T _J = 125 °C (per leg)	0.78	V				
T _J		- 55 to 175	°C				

VOLTAGE RATINGS							
PARAMETER	SYMBOL	VS-30CPQ140PbF	VS-30CPQ140-N3	VS-30CPQ150PbF	VS-30CPQ150-N3	UNITS	
Maximum DC reverse voltage	V_R						
Maximum working peak reverse voltage	V _{RWM}	140	140	150	150	V	

ABSOLUTE MAXIMUM RATINGS							
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS		
Maximum average per devi	е	50 % duty cycle at T _C = 135 °C, rectangular waveform				30	
forward current See fig. 5	eg I _{F(AV)}			15	Δ.		
Maximum peak one cycle non-repetitive surge current per leg	l=a	5 μs sine or 3 μs rect. pulse	Following any rated load condition and with rated	1000	А		
See fig. 7	I _{FSM}	10 ms sine or 6 ms rect. pulse	V _{RRM} applied	340			
Non-repetitive avalanche energy per leg	E _{AS}	$T_{J} = 25 ^{\circ}\text{C}, I_{AS} = 0.50 \text{A}, L = 90 \text{mH}$		11.25	mJ		
Repetitive avalanche current per leg	I _{AR}	Current decaying linearly to ze Frequency limited by T _J maxim		0.50	Α		

Revision: 17-Jul-13 Document Number: 94186



VS-30CPQ1.0PbF Series, VS-30CPQ1.0-N3 Series

www.vishay.com

Vishay Semiconductors

ELECTRICAL SPECIFICATIONS						
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS	
		15 A	T _{.1} = 25 °C	1.00		
Maximum forward voltage drop per leg	V _{FM} ⁽¹⁾	30 A	1] = 23 0	1.19	V	
See fig. 1	VFM ('')	15 A	T _{.1} = 125 °C	0.78		
		30 A	1j=125 C	0.93		
Maximum reverse leakage current per leg	I _{RM} ⁽¹⁾	T _J = 25 °C	V _B = Rated V _B	0.1	- mA	
See fig. 2		T _J = 125 °C	v _R = nateu v _R	15		
Maximum junction capacitance per leg	C _T	V _R = 5 V _{DC} (test signal range 100 kHz to 1 MHz) 25 °C		340	pF	
Typical series inductance per leg	L _S	Measured lead to lead 5 mm from package body		7.5	nΗ	
Maximum voltage rate of change	dV/dt	Rated V _R		10 000	V/µs	

Note

 $^{^{(1)}\,}$ Pulse width < 300 $\mu s,$ duty cycle < 2 %

THERMAL - MECHANICAL SPECIFICATIONS						
PARAMETER		SYMBOL	TEST CONDITIONS	VALUES	UNITS	
Maximum junction and stora temperature range	ge	T _J , T _{Stg}		- 55 to 175	°C	
Maximum thermal resistance, junction to case per leg		R_{thJC}	DC operation See fig. 4	2.20		
Maximum thermal resistance, junction to case per package		□thJC	DC operation	1.10	°C/W	
Typical thermal resistance, case to heatsink		R _{thCS}	Mounting surface, smooth and greased	0.24		
Approximate weight				6	g	
Approximate weight				0.21	OZ.	
Mounting torque	minimum			6 (5)	kgf · cm	
Mounting torque -	maximum			12 (10)	(lbf · in)	
Marking daving			Coop of the TO 247AC (IEDEC)	30CP	Q140	
Marking device			Case style TO-247AC (JEDEC)	30CP	Q150	

www.vishay.com

Vishay Semiconductors




Fig. 1 - Maximum Forward Voltage Drop Characteristics (Per Leg)




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage (Per Leg)




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage (Per Leg)




Fig. 4 - Maximum Thermal Impedance Z_{thJC} Characteristics (Per Leg)

www.vishay.com

Vishay Semiconductors




Fig. 5 - Maximum Allowable Case Temperature vs. Average Forward Current (Per Leg)




Fig. 6 - Forward Power Loss Characteristics (Per Leg)




Fig. 7 - Maximum Non-Repetitive Surge Current (Per Leg)




Fig. 8 - Unclamped Inductive Test Circuit

Note


 $^{(1)}$ Formula used: T_C = T_J - (Pd + Pd_{REV}) x R_{thJC}; Pd = Forward power loss = I_{F(AV)} x V_{FM} at (I_{F(AV)}/D) (see fig. 6); Pd_{REV} = Inverse power loss = V_{R1} x I_R (1 - D); I_R at V_{R1} = 80 % rated V_R

VS-30CPQ1.0PbF Series, VS-30CPQ1.0-N3 Series

Vishay Semiconductors

ORDERING INFORMATION TABLE





1 - Vishay Semiconductors product

2 - Current rating (30 = 30 A)

3 - Circuit configuration:

C = Common cathode

4 - Package:

P = TO-247

5 - Schottky "Q" series

140 = 140 V

6 - Voltage code

150 = 150 V

7 - Environmental digit

• PbF = Lead (Pb)-free and RoHS compliant

• -N3 = Halogen-free, RoHS compliant, and totally lead (Pb)-free

ORDERING INFORMATION (Example)							
PREFERRED P/N	QUANTITY PER T/R	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION				
VS-30CPQ140PbF	25	500	Antistatic plastic tube				
VS-30CPQ140-N3	25	500	Antistatic plastic tube				
VS-30CPQ150PbF	25	500	Antistatic plastic tube				
VS-30CPQ150-N3	25	500	Antistatic plastic tube				


LINKS TO RELATED DOCUMENTS						
Dimensions www.vishay.com/doc?95542						
Dort marking information	TO-247ACPbF	www.vishay.com/doc?95226				
Part marking information	TO-247AC-N3	www.vishay.com/doc?95007				



Vishay Semiconductors

TO-247AC - 50 mils L/F

DIMENSIONS in millimeters and inches



SYMBOL	MILLIM	IETERS	INC	HES	NOTES
STWIDGE	MIN.	MAX.	MIN.	MAX.	NOTES
Α	4.65	5.31	0.183	0.209	
A1	2.21	2.59	0.087	0.102	
A2	1.17	1.37	0.046	0.054	
b	0.99	1.40	0.039	0.055	
b1	0.99	1.35	0.039	0.053	
b2	1.65	2.39	0.065	0.094	
b3	1.65	2.34	0.065	0.092	
b4	2.59	3.43	0.102	0.135	
b5	2.59	3.38	0.102	0.133	
С	0.38	0.89	0.015	0.035	
c1	0.38	0.84	0.015	0.033	
D	19.71	20.70	0.776	0.815	3
D1	13.08	-	0.515	-	4

SYMBOL	MILLIN	IETERS	INC	HES	NOTES
STWIDOL	MIN.	MAX.	MIN.	MAX.	NOTES
D2	0.51	1.35	0.020	0.053	
Е	15.29	15.87	0.602	0.625	3
E1	13.46	-	0.53	-	
е	5.46	BSC	0.215	BSC	
ØK	0.254		0.0	10	
L	14.20	16.10	0.559	0.634	
L1	3.71	4.29	0.146	0.169	
ØΡ	3.56	3.66	0.14	0.144	
Ø P1	-	7.39	-	0.291	
Q	5.31	5.69	0.209	0.224	
R	4.52	5.49	0.178	0.216	
S	5.51 BSC		0.217	BSC	

Notes

- (1) Dimensioning and tolerancing per ASME Y14.5M-1994
- (2) Contour of slot optional
- (3) Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
- (4) Thermal pad contour optional with dimensions D1 and E1
- (5) Lead finish uncontrolled in L1
- (6) Ø P to have a maximum draft angle of 1.5 to the top of the part with a maximum hole diameter of 3.91 mm (0.154")
- $^{(7)}$ Outline conforms to JEDEC® outline TO-247 with exception of dimension c and Q



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.