

Data sheet

RP015xxVBLF Typ 351

Page 1/6

P/N

313511xx

xx=number of poles



2021/09/15

Version: R

Illustrations



Dimensional drawing



See enlarged drawings at the end of document

Product specification

- screw type terminal block, pluggable
- centerline 5.00 mm, direction of connection vertical 0°
- lift system
- color black, mounting flange
- wire entry codeable side perpendicular to plug direction



Data sheet

RP015xxVBLF Typ 351

Page 2/6

P/N
313511xx

xx=number of poles

2021/09/15

Version: R

Technical Data

General Data

Tightening torque SEV	0.5 Nm		
Tightening torque UL	4.4 lb-in		
min. number of poles	2		
max. number of poles	24		
Insulating material class	CTI 600		
clearance/creepage dist.	3.6 mm		
Protection category	IP20		
Min. insul. strip length	8 mm		
Rated current	12 A		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	160 V	400 V	400 V
Rated test voltage	2.5 kV	2.5 kV	2.5 kV

Anschlussdaten

rat.wiring solid AWGmax	0.08 mm ² - 2.5 mm ² / AWG 28 - AWG 12
rat.wiring strand.AWGmax	0.08 mm ² - 2.5 mm ² / AWG 28 - AWG 12

Approvals

extended wiring UL	2 AWG 16-18, or 1 AWG 16 stranded with 1 AWG 18 solid, or 1 AWG 16 stranded with 1 AWG 18 stranded
--------------------	--

 V / A / AWG	300 / 16 / 28 - 12
---	--------------------

approval UL - File No.	E121004
------------------------	---------

 2.5 mm ²	320 V / 4 kV / 13.5 A
---	-----------------------

Material

insulating material	PA66
flammability class	V0
contact material	CuSn
Contact surface	Sn
terminal body thread	M3
terminal body material	CuZnPb
terminal body surface	Ni
screw thread	M3
screw material	8,8
screw surface	Zn Cr(VI)-frei/free
Glow-Wire Flammability GWFI	960 °C acc. to IEC 60695-2-12

U | Contact

Data sheet

RP015xxVBLF Typ 351

Page 3/6

P/N

313511xx

xx=number of poles

2021/09/15

Version: R

Technical Data

Glow-Wire Flammability GWIT	775 °C acc. to IEC 60695-2-13
REACH - substance (SVHC)	Lead / 7439-92-1

Climatic Data

upper limit temperature	105 °C
lower limit temperature	-40 °C

general

Tolerance	ISO 2768 -mH
-----------	--------------

U | Contact

Data sheet

Page 4/6

RP015xxVBLF Typ 351

P/N

313511xx**xx=number of poles**

2021/09/15

Version: R

Accessories

P/N	Designation
700025-01-9	Coding star white with a group of 6 coding pins



U | Contact

Data sheet

Page 5/6

RP015xxVBLF Typ 351

P/N

313511xx**xx=number of poles**

2021/09/15

Version: R

Counterpart

P/N	Designation
313351	PT115xxVBBF Typ 335
313361	PT115xxHBBF Typ 336
313961	PR065xxHBBF Typ 396
313971	PR065xxVBBF Typ 397

U | Contact

Data sheet

RP015xxVBLF Typ 351

Page 6/6

P/N

313511xx


xx=number of poles

2021/09/15

Version: R

Illustrations

Dimensional drawing



$L = (\text{pole size} - 1) \times \text{centerline} + 14.6 \text{ mm} [0.575]$