


CVF020W5 - Plug

<https://www.sauro.net/product/CVF020W5>



Number of poles: 2, Clamp tightening, 15A, 2.5mm², 12AWG, 300V, Pitch 5,08 mm, Modular, Wiring mode Left, Green (RAL 6032), Soldering technology Not applicable, UL, IMQ, CSA

General data

Number of poles	2
Number of levels	1
Sides configuration	Modular
Pitch	5,08 mm
Voltage	300 V
Current	15 A
Housing composition	Monolithic
Wire section	2.5 mm ²
Wire section	30 AWG ÷ 12 AWG
Available approvals	UL, IMQ, CSA

Features

Screw dimension	M3
Recommended tightening torque	0.5 Nm
Stripping length	7.5 mm
Operating temperature range	-40°C ÷ 105°C
Climatic category	-40/105/21 according to EN60068-1
Contact resistance	<15 mOhm
Insulation resistance	>1 GOhm

Certifications

<https://www.sauro.net/product/CVF020W5>

CVF020W5 - Plug



<https://www.sauro.net/product/CVF020W5>

UL (n.E167473)

Usage Group	B	C	D*
Rated voltage	300 V		300 V
Nominal current		15 A	
Wire section		12 AWG	
Tightening torque		7 lbf x in	

* These limited ratings are applicable to a terminal block for use in or with industrial control equipment whereby the load on any single circuit of the terminal block does not exceed 15A at 51-150V, 10A at 151-300V, or 5A at 301-600V, or the maximum ampere rating, whichever is less.

CSA (n.LR 102896)

Rated voltage	300 V
Nominal current	15 A
Wire section	12 AWG
Tightening torque	7 lbf x in

IMQ (n.EM672)

Rated voltage	300 V		
Nominal current	12 A		
Wire section	2.5 mm²		
Insulating category	I		
Overvoltage category/Pollution degree	III/3	III/2	II/2
Impulse voltage	4kV	4kV	4kV
Rated voltage	250V	300V	600V
Insulation voltage	250V	320V	630V
Maximum temp usage	110		

Materials

Screw material	Nickel-plated copper alloy
Spring contact	Tin-plated copper alloy
Clamp tightening	Nickel-plated copper alloy
Insulating housing material	PA Polyamide
Insulating material group	I (CTI >= 600V)

Available colors

Green	similar to RAL 6032
Dark green	similar to RAL 6017
Black	similar to RAL 9005

<https://www.sauro.net/product/CVF020W5>

CVF020W5 - Plug



<https://www.sauro.net/product/CVF020W5>


Light gray	similar to RAL 7035
Dark gray	similar to RAL 7040
Orange	similar to RAL 2003
Blue	similar to RAL 5012
Brown	similar to RAL 8028
Yellow	similar to RAL 1018
White	similar to RAL 9001
Red	similar to RAL 3017
Another color	on demand

<https://www.sauro.net/product/CVF020W5>


CVF020W5 - Plug

<https://www.sauro.net/product/CVF020W5>


Usable with




CIM020A5




CIM020E5



CIM020M5



CIM020P5



CIM020V5




CIM024A5




CIM024M5




CIM024P5




CIM024V5




CIM025A5




CIM025E5




CIM025M5




CIM025P5




CIM025V5




CIM029A5




CIM029E5




CIM029M5



CIM029P5



CIM029V5




CIM02RA5



CIMH020A5-0N



CIMH020F5-0N




CIMH020P5-0N




CIMH020V5-0N



CIMH024M5-0N




CIMH024P5-0N



CIMH024V5-0N



CIMH025A5-0N



CIMH025V5-0N




CIMH029A5-0N


<https://www.sauro.net/product/CVF020W5>

CVF020W5 - Plug


<https://www.sauro.net/product/CVF020W5>




CIMH029F5-0N




CIMH029P5-0N



CIMH029S5-0N



CIMH029V5-0N




CPM020M5




CPM020P5



CPM029M5



CPM029P5



CPMH020M5-0N




CPMH020P5-0N




CPMH029M5-0N




CPMH029P5-0N



CRM020M5




CRM020P5



CRM029M5




CRM029P5





CGM020A5



CGM020M5



CGM020P5



sauro.net

<https://www.sauro.net/product/CVF020W5>