

MOTOR CHARACTERISTICS CURVE

REFERENCE ONLY

Model# : JYN30SA-13107-28VU

PERFORMANECE			
VOLTAGE	DEPRATING RANGE	V/DC	2.0~6.0
	VOLTAGE	V/DC	3.0
AT NO LOAD	SPEED	r/min	9600
	CURRENT	A	0.035
A T MAXINUM EFFICIENCY	EFFICIENCY	%	49.48%
	SPEED	r/min	8000
	CURRENT	A	0.17
	TORQUE	g-cm	3.0
	OUTPUT	W	0.25
AT MAX POWER	OUTPUT	W	0.4
	SPEED	r/min	4800
	CURRENT	A	0.43
	TORQUE	g. cm	9
AT STALL	TORQUE	g. cm	18
	CURRENT	A	0.82

