

Data sheet ASD-C18

Page 1/7

P/N
110270

EAN 4250184120940


2024/10/23

Version: G


Illustrations



Dimensional drawing



Wiring diagram



See enlarged drawings at the end of document

Product specification

Monitoring relay for monitoring asymmetry, phase failure, phase sequence errors, overvoltage and undervoltage of a three-phase connection. With external fault acknowledgement.

- Connection with screw type terminal blocks
- Adjustable response delay
- Adjustable asymmetry
- Selectable fault memory
- 7-segment display
- Not intended for marketing in North America



Technical Data

Supply

Operating voltage	230 V AC -15% ... +10%
Frequency range	50 Hz
Power consumption (max.)	15 mA
Duty cycle relative	100 %

Inputs

Monitoring voltage (L1, L2, L3)	3 x 230/400 V AC, 50 Hz
Response delay	0.1 s - 9.9 s, adjustable
Confirmation time, adjustable	0,1 ... 9,9 min.
Asymmetry, adjustable	5 ... 20 %
Switching hysteresis	20 %
Measurement cycle	max. 100 ms
Temperature error	<= 0.06 %/°C
Measurement error within the operating voltage	<= 5 %

Outputs

Contacts	2 changeover contacts
Contact material	AgNi
Switching voltage (max.)	250 V AC
Continuous Current	8 A
Pick-up delay	230 V~ 6 A AC1
Switch-off delay	230 V~ 3 A AC3
Switching frequency	360 switching cycles/h
Mechanical life	3x10 ⁷ switching cycles
Electrical life	1x10 ⁵ switching cycles
Indicator	green LED

Housing

Dimensions	
Dimension (W x H x D)	50 mm x 69.3 mm x 60 mm
Dimension (W x H x D)	1.969 in. x 2.728 in. x 2.362 in.
Weight	200 g
Mounting style	Standard rail TH35
Mounting position	any



Technical Data	
Housing	
Apposition	without distance
Connection type	Screw type terminal blocks
Terminal blocks	
Wire cross section solid	0.34 mm ² - 2.5 mm ² / AWG 22-12
Wire cross section multi	0.25 mm ² - 2.5 mm ² / AWG 22-12
Wire cross section with wire ferrule	0.25 mm ² - 2.5 mm ² / AWG 22-12
Screw torque (max.)	0.5 Nm
Stripping length (min.)	8 mm
Material	
Material - Housing	Polyamid 6.6 V0
Color	gray
Material - Terminal block	Polyamid 6.6 V0
Material - Covers	Polycarbonat
Protection category according to IEC 60529	
Protection category - housing (acc. to IEC 60529)	IP40
Protection category - terminal blocks (acc. to IEC 60529)	IP20
Climatic Data	
Operating	
Temperature - Operating °C	-5 °C - 55 °C
Temperature - Operating °F	23 °F - 131 °F
Relative humidity	max. 85 % non-condensing
Storage	
Temperature - Storage °C	-20 °C - 70 °C
Temperature - Storage °F	-4 °F - 158 °F
Power loss	
Power loss (typical)	5 W

Technical Data

Classifications

ETIM 7.0	EC001441
ETIM 8.0	EC001441
ETIM 9.0	EC001441


Application note

This product is a standard product of METZ CONNECT. METZ CONNECT is not aware of the specific intended use of the goods by the Customer or any customers of the Customer. The Customer guarantees that it has fully and sufficiently tested the use of the goods and any product modifications, product changes or product enhancements with regard to the specific intended use in accordance with the state of the art or in any other way. At METZ CONNECT's request, the Customer shall submit and make available meaningful evidence (e.g. test and laboratory protocols, certifications, etc.).




Illustrations

Dimensional drawing




Wiring diagram




Illustrations

Schaltbeispiel




Function diagram



Illustrations

Function diagram



Function diagram

